



# CORDLESS POWER TOOLS

**GUARANTEED TOUGH.**

**20V MAX\* COMBO KITS**  
*(continued)*



**20V MAX\* Lithium Ion 4-Tool Combo Kit (3.0Ah)**



**20V MAX\*/12V MAX\* Lithium Ion 2-Tool Combo Kit**



**20V MAX\* Lithium Ion 2-Tool Combo Kit (3.0Ah)**



**20V MAX\* Lithium Ion 2-Tool Combo Kit (3.0Ah)**

SPECIFICATIONS	DCK490L2	DCK294L3	DCK292L2	DCK290L2
Volts	20V MAX*	20V MAX*/12V MAX*	20V MAX*	20V MAX*
Hammerdrill	DCD985	DCD985 (20V MAX*)	DCD985	DCD985
Reciprocating Saw	DCS381	-	DCS380	-
Impact Driver	DCF885	-	-	DCF885
Screwdriver	-	DCF610 (12V MAX*)	-	-
LED Worklight	DCL040	-	-	-
Charger/Batteries	Fast Charger / (2) 20V MAX* Lithium Ion 3.0 Ah	Fast Charger / (2) 20V MAX* Lithium Ion 3.0 Ah, (1) 12V MAX* Lithium Ion	Fast Charger / (2) 20V MAX* Lithium Ion 3.0 Ah	Fast Charger / (2) 20V MAX* Lithium Ion 3.0 Ah
Includes	360° side handle & belt hook	360° side handle bit lip and belt hook	360° side handle	360° side handle and belt hook



**20V MAX\* Lithium Ion 2-Tool Combo Kit (1.5Ah)**



**20V MAX\* Lithium Ion 2-Tool Combo Kit (1.5Ah)**

SPECIFICATIONS	DCK285C2	DCK280C2
Volts	20V MAX*	20V MAX*
Hammerdrill	DCD785	-
Drill/Driver	-	DCD780
Impact Driver	DCF885	DCF885
Charger/Batteries	Fast Charger / (2) 20V MAX* Lithium Ion 1.5 Ah	Fast Charger / (2) 20V MAX* Lithium Ion 1.5 Ah
Includes	(2) belt hooks and bit holder	(2) belt hooks and bit holder

**18V COMBO KITS**



**18V Cordless 9-Tool Combo Kit**

SPECIFICATIONS	DCK955X
Volts	18V
Hammerdrill/Drill/Driver	DCD950
Circular Saw	DC390 (6-1/2")
Reciprocating Saw	DC385
Out-Of Tool	DC411
Out-Of Tool	DCS50
Jig Saw	DC330
Impact Driver	DC825
Impact Wrench	DW059
Flexible Floodlight	DW919
Charger/Batteries	1 Hour Charger / (2) 18V XRP™
Includes	360° side handle, carbide tipped circular saw blade, type 1 guard, wrench, (2) matched flanges, 2-position side handle

**18V COMBO KITS**



**18V Cordless Li-Ion 6-Tool Combo Kit**



**18V Cordless 6-Tool Combo Kit**



**18V Cordless 5-Tool Combo Kit**



**18V Cordless Li-Ion 4-Tool Combo Kit**

SPECIFICATIONS	DCK673L	DCK655X	DCK555X	DCK475L
Volts	18V	18V	18V	18V
Hammerdrill/Drill/Driver	DCD970	DCD950	DCD950	DCD970
Circular Saw	-	DC390 (6-1/2")	DC390 (6-1/2")	-
Reciprocating Saw	DC385	DC385	DC385	DC385
Out-Of Tool	DC411	DC411	-	-
Out-Of Tool	-	-	-	-
Jig Saw	-	-	-	-
Impact Driver	DC827	DC825	DC825	DC827
Impact Wrench	DW059	-	-	-
Flexible Floodlight	DW919	DW919	DW919	DW919
Charger/Batteries	1 Hour NiCd/MH/Li-Ion Charger / (2) 18V XRP™ Li-Ion	1 Hour Charger / (2) 18V XRP™	1 Hour Charger / (2) 18V XRP™	1 Hour NiCd/MH/Li-Ion Charger / (2) 18V XRP™ Li-Ion
Includes	360° side handle, type 1 guard, wrench, (2) matched flanges, 2-position side handle	360° side handle, carbide tipped circular saw blade, type 1 guard, wrench, (2) matched flanges, (1) type 1 wheel, & 2-position side handle	360° side handle & carbide tipped circular saw blade	360° side handle