




Hex Nuts / Machine Screw & Finished PC 4100, 4010, 4300, 4015, 4018

FASTENERS & HARDWARE > HEX NUTS

Hex machine screw nuts are for screws smaller than 1/4" diameter. Finished hex nuts are heavier (thicker) and are furnished in sizes 1/4" and up.

- Zinc Plated - General Use
- Grade 5 - Medium Strength
- Stainless - Corrosion & Chemical Resistant
- Solid Brass Good Near Water & Salt Air
- Silicon Bronze: Harder Than Brass - Used In Direct Burial
- Invincibox™ Up To 1/2"

CAT NO	UPC		SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
Zinc Plated Steel - PC 4100								
HN632	17010		6-32	100	500	4000	0.21#	C
HN832	17015	Machine	8-32	100	500	4000	0.28#	C
HN1024	17020	Screw	10-24	100	500	4000	0.33#	C
HN1032	17025	Nuts	10-32	100	500	4000	0.33#	C
HN1224	17030		12-24	100	500	2000	0.56#	C
HN14	17035		1/4-20	100	500	2000	0.68#	C
HN516	17040		5/16-18	50	250	2000	0.51#	C
HN38	17045	Finished	3/8-16	50	250	2000	0.74#	C
HN12	17050	Hex	1/2-13	25	125	1000	0.90#	C
HN58	17055	Nuts	5/8-11	25	125	750	1.77#	C
HN34	17060		3/4-10	25	125	250	2.95#	C
HNT14	17051	Tuff Pack	1/4-20	500		3000	3.70#	C
HNT38	17052		3/8-16	250		1500	3.86#	C
HNT12	17053		1/2-13	150		900	4.62#	C
Stainless Steel - PC 4010								
HNS632	69776		6-32	100	500	4000	0.22#	C
HNS832	69878	Machine	8-32	100	500	4000	0.30#	C
HNS1024	69780	Screw	10-24	100	500	4000	0.33#	C
HNS1032	69872	Nuts	10-32	100	500	4000	0.32#	C
HNS1224	69784		12-24	100	500	2000	0.58#	C
HNS14	69786		1/4-20	100	500	2000	0.72#	C
HNS516	69788		5/16-18	50	250	2000	0.55#	C
HNS38	69790	Finished	3/8-16	50	250	2000	0.79#	C
HNS12	69792	Hex	1/2-13	25	125	1000	1.22#	C
HNS58	69794	Nuts	5/8-11	25	125	750	1.84#	C
HNS34	69796		3/4-10	25	125	250	2.95#	C
Solid Brass - PC 4300								
HNBR632	17110		6-32	100	500	4000	0.21#	C
HNBR832	17115	Machine	8-32	100	500	4000	0.28#	C
HNBR1024	17120	Screw	10-24	100	500	4000	0.33#	C
HNBR1032	17125	Nuts	10-32	100	500	4000	0.33#	C
HNBR1224	17150		12-24	100	500	4000	0.56#	C
HNBR14	17135		1/4-20	100	500	4000	0.68#	C
HNBR516	17105	Finished	5/16-18	50	250	2000	0.51#	C
HNBR38	17140	Hex	3/8-16	50	250	2000	0.74#	C
HNBR12	17145	Nuts	1/2-13	25	125	1000	0.90#	C
Silicon Bronze - PC 4015								
HNBZ632	17160		6-32	100	500	4000	0.21#	C
HNBZ832	17161	Machine	8-32	100	500	4000	0.28#	C
HNBZ1024	17162	Screw	10-24	100	500	4000	0.33#	C
HNBZ1032	17163	Nuts	10-32	100	500	4000	0.33#	C
HNBZ14	17164		1/4-20	100	500	4000	0.68#	C
HNBZ516	17165	Finished	5/16-18	50	250	2000	1.02#	C
HNBZ38	17166	Hex	3/8-16	50	250	2000	0.75#	C
HNBZ12	17167	Nuts	1/2-13	25	125	1000	1.02#	C
Grade 5 - Zinc Plated - PC 4018								
5HN14	13000		1/4-20	100	500	4000	0.68#	C
5HN38	13001	Finished	3/8-16	50	250	2000	0.75#	C
5HN12	13002	Hex	1/2-13	25	125	1000	0.90#	C
5HN58	13003	Nuts	5/8-11	25	125	750	1.85#	C
5HN34	13004		3/4-10	25	125	500	2.97#	C



Dottie

To Order: Phone (323)725-1000 / Fax (323)721-0000