



**Fastener Kits  
PC 4760**

Dottie introduced assorted screw kits over 40 years ago and has a comprehensive variety for almost any imaginable need.

- Reusable Six Compartment Box
- Handy Assortment

| CAT NO                           | UPC   | DESCRIPTION   | STD | MSTR | WT/STD | UNIT |
|----------------------------------|-------|---|-----|------|--------|------|
| 632                              | 18140 | 370 Assorted 6-32 Slotted Flat Head Machine Screws; 3/4" Thru 3"<br>100 - 1/2", 75 - 3/4", 75 - 1", 50 - 1-1/4", 40 - 1-1/2", 30 - 2"   | 1   | 6    | 1.85#  | Ea   |
| 632DD                            | 29655 | 370 Assorted 6-32 Square/Phillips Flat Head Machine Screws; 1/2" Thru 2"<br>100 - 1/2", 75 - 3/4", 75 - 1", 50 - 1-1/4", 40 - 1-1/2", 30 - 2"                                       | 1   | 6    | 1.88#  | Ea   |
| 632PS                            | 29657 | 370 Assorted 6-32 Phillips/Slotted Round Head Machine Screws; 1/2" Thru 2", 100 - 1/2", 75 - 3/4", 75 - 1", 50 - 1-1/4", 40 - 1-1/2", 30 - 2"                                       | 1   | 6    | 1.59#  | Ea   |
| 832DS                            | 29665 | 310 Assorted 8-32 Square/Slotted Round Head Machine Screws; 1/2" Thru 2"<br>100 - 1/2", 60 - 3/4", 50 - 1", 40 - 1-1/4", 35 - 1-1/2", 25 - 2"                                       | 1   | 6    | 2.31#  | Ea   |
| 832PS                            | 29660 | 370 Assorted 8-32 Phillips/Slotted Round Head Machine Screws; 1/2" Thru 2"<br>100 - 1/2", 75 - 3/4", 75 - 1", 50 - 1-1/4", 40 - 1-1/2", 30 - 2"                                     | 1   | 6    | 2.30#  | Ea   |
| 1032PS                           | 10323 | 245 Assorted 10-32 Phillips/Slotted Round Head Machine Screws; 1/2" Thru 2"<br>75 - 1/2", 50 - 3/4", 40 - 1", 30 - 1-1/4", 25 - 1-1/2", 25 - 2"                                     | 1   | 6    | 3.13#  | Ea   |
| 1420PS                           | 14205 | 110 Assorted 1/4-20 Phillips/Slotted Round Head Machine Screws; 1/2" Thru 2"<br>30 - 1/2", 25 - 3/4", 20 - 1", 15 - 1-1/4", 10 - 1-1/2", 10 - 2"                                    | 1   | 6    | 1.87#  | Ea   |
| <b>Stove Bolt Kits with Nuts</b> |       |   |     |      |        |      |
| 316                              | 16560 | 220 Assorted 3/16 (10-24) Slotted Truss Head Stove Bolts with Hex Nuts; 1/2" Thru 2"<br>50 - 1/2", 50 - 3/4", 40 - 1", 30 - 1-1/4", 30 - 1 1/2", 20 - 2"                            | 1   | 6    | 2.82#  | Ea   |
| 1420                             | 14200 | 110 Assorted 1/4-20 Slotted Truss Head Stove Bolts with Hex Nuts; 1/2" Thru 2"<br>30 - 1/2", 25 - 3/4", 20 - 1", 15 - 1-1/4", 10 - 1-1/2"   | 1   | 6    | 2.77#  | Ea   |
| <b>Hex Nut Kit</b>               |       |   |     |      |        |      |
| 339                              | 17000 | 339 Assorted Zinc Plated Hex Nuts<br>10 sizes: 6-32" Thru 5/8": 50 - 6-32", 50 - 8-32", 50 - 10-24", 25 - 10-32", 25 - 12-24", 75 - 1/4", 25 - 5/16", 30 - 3/8", 6 - 1/2", 3 - 5/8" | 1   | 6    | 2.60#  | Ea   |



**Machine Screw Kit • Truss Head  
PC 4760**

Dottie introduces the Truss Head Combo Assorted Machine Screw Kit. Contractors speak and Dottie listens. These Truss Head Machine Screws are needed when installing wiring devices behind wall plates. Great when a low profile fastener is needed.

- Truss Head
- Low Profile
- Phillips / Slotted
- Zinc Plated

| CAT NO | UPC   | DESCRIPTION  | STD | MSTR | WT/STD | UNIT |
|--------|-------|--|-----|------|--------|------|
| 632TCS | 29658 | 370 Assorted 6-32 Slotted / Phillips Truss Head Machine Screws; 1/2" thru 2"<br>100 - 1/2", 75 - 3/4, 75 - 1", 50 - 1-1/4", 40 - 1-1/2", 30 - 2" | 1   | 6    | 1.59#  | Ea   |

