

Premium Color Coding PVC Tape PC 5330

- UL Listed
- 7.5 Mil 3/4" x 66 Ft.
- 600 Volt Rated, 80° C, 176° F
- Individual Cello Wrap - 10 Per STD Sleeve
- Weather & Cold Resistant
- Flame Retardant

PVC Tape is used for insulation and protection over wires and connectors or over splicing and filler compounds; the holding of high voltage electrical appliances; color code identification; wire harnessing and home maintenance.



CAT NO	UPC	DIMENSIONS	COLOR	STD	MSTR	WT/STD	UNIT
66CBLU	59650	3/4" x 66'	Blue	10	100	2.22#	Ea
66CBRN	59651	3/4" x 66'	Brown	10	100	2.22#	Ea
66CGRN	59652	3/4" x 66'	Green	10	100	2.22#	Ea
66CGRY	59653	3/4" x 66'	Gray	10	100	2.22#	Ea
66CORG	59654	3/4" x 66'	Orange	10	100	2.22#	Ea
66CRED	59655	3/4" x 66'	Red	10	100	2.22#	Ea
66CWHT	59656	3/4" x 66'	White	10	100	2.22#	Ea
66CYEL	59657	3/4" x 66'	Yellow	10	100	2.22#	Ea

Premium Black PVC Tape 99PC

UPC	15431	DIMENSIONS	3/4" x 66'	COLOR	Black	STD	10	MSTR	100	WT/STD	2.22#	UNIT	Ea
-----	-------	------------	------------	-------	-------	-----	----	------	-----	--------	-------	------	----

Economy PVC Tape PC 5350

- UL Listed
- 600 Volt Rated, 80° C, 176° F
- 7 Mil 3/4" x 60 Ft.
- Individual Cello Wrap - 10 Per STD Sleeve

PVC Tape is used for insulation and protection over wires and connectors or over splicing and filler compounds; the holding of high voltage electrical appliances; wire harnessing and home maintenance.



CAT NO	UPC	DIMENSIONS	COLOR	STD	MSTR	WT/STD	UNIT
360	15890	3/4" x 60'	Black	10	200	1.81#	Ea

Rubber Tape PC 5370

- UL Listed
- 3/4" x 22 Ft.
- 30 Mil

Rubber Tape is used in combination with friction and vinyl tape for primary insulation up to 600 volts and for use around split bolt connections, terminal lugs and compression connectors. It is used in insulating and waterproof applications, and easily conforms to irregular shapes and surfaces yielding a void free, electrically stable buildup. It is compatible with all extruded dielectric cable insulations.



CAT NO	UPC	DIMENSIONS	STD	MSTR	WT/STD	UNIT
822	28120	3/4" x 22'	10	100	3.60#	Ea

Friction Tape PC 5360

- UL Listed
- 3/4" x 60 Ft.
- 600 Volt Rated
- Adhesive Compound on Both Sides

Friction Tape is used for providing mechanical protection against abrasion and penetration of cable, splices and wire. Also used as a temporary binding and harnessing tape and a multitude of miscellaneous general purpose uses. When applied over tool handles, it creates a non-slip surface.



CAT NO	UPC	DIMENSIONS	STD	MSTR	WT/STD	UNIT
860	28130	3/4" x 60'	10	100	3.20#	Ea