



- UL Listed
- Allow Cables To Pull Easily, Prevent Hang-ups
- Snaps Securely Into Metal Studs
- 24 to 12 Gauge

Universal Plastic Stud Bushings are used to protect wires from abrasion in metal studs. Due to their molded high-strength, non-conductive polypropylene construction, the USB allows for the installation of multiple cables through a single opening while providing a smooth wire pulling surface. Dottie's USB's can be used with power cabling, low voltage datacom, video and voice cables. Fits all standard pre-punched and field punched holes.

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
USB	81031	3/8"	25	500	0.34#	C

Locknuts PC 5660



- Steel
- Zinc Plated

Locknuts are used to secure conduit by running or threading conduit into a box or panel and attaching the locknut and cinching up until tight.

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
LN38*	12300	3/8"	100	1000	3.02#	C
LN50	12301	1/2"	100	1000	1.34#	C
LN75	12302	3/4"	100	1000	2.05#	C
LN100	12303	1"	100	500	2.78#	C
LN125	12304	1-1/4"	50	250	2.08#	C
LN150	12305	1-1/2"	50	250	2.95#	C
LN200	12306	2"	50	100	3.22#	C
LN250	12307	2-1/2"	25	100	3.30#	C
LN300	12308	3"	25	100	3.94#	C
LN350	12309	3-1/2"	25	50	5.00#	C
LN400	12310	4"	25	50	6.06#	C
LN500	12311	5"	10	10	8.95#	C
LN600	12312	6"	10	10	9.90#	C

* LN38 Square Fixture Locknut

Sealing Locknuts PC 5665 Rated: NEMA FB1



- UL Listed
- Steel Locknut
- PVC Sealing Ring
- Zinc Plated

Used wherever a liquid tight application is needed when fastening threaded conduit to an unthreaded opening in a box or enclosure.

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
LNS50	12330	1/2"	100	1000	1.34#	C
LNS75	12331	3/4"	100	1000	2.05#	C
LNS100	12332	1"	100	500	2.78#	C
LNS125	12333	1-1/4"	50	250	2.08#	C
LNS150	12334	1-1/2"	50	250	2.95#	C
LNS200	12336	2"	50	100	3.22#	C
LNS250	12338	2-1/2"	25	100	3.30#	C
LNS300	12340	3"	25	100	3.94#	C
LNS350	12342	3-1/2"	25	50	5.00#	C
LNS400	12344	4"	25	50	6.06#	C

FITTINGS & STAMPINGS > UNIVERSAL PLASTIC STUD BUSHING > LOCKNUTS > SEALING LOCKNUTS