

## HAND TOOLS & STORAGE

**GUARANTEED TOUGH.**

### SCREWDRIVER & SCREWDRIVER SETS

#### SCREWDRIVER SETS

- Magnetic tip holds screw securely
- Color-coded handle for easy selection
- Bi-material quad-lobe handle for torque and comfort

CAT #	# OF PIECES IN SET	TIP STYLES	TIP SIZE	BAR LENGTH	BOLSTER	WEIGHT
DWHT62513L	10	Standard	1/8", 1/4", 1/4", 3/16"	3", 1-3/4", 4", 4"	No	1.63 lbs
		Cabinet	3/16"	6"	No	
		Phillips®	Opt, 2pt, 1pt, 2pt, 2pt	1/4", 1-3/4", 3", 4", 6"	No	
DWHT62512	4	Standard	1/4"	4"	No	0.88 lbs
		Cabinet	3/16"	4"	No	
		Phillips®	1pt, 2pt	3", 4"	No	



#### VINYL GRIP INSULATED SCREWDRIVERS

- 1,000V rated, 10,000V tested
- Space saving multi-blade design with quick-release mechanism for secure and easy blade change
- Pouch included for easy organization

CAT #	# OF PIECES IN SET	TIP STYLE	TIP SIZE	BOLSTER	WEIGHT
DWHT66417	8 Blades	Standard	1/8", 3/16", 1/4"	No	1.01 lbs
	1 Full Size Handle	Phillips®	Opt, 1pt, 2pt		
	1 Precision Handle	Square	1pt, 2pt		
	1 Tool Pouch				



### STAPLERS & STAPLES

#### HEAVY-DUTY STAPLE & BRAD TACKER

- Easy squeeze technology helps reduce actuation force
- Uses DeWALT heavy-duty staples series DWHTTA700 and 18 gauge headed brads in sizes 1/2", 5/8" & 9/16"

CAT #	HANDLE LENGTH	MAXIMUM STAPLE LENGTH	WEIGHT
DWHTTR350	4.25"	0.56"	2.00 lbs



#### HEAVY-DUTY HAMMER TACKER

- Lightweight die-cast aluminum housing design for durability
- Uses DeWALT heavy-duty staples series DWHTTA700 and 18 gauge headed brads in sizes 1/2", 5/8" & 9/16"

CAT #	HANDLE LENGTH	MAXIMUM STAPLE LENGTH	WEIGHT
DWHTHT450	10.50"	0.50"	2.50 lbs



#### HEAVY-DUTY CONTRACTOR PACK STAPLES

- Compatible with most heavy-duty tackers
- DeWALT heavy-duty staples 5,000 pieces per reusable plastic case
- Durable plastic storage box helps prevent rusting and stick breakage

CAT #	LENGTH	PACK SIZE
DWHTTA7055C	5/16" (8mm)	5,000 pcs
DWHTTA7065	3/8" (10mm)	5,000 pcs
DWHTTA7085C	1/2" (12mm)	5,000 pcs



1-800-4DEWALT

HAND TOOLS & STORAGE 93