



# Hex Head Cap Screws Grade 5 Zinc Plated - PC 4018

Grade 5 hex head cap screws are medium strength (120,000 PSI tensile) and are made from carbon steel. Length is determined from the base of the fastener head.

- Hex Head Cap Screws
- Grade 5
- Partial Thread
- Zinc Plated Steel

CAT NO	UPC	SIZE	HEX SIZE	STD	MSTR	WT/STD	UNIT
5MB1412	18000	1/4 x 1/2	7/16"	100	4000	1.18#	C
5MB1434	18001	1/4 x 3/4	7/16"	100	3000	1.44#	C
5MB141	18002	1/4 x 1	7/16"	100	3000	1.67#	C
5MB14114	18003	1/4 x 1-1/4	7/16"	100	1000	2.01#	C
5MB14112	18004	<b>1/4-20</b> 1/4 x 1-1/2	7/16"	100	1000	2.36#	C
5MB142	18005	1/4 x 2	7/16"	100	1000	3.07#	C
5MB14212	18006	1/4 x 2-1/2	7/16"	100	1000	3.75#	C
5MB143	18007	1/4 x 3	7/16"	100	1000	4.35#	C
5MB14312	18008	1/4 x 3-1/2	7/16"	100	1000	5.10#	C
5MB144	18009	1/4 x 4	7/16"	100	1000	5.75#	C
<hr/>							
5MB51612	18014	5/16 x 1/2	1/2"	100	1000	1.95#	C
5MB51634	18015	5/16 x 3/4	1/2"	100	1000	2.33#	C
5MB5161	18016	5/16 x 1	1/2"	100	1000	2.74#	C
5MB516114	18017	5/16 x 1-1/4	1/2"	100	1000	3.23#	C
5MB516112	18018	<b>5/16-18</b> 5/16 x 1-1/2	1/2"	100	1000	3.82#	C
5MB5162	18019	5/16 x 2	1/2"	100	1000	4.82#	C
5MB516212	18020	5/16 x 2-1/2	1/2"	100	1000	5.95#	C
5MB5163	18021	5/16 x 3	1/2"	100	1000	6.91#	C
5MB516312	18022	5/16 x 3-1/2	1/2"	50	500	3.62#	C
5MB5164	18023	5/16 x 4	1/2"	50	500	3.82#	C
<hr/>							
5MB3812	18028	3/8 x 1/2	9/16"	100	1000	2.93#	C
5MB3834	18029	3/8 x 3/4	9/16"	100	1000	3.55#	C
5MB381	18030	3/8 x 1	9/16"	100	1000	4.03#	C
5MB38114	18031	3/8 x 1-1/4	9/16"	100	1000	4.48#	C
5MB38112	18032	<b>3/8-16</b> 3/8 x 1-1/2	9/16"	100	1000	5.54#	C
5MB382	18033	3/8 x 2	9/16"	100	1000	6.94#	C
5MB38212	18034	3/8 x 2-1/2	9/16"	100	500	8.68#	C
5MB383	18035	3/8 x 3	9/16"	100	500	9.49#	C
5MB38312	18036	3/8 x 3-1/2	9/16"	50	500	5.65#	C
5MB384	18037	3/8 x 4	9/16"	50	500	6.94#	C
<hr/>							
5MB1234	18042	1/2 x 3/4	3/4"	50	500	4.05#	C
5MB121	18043	1/2 x 1	3/4"	50	500	4.15#	C
5MB12114	18044	1/2 x 1-1/4	3/4"	50	500	4.69#	C
5MB12112	18045	1/2 x 1-1/2	3/4"	50	500	5.21#	C
5MB122	18046	<b>1/2-13</b> 1/2 x 2	3/4"	50	500	6.73#	C
5MB12212	18047	1/2 x 2-1/2	3/4"	50	200	8.02#	C
5MB123	18048	1/2 x 3	3/4"	50	200	9.37#	C
5MB12312	18049	1/2 x 3-1/2	3/4"	50	200	10.75#	C
5MB124	18050	1/2 x 4	3/4"	25	100	6.02#	C



BUILDING A BETTER BRAND

