



ACCESSORIES

WOOD & METAL DRILLING

BLACK OXIDE



| CAT # | DIAMETER | DRILLING DEPTH | OVERALL LENGTH | QTY. |
|----------|----------|----------------|----------------|------|
| DW1104 | 1/16" | .88" | 1.88" | 2 |
| DW1105 | 5/64" | 1" | 2" | 2 |
| DW1106 | 3/32" | 1.25" | 2.25" | 2 |
| DW1107 | 7/64" | 1.5" | 2.62" | 2 |
| DW1108 | 1/8" | 1.62" | 2.75" | 2 |
| DW1109 | 9/64" | 1.75" | 2.88" | 1 |
| DW1110 | 5/32" | 2" | 3.12" | 1 |
| DW1111 | 11/64" | 2.12" | 3.25" | 1 |
| DW1112 | 3/16" | 2.31" | 3.5" | 1 |
| DW1113 | 13/64" | 2.44" | 3.62" | 1 |
| DW1114 | 7/32" | 2.5" | 3.75" | 1 |
| DW1115 | 15/64" | 2.62" | 3.88" | 1 |
| DW1116 | 1/4" | 2.75" | 4.00" | 1 |
| DW1117 | 17/64" | 2.88" | 4.12" | 1 |
| DW1118 | 9/32" | 2.94" | 4.25" | 1 |
| DW1119 | 19/64" | 3.06" | 4.38" | 1 |
| DW1120 | 5/16" | 3.19" | 4.5" | 1 |
| DW1121 | 21/64" | 3.31" | 4.62" | 1 |
| DW1122 | 11/32" | 3.44" | 4.75" | 1 |
| DW1123 | 23/64" | 3.5" | 4.88" | 1 |
| DW1124 | 3/8" | 3.62" | 5.00" | 1 |
| DW1125** | 25/64" | 3.75" | 5.12" | 1 |
| DW1126** | 13/32" | 3.88" | 5.25" | 1 |
| DW1127** | 27/64" | 3.94" | 5.38" | 1 |
| DW1128** | 7/16" | 4.06" | 5.50" | 1 |

| CAT # | DIAMETER | DRILLING DEPTH | OVERALL LENGTH | QTY. |
|--------------------------------|----------|----------------|----------------|------|
| DW1129** | 29/64" | 4.19" | 5.62" | 1 |
| DW1130** | 15/32" | 4.31" | 5.75" | 1 |
| DW1131** | 31/64" | 4.38" | 5.88" | 1 |
| DW1132** | 1/2" | 4.5" | 6.00" | 1 |
| Reduced Shank | | | | |
| DW1620** | 9/16" | 3" | 6" | 1 |
| DW1622** | 5/8" | 3" | 6" | 1 |
| DW1623** | 11/16" | 3" | 6" | 1 |
| DW1625** | 3/4" | 3" | 6" | 1 |
| DW1627** | 7/8" | 3" | 6" | 1 |
| DW1629** | 1" | 3" | 6" | 1 |
| 6" Extended Length Bit | | | | |
| DW1603 | 1/8" | 1.65" | 6" | 1 |
| DW1605 | 3/16" | 2.36" | 6" | 1 |
| DW1607 | 1/4" | 2.83" | 6" | 1 |
| DW1609 | 5/16" | 3.27" | 6" | 1 |
| DW1611 | 3/8" | 3.74" | 6" | 1 |
| DW1615 | 1/2" | 4.65" | 6" | 1 |
| 12" Extended Length Bit | | | | |
| DW1602 | 1/8" | 1.65" | 12" | 1 |
| DW1604 | 3/16" | 2.36" | 12" | 1 |
| DW1606 | 1/4" | 2.83" | 12" | 1 |
| DW1608 | 5/16" | 3.26" | 12" | 1 |
| DW1610 | 3/8" | 3.74" | 12" | 1 |
| DW1612** | 7/16" | 4.17" | 12" | 1 |
| DW1614** | 1/2" | 4.64" | 12" | 1 |



DW1116

**3/8" Reduced Shank
 ***1/2" Reduced Shank

BLACK OXIDE SETS

| CAT # | DESCRIPTION | INCLUDES |
|--------|----------------------------------|--|
| DW1163 | 13 Pc. Black Oxide Drill Bit Set | (2) 1/16", 5/64", (2) 3/32", 7/64", (2) 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", TOUGH CASE® Container |
| DW1167 | 17 Pc. Black Oxide Drill Bit Set | (2) 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 11/64", 3/16", 13/64", 7/32", 15/64", 1/4", 5/16", 3/8", 1/2", TOUGH CASE® Container |
| DW1176 | 16 Pc. Black Oxide Drill Bit Set | (2) 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", (2) 5/32", 11/64", (2) 3/16", 7/32", 1/4", 5/16", 3/8", TOUGH CASE® Container |
| DW1177 | 20 Pc. Black Oxide Drill Bit Set | (3) 1/16", 5/64", (2) 3/32", 7/64", (2) 1/8", 9/64", 5/32", 11/64", 3/16", 13/64", 7/32", 15/64", 1/4", 5/16", 3/8", 1/2", TOUGH CASE® Container |
| DW1162 | 14 Pc. Black Oxide Drill Bit Set | (2) 1/16", 5/64", 3/32", 7/64", (2) 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", 5/16", 3/8", TOUGH CASE® Container |



DW1177

IMPACT READY DRILLING



| CAT # | QTY./CARD | BULK | BULK QTY. | DIA. INCHES | DIA. DECIMAL | OVERALL LENGTH |
|--------|-----------|----------|-----------|-------------|--------------|----------------|
| DD5008 | 1 | DD5008B6 | 6 | 1/8" | .1250" | 2.625" |
| DD5009 | 1 | DD5009B6 | 6 | 9/64" | .1406" | 2.75" |
| DD5010 | 1 | DD5010B6 | 6 | 5/32" | .1562" | 2.8125" |
| DD5011 | 1 | DD5011B6 | 6 | 11/64" | .1719" | 2.9375" |
| DD5012 | 1 | DD5012B6 | 6 | 3/16" | .1875" | 3" |
| DD5013 | 1 | DD5013B6 | 6 | 13/64" | .2031" | 3.0625" |
| DD5014 | 1 | DD5014B6 | 6 | 7/32" | .2188" | 3.125" |

| CAT # | QTY./CARD | BULK | BULK QTY. | DIA. INCHES | DIA. DECIMAL | OVERALL LENGTH |
|--------|-----------|----------|-----------|-------------|--------------|----------------|
| DD5015 | 1 | DD5015B6 | 6 | 15/64" | .2344" | 3.15625" |
| DD5016 | 1 | DD5016B6 | 6 | 1/4" | .2500" | 3.1875" |
| DD5018 | 1 | DD5018B3 | 3 | 9/32" | .2812" | 3.5" |
| DD5020 | 1 | DD5020B3 | 3 | 5/16" | .3125" | 4" |
| DD5022 | 1 | DD5022B3 | 3 | 11/32" | .3437" | 4" |
| DD5024 | 1 | DD5024B3 | 3 | 3/8" | .3750" | 4" |
| DD5028 | 1 | DD5028B3 | 3 | 7/16" | .4375" | 4" |
| DD5032 | 1 | DD5032B3 | 3 | 1/2" | .5000" | 4" |

IMPACT READY SETS

| CAT # | DESCRIPTION | INCLUDES |
|--------|----------------------------|--|
| DD5055 | 5 Pc. Impact Drilling Set | (2) 1/8", 5/32", 3/16", 1/4" |
| DD5057 | 7 Pc. Impact Drilling Set | (2) 1/8", 5/32", 3/16", 7/32", 1/4", 5/16" |
| DD5060 | 10 Pc. Impact Drilling Set | (2) 1/8", 9/64", 5/32", 11/64", 3/16", 7/32", 1/4", 5/16", 3/8", TOUGH CASE® Container |



DD5057



DD5060