



Pan head combo (slotted/Phillips) sheet metal screws will tap their own mating threads when driven into preformed holes in metal. Length is determined from the base of the fastener head.

- Sheet Metal Screws
- Pan Head
- Slotted/Phillips
- Zinc Plated Steel

SHEET METAL SCREWS

CAT NO	UPC		SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
2WS612	58162	#6	6 x 1/2	100	500	5000	0.20#	C
2WS634	58164		6 x 3/4	100	500	5000	0.27#	C
2WS61	58166		6 x 1	100	500	5000	0.34#	C
2WS6114	58168		6 x 1-1/4	100	500	5000	0.42#	C
2WS6112	58170		6 x 1-1/2	100	500	5000	0.49#	C
2WS62	58172		6 x 2	100	500	5000	0.64#	C
2WS812	58150	#8	8 x 1/2	100	500	5000	0.31#	C
2WS834	58152		8 x 3/4	100	500	5000	0.41#	C
2WS81	58154		8 x 1	100	500	5000	0.51#	C
2WS8114	58156		8 x 1-1/4	100	500	5000	0.61#	C
2WS8112	58158		8 x 1-1/2	100	500	5000	0.69#	C
2WS82	58160		8 x 2	100	500	3000	0.89#	C
2WS1012	58200	#10	10 x 1/2	100	500	5000	0.43#	C
2WS1034	58202		10 x 3/4	100	500	5000	0.54#	C
2WS101	58204		10 x 1	100	500	5000	0.69#	C
2WS10114	58206		10 x 1-1/4	100	500	5000	0.80#	C
2WS10112	58208		10 x 1-1/2	100	500	3000	0.91#	C
2WS102	58210		10 x 2	100	500	3000	1.26#	C
2WS1212	58174	#12	12 x 1/2	100	500	5000	0.61#	C
2WS1234	58176		12 x 3/4	100	500	5000	0.81#	C
2WS121	58178		12 x 1	100	500	5000	0.96#	C
2WS12114	58180		12 x 1-1/4	100	500	3000	1.15#	C
2WS12112	58182		12 x 1-1/2	100	500	3000	1.30#	C
2WS122	58184		12 x 2	100	500	3000	1.61#	C
2WS1412	58186	#14	14 x 1/2	100	500	5000	0.86#	C
2WS1434	58188		14 x 3/4	100	500	5000	1.09#	C
2WS141	58190		14 x 1	100	500	3000	1.28#	C
2WS14114	58192		14 x 1-1/4	100	500	3000	1.57#	C
2WS14112	58194		14 x 1-1/2	100	500	3000	1.77#	C
2WS142	58196		14 x 2	100	500	3000	2.21#	C
2WST834	58161	#8	Tuff Pack 8 x 3/4	500		3000	2.24#	C
2WST81	58163		Tuff Pack 8 x 1	500		3000	3.29#	C
2WST1034	58165	#10	10 x 3/4	500		3000	3.70#	C
2WST101	58167		10 x 1	500		3000	3.60#	C

Phillips Pan Head Sheet Metal Screws • Stainless Steel | PC 4010



Stainless steel pan head Phillips sheet metal screws will tap their own mating threads when driven into preformed holes in metal. Length is determined from the base of the fastener. Stainless steel resists corrosion and is ideal for applications where chemical resistance is required.

- Sheet Metal Screws
- Pan Head
- Phillips
- Stainless Steel

CAT NO	UPC		SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
PHSMSS612	70204	#6	6 x 1/2	100	500	5000	0.20#	C
PHSMSS634	70206		6 x 3/4	100	500	5000	0.27#	C
PHSMSS61	70208		6 x 1	100	500	5000	0.34#	C
PHSMSS6114	70210		6 x 1-1/4	100	500	5000	0.42#	C
PHSMSS6112	70212		6 x 1-1/2	100	500	5000	0.49#	C
PHSMSS62	70214		6 x 2	100	500	5000	0.64#	C
PHSMSS812	70220	#8	8 x 1/2	100	500	5000	0.31#	C
PHSMSS834	70222		8 x 3/4	100	500	5000	0.41#	C
PHSMSS81	70224		8 x 1	100	500	5000	0.51#	C

To Order: Phone (323) 725-1000 / Fax (323) 721-0000

