

Tapered with Wings PC 4370



- Tapered with Wings
- Plastic
- Packed in Invincibox™
- Wings Secure Anchor From Spinning

Plastic anchors: Tapered with Wings. Drill a hole into drywall, concrete, brick or block and insert anchor. The screw is then installed through the fixture into the anchor. Used for light duty work.

CAT NO	UPC	SCREW SIZE	DRILL SIZE	LENGTH	COLOR	STD	SLEEVE	MSTR	WT/STD	UNIT
121	31430	4-6-8	3/16"	1"	White	100	500	4000	0.11#	C
122	31432	8-10-12	1/4"	1-1/4"	Yellow	100	500	3000	0.20#	C
123	31434	12-14-16	5/16"	1-1/2"	Green	50	250	1500	0.15#	C

Tapered with Collar PC 4370



- Tapered with Collar
- Plastic
- Packed in Invincibox™

Plastic anchors: Tapered w/Collar. Drill a hole into drywall, concrete, brick or block and insert anchor. The screw is then installed through the fixture into the anchor. Used for light duty work.

CAT NO	UPC	SCREW SIZE	DRILL SIZE	LENGTH	COLOR	STD	SLEEVE	MSTR	WT/STD	UNIT
20	15080	4-6-8	3/16"	3/4"	Red	100	500	4000	0.08#	C
21	15085	6-8-10	3/16"	7/8"	Red	100	500	4000	0.08#	C
22	15090	8-10-12	1/4"	1"	Red	100	500	3000	0.15#	C
23	15095	12-14-16	5/16"	1-1/2"	Red	50	250	1500	0.14#	C

Straight PC 4370



- Straight
- Ribbed Body
- Plastic
- Packed in Invincibox™

Plastic anchors: Straight. Drill a hole into drywall, concrete, brick or block and insert anchor. The screw is then installed through the fixture into the anchor. Used for light duty work.

CAT NO	UPC	SCREW SIZE	DRILL SIZE	LENGTH	COLOR	STD	SLEEVE	MSTR	WT/STD	UNIT
221	16085	6-8	3/16"	1"	White	100	500	4000	0.15#	C
222	16090	10-12	1/4"	1"	Green	100	500	3000	0.22#	C
223	16095	12-14	5/16"	1-1/2"	Blue	50	250	1500	0.23#	C

Nylon Button Head with Pins PC 4370



- Straight
- Ribbed Body
- Nylon
- Steel Pin

Nylon button head anchors with pins. Fast and easy to install. Position the fixture, drill a hole into concrete, brick or block and insert anchor through the fixture into the hole. Hammer the nail to spread and secure anchor. Used for light duty work.

CAT NO	UPC	SIZE	LENGTH	COLOR	STD	SLEEVE	MSTR	WT/STD	UNIT
1711	10070	3/16"	1"	White	100	500	3000	0.55#	C
1714	10075	1/4"	1"	White	100	500	3000	0.57#	C

Triple Grip PC 4370



- Claws Grip For Strength
- Wings For Strength and Vibration Resistance
- Core Expands For additional Holding Power



CAT NO	UPC	SCREW SIZE	DRILL SIZE	LENGTH	COLOR	STD	SLEEVE	MSTR	WT/STD	UNIT
6	81643	#6	1/4"	1-1/4"	Beige	100	500	4000	0.91#	C
8	81644	#8	1/4"	1-1/4"	Gray	100	500	4000	0.97#	C
10	81645	#10	5/16"	1-1/2"	Blue	50	250	1500	0.60#	C
12	81646	#12	3/8"	1-1/2"	Green	50	250	1500	1.23#	C