



## Pull Rope PC 6000

Polypropylene Pull Rope is a lightweight, strong rope that is rot proof and unaffected by water, oil, gasoline and most chemicals.

- Polypropylene
- Safety Yellow

CAT NO	UPC	SIZE	WORK LOAD	TENSILE	STD	MSTR	WT/STD	UNIT
18100	61300	1/8" x 1000'	48#	480#	1	1	4.05#	Ea
18250	61305	1/8" x 2500'	48#	480#	1	1	10.58#	Ea
3625	61302	3/16" x 250'	72#	720#	1	1	2.69#	Ea
3660	61304	3/16" x 600'	72#	720#	1	1	6.52#	Ea
36100	61306	3/16" x 1000'	72#	720#	1	1	9.39#	Ea
36120	61308	3/16" x 1200'	72#	720#	1	1	10.62#	Ea
36300	60314	3/16" x 3000'	72#	720#	1	1	23.47#	Ea
36360	60316	3/16" x 3600'	72#	720#	1	1	30.78#	Ea
1425	61310	1/4" x 250'	113#	1130#	1	1	4.99#	Ea
1460	61312	1/4" x 600'	113#	1130#	1	1	8.96#	Ea
14100	61314	1/4" x 1000'	113#	1130#	1	1	15.72#	Ea
14120	61316	1/4" x 1200'	113#	1130#	1	1	17.84#	Ea
14240	61313	1/4" x 2400'	113#	1130#	1	1	34.02#	Ea
14400	61315	1/4" x 4000'	113#	1130#	1	1	51.54#	Ea
3830	61318	3/8" x 300'	243#	2430#	1	1	8.93#	Ea
3860	61320	3/8" x 600'	243#	2430#	1	1	18.55#	Ea
38120	61322	3/8" x 1200'	243#	2430#	1	1	36.92#	Ea
38250	60312	3/8" x 2500'	243#	2430#	1	1	70.00#	Ea
38360	60318	3/8" x 3600'	243#	2430#	1	1	111.00#	Ea
1230	61324	1/2" x 300'	378#	3780#	1	1	16.98#	Ea
1260	61326	1/2" x 600'	378#	3780#	1	1	33.10#	Ea
12120	61328	1/2" x 1200'	378#	3780#	1	1	62.22#	Ea



## Pull Line PC 6000

Pull Line is used to pull rope through conduit and can be used with power fishing systems.

- Two Ply Pull Line
- Dispensing Pail
- Dispensing Box
- Rot & Mildew Resistant

CAT NO	UPC	COLOR	LENGTH	WORK LOAD	TENSILE	STD	MSTR	WT/STD	UNIT
6502	15745	Blue / White	6500'	20#	200#	1	1	10.00#	Ea
6502P	15747	Blue / White	6500' Pail	20#	200#	1	1	11.65#	Ea
<b>Heavy Duty</b>									
2203P	27506	Red / White	2200' Pail	50#	500#	1	1	12.66#	Ea

## TECH TALK

**Polypropylene Pull Rope** is lightweight and strong. For most requirements, polypropylene is the most economical rope to use.

**Polyester Pull Line/Measuring Tape** provides a lower coefficient of friction than other competitive tapes due to special prelubrication and high abrasion yarns. It is provided with accurate sequential footage markings. It is soft to the touch and comfortable to handle.

**Nylon Line** resists rot and mildew.



Dottie

To Order: Phone (323)725-1000 / Fax (323)721-0000