

# Wire Hangers PC 5100

- 10 Gauge Steel
- Plain (Uncoated)
- Plastic Coated
- Caution! Always Wear Eye Protection

Wire Hangers are used to secure pipe or tubing transversing wood beams.



| CAT NO                | UPC   | SIZE     | STD | MSTR | WT/STD | UNIT |
|-----------------------|-------|----------|-----|------|--------|------|
| <b>Plain</b>          |       |          |     |      |        |      |
| WH124                 | 27200 | 1/2 x 4" | 100 | 500  | 4.38#  | M    |
| WH126                 | 27202 | 1/2 x 6" | 100 | 500  | 6.22#  | M    |
| WH344                 | 27204 | 3/4 x 4" | 100 | 500  | 4.36#  | M    |
| WH346                 | 27206 | 3/4 x 6" | 100 | 500  | 7.40#  | M    |
| <b>Plastic Coated</b> |       |          |     |      |        |      |
| PC124                 | 27208 | 1/2 x 4" | 100 | 500  | 4.52#  | M    |
| PC126                 | 27210 | 1/2 x 6" | 100 | 500  | 6.20#  | M    |
| PC344                 | 27212 | 3/4 x 4" | 100 | 500  | 4.60#  | M    |
| PC346                 | 27214 | 3/4 x 6" | 100 | 500  | 6.30#  | M    |

## Hook on Clips · Hook on Straps PC 5110, 5120

- Hook on Clips & Straps
- Formed Wire
- Supplied With Insulator
- Caution! Always Wear Eye Protection

Hook on Straps & Clips are used to secure pipe or tubing running parallel with studs. The hook on straps are nailed across two studs. The hook on clips with insulator snap into holes in the strap and tubing or pipe is then secured perpendicular to the strap.



| CAT NO                    | UPC   | SIZE       | STD | MSTR | WT/STD | UNIT |
|---------------------------|-------|------------|-----|------|--------|------|
| <b>14 Gauge - PC 5110</b> |       |            |     |      |        |      |
| HC50                      | 27220 | 1/2" Pipe  | 100 | 1000 | 1.66#  | M    |
| HC75                      | 27225 | 3/4" Pipe  | 100 | 1000 | 1.75#  | M    |
| <b>12 Gauge - PC 5120</b> |       |            |     |      |        |      |
| 5818                      | 27230 | 18" Length | 100 | 100  | 21.08# | C    |
| 5826                      | 27235 | 26" Length | 100 | 100  | 30.58# | C    |

## Plumber's Tape PC 5130, 5140

- Galvanized Steel
- Solid Copper

Plumber's Tape is 3/4" wide and is perforated with alternating size holes to accommodate nails or bolts. It is used to strap or support pipe, ducts & other fastening applications. Copper strap also used for grounding.



| CAT NO                            | UPC   | LENGTH    | GAUGE | STD | MSTR | WT/STD | UNIT |
|-----------------------------------|-------|-----------|-------|-----|------|--------|------|
| <b>Galvanized Steel - PC 5130</b> |       |           |       |     |      |        |      |
| PT28                              | 30945 | 3/4 x 10' | 28    | 100 | 100  | 35.16# | Ea   |
| PT26                              | 30940 | 3/4 x 10' | 26    | 100 | 100  | 46.24# | Ea   |
| PT22                              | 30935 | 3/4 x 10' | 22    | 50  | 50   | 37.64# | Ea   |
| <b>Solid Copper - PC 5140</b>     |       |           |       |     |      |        |      |
| CU10                              | 27550 | 3/4 x 10' | 23    | 1   | 10   | 0.58#  | Ea   |
| CU25                              | 27555 | 3/4 x 25' | 23    | 1   | 6    | 1.48#  | Ea   |
| CU50                              | 27560 | 3/4 x 50' | 23    | 1   | 6    | 2.97#  | Ea   |