



Pan Head Phillips Self Drilling Screws Zinc Plated - PC 4220

Self drilling phillips pan head screws drill a hole and tap threads in one operation. The drilling operation removes metal and can be used with heavier gauge metals. Length is determined from the base of the fastener head.

- Self Drilling
- Pan Head
- Phillips
- Zinc Plated Steel
- Invincibox™ Up To 2"

CAT NO	UPC	SIZE	BIT SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
TEKPH612	17370	6 x 1/2	#1	100	500	4000	0.26#	C
TEKPH634	17375	#6	6 x 3/4	#1	100	500	4000	0.30#
TEKPH61	17380	6 x 1	#1	100	500	4000	0.34#	C
TEKPH812	17410	8 x 1/2	#2	100	500	4000	0.36#	C
TEKPH834	17415	8 x 3/4	#2	100	500	4000	0.43#	C
TEKPH81	17420	8 x 1	#2	100	500	4000	0.58#	C
TEKPH8114	17385	#8	8 x 1-1/4	#2	100	500	4000	0.61#
TEKPH8112	17390	8 x 1-1/2	#2	100	500	3000	0.72#	C
TEKPH82	17395	8 x 2	#2	100	500	4000	0.92#	C
TEKPH1012	17425	10 x 1/2	#2	100	500	4000	0.47#	C
TEKPH1034	17430	10 x 3/4	#2	100	500	4000	0.59#	C
TEKPH101	17435	#10	10 x 1	#2	100	500	4000	0.76#
TEKPH10114	17440	10 x 1-1/4	#2	100	500	3000	0.82#	C
TEKPH10112	17445	10 x 1-1/2	#2	100	500	3000	0.93#	C
TEKPH102	17450	10 x 2	#2	50	250	1500	0.61#	C




Pan Head Square Drive Self Drilling Screws Zinc Plated - PC 4220

Self drilling square drive pan head screws drill a hole and tap threads in one operation. The drilling operation removes metal and can be used with heavier gauge metals. Length is determined from the base of the fastener head.

- Self Drilling
- Pan Head
- Square Drive
- Zinc Plated Steel
- Invincibox™ Up To 2"

CAT NO	UPC	SIZE	BIT SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
TEKDD812	59500	8 x 1/2	#2	100	500	4000	0.36#	C
TEKDD834	59502	8 x 3/4	#2	100	500	4000	0.43#	C
TEKDD81	59504	#8	8 x 1	#2	100	500	4000	0.58#
TEKDD8114	59517	8 x 1-1/4	#2	100	500	4000	0.82#	C
TEKDD8112	59518	8 x 1-1/2	#2	100	500	3000	0.93#	C
TEKDD82	59519	8 x 2	#2	100	500	3000	1.22#	C
TEKDD1012	59506	10 x 1/2	#2	100	500	4000	0.47#	C
TEKDD1034	59508	10 x 3/4	#2	100	500	4000	0.59#	C
TEKDD101	59510	#10	10 x 1	#2	100	500	4000	0.76#
TEKDD10114	59520	10 x 1-1/4	#2	100	500	3000	0.82#	C
TEKDD10112	59521	10 x 1-1/2	#2	100	500	3000	0.93#	C
TEKDD102	59522	10 x 2	#2	50	250	1500	0.61#	C
TEKDDT812	59511	#8 Tuff Pack	8 x 1/2	#2	500	3000	1.76#	C
TEKDDT834	59512	8 x 3/4	#2	500	3000	2.28#	C	
TEKDDT81	59513	8 x 1	#2	500	3000	2.76#	C	
TEKDDT1012	59514	10 x 1/2	#2	500	3000	2.48#	C	
TEKDDT1034	59515	#10 Tuff Pack	10 x 3/4	#2	500	3000	3.10#	C
TEKDDT101	59516	10 x 1	#2	500	3000	3.60#	C	

TECH TALK



Self Drilling Screws

- Manufactured from high quality cold headed material and heat treated under controlled conditions yielding optimum drill performance.
- Better thread engagement and optimum holding powers are achieved by using a product which self-drills its own hole size.
- Available in a variety of head styles and drive systems to meet special application and installation demands.