






EYDM 25% * Fill Vertical Conduit Drain Sealing Fittings for Close Turning Radius

Explosionproof, Dust-Ignitionproof, Raintight

UNILETS® for Use with Threaded Rigid Metal Conduit and IMC.

Class I, Division 1 and 2 Groups B♦, C, D
Class II, Division 1 and 2 Groups E, F, G
Class III

| | Trade Size (Inches) | Inches/Centimeters | | | Kwiko® A Cement Required Ounces/Grams | Catalog Number ‡ | |
|--|---------------------|--------------------|-----------|------------------|---------------------------------------|-------------------|-------------------|
| | | A (Length) | B (Width) | Turning Radius † | | Malleable Iron | Almag 35 Aluminum |
| EYDM Vertical Conduit Drain Seals for Close Turning Radius (25% fill) ‡ | | | | | | | |
| Male/Female (Removable Male Nipple) | | | | | | | |
|  | 1/2 | 3.63/9.2 | 1.38/3.5 | 1.94/4.9 | 2.00/56.7 | EYDM-50 ♦ | EYDM-50AL |
| | 3/4 | 3.63/9.2 | 1.38/3.5 | 1.94/4.9 | 2.00/56.7 | EYDM-75 ♦ | EYDM-75AL |
|  | 1 | 4.06/10.3 | 1.56/4.0 | 2.06/5.2 | 3.00/85.1 | EYDM-100 ♦ | EYDM-100AL |
| | 1-1/4 | 4.94/12.5 | 2.00/5.1 | 1.75/4.5 | 7.00/198.4 | EYDM-125 ♦ | EYDM-125AL |
|  | 1-1/2 | 5.50/14.0 | 2.38/6.0 | 2.06/5.2 | 13.00/368.5 | EYDM-150 ♦ | EYDM-150AL |
| | 2 | 6.13/15.6 | 2.88/7.3 | 2.31/5.9 | 22.00/623.7 | EYDM-200 ♦ | EYDM-200AL |
| | 2-1/2 | 7.50/19.1 | 3.38/8.6 | 2.69/6.8 | 36.00/1020.6 | EYDM-250 ♦ | EYDM-250AL |
| | 3 | 8.13/20.6 | 4.13/10.5 | 3.13/7.9 | 61.00/1729.3 | EYDM-300 ♦ | EYDM-300AL |
|  | 3-1/2 | 8.94/22.7 | 4.75/12.1 | 3.44/8.7 | 89.00/2523.1 | EYDM-350 ♦ | EYDM-350AL |
| | 4 | 9.38/23.8 | 5.13/13.0 | 3.69/9.4 | 114.00/3231.8 | EYDM-400 ♦ | EYDM-400AL |



* Per NEC 501.15(C)(6), seals in Class I, Division 1 and 2 must be limited to conductor fill of 25% of cross sectional area of a rigid metal conduit of the same trade size unless approved for higher percentage fill. See 40% fill sealing fittings.

† Turning radius with cover or plug removed.

‡ PVC coating available on select sealing fittings. Add suffix **-PVC** to catalog number.

♦ Indicated items in the shaded area which are UL Listed for Class I, Groups B, C, D; Class II, Groups E, F, G; and Class III.