



**Fastener Kits  
PC 4760**

Dottie introduced assorted screw kits over 40 years ago and has a comprehensive variety for almost any imaginable need.

- Reusable Six Compartment Box
- Handy Assortment

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
632	18140	370 Assorted 6-32 Slotted Flat Head Machine Screws; 3/4" Thru 3" 100 - 1/2", 75 - 3/4", 75 - 1", 50 - 1-1/4", 40 - 1-1/2", 30 - 2"	1	6	1.85#	Ea
632DD	29655	370 Assorted 6-32 Square/Phillips Flat Head Machine Screws; 1/2" Thru 2" 100 - 1/2", 75 - 3/4", 75 - 1", 50 - 1-1/4", 40 - 1-1/2", 30 - 2"	1	6	1.88#	Ea
632PS	29657	370 Assorted 6-32 Phillips/Slotted Round Head Machine Screws; 1/2" Thru 2", 100 - 1/2", 75 - 3/4", 75 - 1", 50 - 1-1/4", 40 - 1-1/2", 30 - 2"	1	6	1.59#	Ea
832DS	29665	310 Assorted 8-32 Square/Slotted Round Head Machine Screws; 1/2" Thru 2" 100 - 1/2", 60 - 3/4", 50 - 1", 40 - 1-1/4", 35 - 1-1/2", 25 - 2"	1	6	2.31#	Ea
832PS	29660	370 Assorted 8-32 Phillips/Slotted Round Head Machine Screws; 1/2" Thru 2" 100 - 1/2", 75 - 3/4", 75 - 1", 50 - 1-1/4", 40 - 1-1/2", 30 - 2"	1	6	2.30#	Ea
1032PS	10323	245 Assorted 10-32 Phillips/Slotted Round Head Machine Screws; 1/2" Thru 2" 75 - 1/2", 50 - 3/4", 40 - 1", 30 - 1-1/4", 25 - 1-1/2", 25 - 2"	1	6	3.13#	Ea
1420PS	14205	110 Assorted 1/4-20 Phillips/Slotted Round Head Machine Screws; 1/2" Thru 2" 30 - 1/2", 25 - 3/4", 20 - 1", 15 - 1-1/4", 10 - 1-1/2", 10 - 2"	1	6	1.87#	Ea
<b>Stove Bolt Kits with Nuts</b>						
316	16560	220 Assorted 3/16 (10-24) Slotted Truss Head Stove Bolts with Hex Nuts; 1/2" Thru 2" 50 - 1/2", 50 - 3/4", 40 - 1", 30 - 1-1/4", 30 - 1 1/2", 20 - 2"	1	6	2.82#	Ea
1420	14200	110 Assorted 1/4-20 Slotted Truss Head Stove Bolts with Hex Nuts; 1/2" Thru 2" 30 - 1/2", 25 - 3/4", 20 - 1", 15 - 1-1/4", 10 - 1-1/2"	1	6	2.77#	Ea
<b>Hex Nut Kit</b>						
339	17000	339 Assorted Zinc Plated Hex Nuts 10 sizes: 6-32" Thru 5/8": 50 - 6-32", 50 - 8-32", 50 - 10-24", 25 - 10-32", 25 - 12-24", 75 - 1/4", 25 - 5/16", 30 - 3/8", 6 - 1/2", 3 - 5/8"	1	6	2.60#	Ea



**Machine Screw Kit • Truss Head  
PC 4760**

Dottie introduces the Truss Head Combo Assorted Machine Screw Kit. Contractors speak and Dottie listens. These Truss Head Machine Screws are needed when installing wiring devices behind wall plates. Great when a low profile fastener is needed.

- Truss Head
- Low Profile
- Phillips / Slotted
- Zinc Plated

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
632TCS	29658	370 Assorted 6-32 Slotted / Phillips Truss Head Machine Screws; 1/2" thru 2" 100 - 1/2", 75 - 3/4", 75 - 1", 50 - 1-1/4", 40 - 1-1/2", 30 - 2"	1	6	1.59#	Ea

