

## Wiha Insulated SlimLine Screwdrivers

### Insulation Test Standards:

Insulation according to EN/IEC 60900, ASTM F-1505-01, VDE 0682/part 201, DIN 7437, NFPA70E & CSA specification

**Wiha SlimTECHNOLOGY**  
Achieves blade diameters up to 33% narrower utilizing integrated insulation



Ideal for jobs where access is limited

Integrated Slim Insulation molded directly onto blade

**1000Volt Rated**  
10,000Volt Tested



**WH320 Insulated Slotted SlimLine Screwdrivers**  
Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  $\Delta$  up to 1000 Volt. Individually Tested to 10,000Volts.

High quality CV steel, through hardened. SlimLine blades have up to 33% narrower insulation diameter than standard insulated tools. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	⊖	⊖	⊖	Slim	⊖	⊖	⊖	⊖
	mm	Inch	Inch	Dia.	mm	mm	lbs.	Pkg.
WH32046	3.5	.139	9/64	3.5	100	204	.07	1
WH32049	4.0	.157	5/32	4.0	100	211	.12	1
WH32052	4.5	.177	3/16	4.5	125	211	.14	1
WH32055	5.5	.216	7/32	5.5	125	243	.21	1
WH32058	6.5	.255	1/4	6.5	150	268	.25	1



**WH307 Insulated Xeno SlimLine Screwdrivers For Terminal Screws**  
Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  $\Delta$  up to 1000 Volt. Individually Tested to 10,000Volts.

High quality CV steel, through hardened. SlimLine blades have up to 33% narrower insulation diameter than standard insulated tools. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	⊕	Slim	⊖	⊖	⊖	⊖
	Size	Dia.	mm	mm	lbs.	Pkg.
WH30746	1	4.5	80	191	.12	1
WH30747	2	6.0	100	218	.21	1



**WH321 Insulated Phillips SlimLine Screwdrivers**  
Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  $\Delta$  up to 1000 Volt. Individually Tested to 10,000Volts.

High quality CV steel, through hardened. SlimLine blades have up to 33% narrower insulation diameter than standard insulated tools. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	⊕	Slim	⊖	⊖	⊖	⊖
	Size	Dia.	mm	mm	lbs.	Pkg.
WH32145	1	4.5	80	204	.12	1
WH32146	2	6.0	100	211	.21	1



**WH358 Insulated Square SlimLine Screwdrivers**  
Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E & CSA,  $\Delta$  up to 1000 Volt. Individually Tested to 10,000Volts.

High quality CV steel, through hardened. SlimLine blades have up to 33% narrower insulation diameter than standard insulated tools. Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.	⊖	Slim	⊖	⊖	⊖	⊖
	Size	Dia.	mm	mm	lbs.	Pkg.
WH35844	1	4.0	100	218	.12	1
WH35845	2	4.5	125	243	.19	1