

Data Tables

TABLE 4-11. METER PACKS — ALUMINUM BUS

Socket Ampere Rating	Number of Meter Sockets	Bus Ampacity	Main Tenant Breaker Type	Catalog Number	UPC Code	Semi-flush Flange Kit Catalog Number	UPC Code
Ring Style Meter Socket Covers ①							
125 ②	2 ④	200	Plug-on Type	1MP2122R ⑤⑥	786849052379	1MPSFK1	786849054069
	3	400	BR_	1MP3124R	786849052386	1MPSFK2	786849054076
	4	400	BRH_	1MP4124R	786849052393	1MPSFK2	786849054076
	5 ④	600	BRHH_	1MP5126R	786849052409	1MPSFK3	786849054083
	6 ④	600	—	1MP6126R	786849052416	1MPSFK3	786849054083
200 ③	2	400	Bolt-on Type	1MP2204R	786849052423	1MPSFK4	786849054090
	3	600	CC2_X	1MP3206R	786849052430	1MPSFK5	786849054106
	4	600	CHH2_H2X	1MP4206R	786849052447	1MPSFK5	786849054106
	5	600	CHH2_H4X	1MP5206R	786849052454	1MPSFK6	786849054113
	6	600	CHH_X	1MP6206R	786849052461	1MPSFK6	786849054113
Ringless Style Meter Socket Covers ⑦							
125	2	200	Plug-on Type	1MP2122RRL ⑤⑥	786849052478	1MPSFK1	786849054069
	3	400	BR_	1MP3124RRL	786849052485	1MPSFK2	786849054076
	4	400	BRH_	1MP4124RRL	786849052492	1MPSFK2	786849054076
	5	600	BRHH_	1MP5126RRL	786849052508	1MPSFK3	786849054083
	6	600	—	1MP6126RRL	786849052515	1MPSFK3	786849054083
200	2	400	Bolt-on Type	1MP2204RRL	786849052522	1MPSFK4	786849054090
	3	600	CC2_X	1MP3206RRL	786849052539	1MPSFK5	786849054106
	4	600	CHH2_H2X	1MP4206RRL	786849052546	1MPSFK5	786849054106
	5	600	CHH2_H4X	1MP5206RRL	786849052553	1MPSFK6	786849054113
	6	600	CHH_X	1MP6206RRL	786849052560	1MPSFK6	786849054113
Ringless Style Covers with Horn Bypass ⑦							
125	2	200	Plug-on Type	1MP2122RRLB ⑤⑥	786849052577	1MPSFK1	786849054069
	3	400	BR_	1MP3124RRLB	786849052584	1MPSFK2	786849054076
	4	400	BRH_	1MP4124RRLB	786849052591	1MPSFK2	786849054076
	5	600	BRHH_	1MP5126RRLB	786849052607	1MPSFK3	786849054083
	6	600	—	1MP6126RRLB	786849052720	1MPSFK3	786849054083
200	2	400	Bolt-on Type	1MP2204RRLB	786849052737	1MPSFK4	786849054090
	3	600	CC2_X	1MP3206RRLB	786849052744	1MPSFK5	786849054106
	4	600	CHH2_H2X	1MP4206RRLB	786849052751	1MPSFK5	786849054106
	5	600	CHH2_H4X	1MP5206RRLB	786849052768	1MPSFK6	786849054113
	6	600	CHH_X	1MP6206RRLB	786849052775	1MPSFK6	786849054113

① Ring Style Meter Packs do not come with fifth jaw. Order **1MM5KJ** if needed.

② To change in field from ring to ringless — order **1MMRC125**.

③ To change in field from ring to ringless — order **1MMRC200**.

④ To change from ring to ringless covers, the top socket only in 2, 5 and 6 socket designs — order **1MMRC125T**. Top socket only — other sockets see ⑥.

⑤ Main lugs included. #6 – 300 kcmil. (Optional lugs are not available.)

⑥ Bottom feed only.

⑦ Fifth jaw factory installed at 9 o'clock position.