

McGILL® 5000 Series Industrial Extension Lights

Thermoplastic Handle With or Without Receptacle

	Catalog Numbers			
	with out Cord	with 1' / 0.3m 16/3-SJTW Cord	with 25' / 7.6m 16/3-SJTW Cord	with 50' / 15.2m 16/3-SJTW Cord
Closed-End Extension Lights				
Handle and cage	5000-G	—	5025-G	5050-G
Handle and cage	C5000-G ¹	—	C5025-G ¹	C5050-G ¹
Handle and cage with reflector	5000-RG	—	5025-RG	5050-RG
Handle and cage with reflector	C5000-RG ¹	—	C5025-RG ¹	C5050-RG ¹
Handle and cage with switch	5000-SG	—	5025-SG	5050-SG
Handle and cage with switch	C5000-SG ¹	—	C5025-SG ¹	C5050-SG ¹
Handle and cage with switch and reflector	5000-SRG	5012-SRG ¹	5025-SRG	5050-SRG
Handle and cage with switch and reflector	C5000-SRG ¹	5012-SRG ¹	C5025-SRG ¹	C5050-SRG ¹
Handle and cage with switch and reflector and GFCI	—	—	5025-SRG-GFCI	—
Handle and cage, no receptacle	5000-GN	—	5025-GN	5050-GN
Handle and cage, no receptacle	C5000-GN ¹	—	C5025-GN ¹	C5050-GN ¹
Handle and cage with reflector, no receptacle	5000-RGN	—	5025-RGN	5050-RGN
Handle and cage with reflector, no receptacle	C5000-RGN ¹	—	C5025-RGN ¹	C5050-RGN ¹
Handle and cage with switch, no receptacle	5000-SGN	—	5025-SGN	5050-SGN
Handle and cage with switch, no receptacle	C5000-SGN ¹	—	C5025-SGN ¹	C5050-SGN ¹
Handle and cage with switch and reflector, no receptacle	5000-SRGN	—	5025-SRGN	5050-SRGN
Handle and cage with switch and reflector, no receptacle	C5000-SRGN ¹	—	C5025-SRGN ¹	C5050-SRGN ¹
Handle and non-metallic cage	—	—	5999-GH	—
Handle and non-metallic cage	—	—	C5999-GH ¹	—
Handle and non-metallic cage with reflector	—	—	5999-RGH	—
Handle and non-metallic cage with reflector	—	—	C5999-RGH ¹	—
Handle and non-metallic cage with switch	—	—	5999-SGH	—
Handle and non-metallic cage with switch	—	—	C5999-SGH ¹	—
Handle and non-metallic cage with switch and reflector	—	—	5999-SRGH	—
Handle and non-metallic cage with switch and reflector	—	—	C5999-SRGH ¹	—
Replacement Cord Sets				
Cord set with molded plugs			6229-1	6229-2
			Catalog Number	
			With Out Reflector	With Reflector
Cages				
Wire cage			8171	8170
Vinyl insulated metal cage (100 Watt A-21)			08171	08170
Non-metallic cage (100 Watt A-19)			—	8224
			Catalog Number	
			With Out Switch	With Switch
Handles and Sockets				
Handle and socket for 5000			0877	0865
Handle and socket for 5000-N			0877-N	0865-N
Socket for 5000 and 5000-N			00868	868

¹ 100 Watt Maximum for UL Listing and CSA Certification.
¹ CSA Certification only.