

EFD/EFDB Series Factory Sealed Combination Push Button and Pilot Light Stations

Explosionproof, Dust-Ignitionproof

10 Amp, 600 Vac Max. for Heavy Duty Use. Momentary Contact. Furnished with Internal Ground Screw.

Class I, Division 1, Groups B*, C, D
 Class I, Division 2, Groups B, C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 3, 7CD, 9EFG

Controls

CONTROLS: HAZARDOUS LOCATION CONTROL STATIONS AND SWITCHES

		Hub Size (Inches)	Description	Nameplate Marking	Catalog Number Dead-End	Feed-Thru			
1-Gang *†									
 1 Circuit, 1 Pilot Light	 2 Circuit, 1 Pilot Light	1/2	1 Circuit		Start/Stop	EFDB150-J1U1	EFDCB150-J1U1		
		3/4	Universal and 1 Pilot Light			EFDB175-J1U1	EFDCB175-J1U1		
		1				EFDB110-J1U1	EFDCB110-J1U1		
			1/2	2 Circuit		Start/Stop	EFDB150-J1U2	EFDCB150-J1U2	
			3/4	Universal and 1 Pilot Light			EFDB175-J1U2	EFDCB175-J1U2	
			1				EFDB110-J1U2	EFDCB110-J1U2	
2-Gang									
 2 Circuit, 1 Pilot Light	 2 Circuit, 2 Pilot Light	1/2	2 Circuit		Start/Stop	efd250-J1U2	efdc250-J1U2		
				3/4		Universal and 1 Pilot Light		efd275-J1U2	efdc275-J1U2
				1				efd210-J1U2	efdc210-J1U2
			1/2	2 Circuit		Start/Stop	efd250-J2U2	efdc250-J2U2	
			3/4	Universal and 2 Pilot Lights			efd275-J2U2	efdc275-J2U2	
			1				efd210-J2U2	efdc210-J2U2	
3-Device †									
 2 Circuit, 1 Pilot Light	 1 Circuit, 2 Pilot Lights	1/2	2 Circuit		Start/Stop	efdl50-J1U2	efdcl50-J1U2		
				3/4		Universal and 1 Pilot Light		efdl75-J1U2	efdcl75-J1U2
				1				efdl10-J1U2	efdcl10-J1U2
			1/2	1 Circuit		Start/Stop	efdl50-J2U1	efdcl50-J2U1	
			3/4	Universal and 2 Pilot Lights			efdl75-J2U1	efdcl75-J2U1	
			1				efdl10-J2U1	efdcl10-J2U1	
2-Gang Tandem †									
 2 Circuit, 2 Pilot Lights	 2 Circuit, 1 Pilot Light	1/2	2 Circuit		Start/Stop	efdt50-J1U2	efdct50-J1U2		
				3/4		Universal and 1 Pilot Light		efdt75-J1U2	efdct75-J1U2
				1				efdt10-J1U2	efdct10-J1U2
			1/2	2 Circuit		Start/Stop	efdt50-J2U2	efdct50-J2U2	
			3/4	Universal and 2 Pilot Lights			efdt75-J2U2	efdct75-J2U2	
			1				efdt10-J2U2	efdct10-J2U2	

For tandem bodies, external seals must be installed within 5 feet/1.5 meters of each conduit entrance for Class I, Groups C and D. Pilot Lights furnished with 6 Watt, 120 Vac 6S6 lamp and red jewel—Other colored jewels and LED's listed under accessories and parts.

† Malleable iron body and aluminum cover. For aluminum body, add suffix -A.
 ‡ Aluminum body not available.

◆ Shaded area indicates items suitable for Class I, Division 1 and 2, Groups B, C and D; Class II, Groups E, F and G and Class III. For Class I, Group B, external seals must be installed at each conduit entrance.