

# Cross-Reference

## GENERAL-DUTY SAFETY SWITCHES

TABLE 6-31. GENERAL-DUTY

| Ampere Rating                                       | Catalog Number |                   |          |           |
|---|----------------|-------------------|----------|-----------|
|   | Cutler-Hammer® | General Electric® | Siemens® | Square D® |
| <b>Plug Fuse, 1-Pole, 2-Wire, 120 Vac, NEMA 1</b>   |                |                   |          |           |
| 30  | DP111NGB       | TPF130            | LF111N   | D211N     |
| <b>Plug Fuse, 2-Pole, 3-Wire, 240 Vac, NEMA 1</b>   |                |                   |          |           |
| 30  | DP221NGB       | TPF230            | LF211N   | D211N     |
| <b>Fusible, 2-Pole, 3-Wire, 240 Vac, NEMA 1</b>     |                |                   |          |           |
| 30  | DG221NGB       | TG3221            | GF221N   | D221N     |
| 60  | DG222NGB       | TG3222            | GF222N   | D222N     |
| 100   | DG223NGB       | TG3223            | GF223N   | D223N     |
| 200   | DG224NGK       | TG3224            | GF224N   | D224N     |
| 400   | DG225NGK       | TG3225            | GF225N   | D225N     |
| 600   | DG226NGK       | TG3226            | GF226N   | D226N     |
| <b>Fusible, 3-Pole, 3-Wire, 240 Vac, NEMA 1</b>     |                |                   |          |           |
| 30  | DG321NGB       | TG4321            | GF321N   | D321N     |
| 60  | DG322NGB       | TG4322            | GF322N   | D322N     |
| 100   | DG323NGB       | TG4323            | GF323N   | D323N     |
| 200   | DG324NGK       | TG4324            | GF324N   | D324N     |
| 400   | DG325FGK       | TG3325            | GF325N   | D325N     |
| 600   | DG326FGK       | TG3326            | GF326N   | D326N     |
| <b>Fusible, 3-Pole, 4-Wire, 240 Vac, NEMA 1</b>     |                |                   |          |           |
| 30  | DG321NGB       | TG4321            | GF321N   | D321N     |
| 60  | DG322NGB       | TG4322            | GF322N   | D322N     |
| 100   | DG323NGB       | TG4323            | GF323N   | D323N     |
| 200   | DG324NGK       | TG4324            | GF324N   | D324N     |
| 400   | DG325NGK       | TG4325            | GF325N   | D325N     |
| 600   | DG326NGK       | TG4326            | GF326N   | D326N     |
| <b>Non-Fusible, 2-Pole, 2-Wire, 240 Vac, NEMA 1</b> |                |                   |          |           |
| 30  | DG221UGB       | TGN3321           | N/A      | N/A       |
| 60  | DG222UGB       | TGN3322           | N/A      | Q0260NATS |
| 100   | DG223UGB       | TGN3323           | N/A      | Q02000NS  |
| 200   | DG324UGK       | TGN3324           | N/A      | DU324     |
| 400   | DG325UGK       | TGN3325           | N/A      | DU325     |
| 600   | DG326UGK       | TGN3326           | N/A      | DU326     |
| <b>Non-Fusible, 3-Pole, 3-Wire, 240 Vac, NEMA 1</b> |                |                   |          |           |
| 30  | DG321UGB       | TGN3321           | GNF321   | DU321     |
| 60  | DG322UGB       | TGN3322           | GNF322   | DU322     |
| 100   | DG323UGB       | TGN3323           | GNF323   | DU323     |
| 200   | DG324UGK       | TGN3324           | GNF324   | DU324     |
| 400   | DG325UGK       | TGN3325           | GNF325   | DU325     |
| 600   | DG326UGK       | TGN3326           | GNF326   | DU326     |

**Note:** Always verify the number of poles and wires required since catalog numbers may appear in multiple tables.

GENERAL-DUTY (CONTINUED)

| Ampere Rating  | Catalog Number |                  |         |           |
|--|----------------|------------------|---------|-----------|
|  | Cutler-Hammer  | General Electric | Siemens | Square D  |
| <b>Fusible, 2-Pole, 3-Wire, 240 Vac, NEMA 3R</b>     |                |                  |         |           |
| 30   | DG221NRB       | TG3221R          | GF221NR | D221NRB   |
| 60   | DG222NRB       | TG3222R          | GF222NR | D222NRB   |
| 100  | DG223NRB       | TG3223R          | GF223NR | D223NRB   |
| 200  | DG224NRK       | TG3224R          | GF224NR | D224NRB   |
| 400  | DG225NRK       | TG3225R          | GF225NR | D225NR    |
| 600  | DG226NRK       | TG3226R          | GF226NR | D226NR    |
| <b>Fusible, 3-Pole, 3-Wire, 240 Vac, NEMA 3R</b>     |                |                  |         |           |
| 30   | DG321NRB       | TG4321R          | GF321NR | D321NRB   |
| 60   | DG322NRB       | TG4322R          | GF322NR | D322NRB   |
| 100  | DG323NRB       | TG4323R          | GF323NR | D323NRB   |
| 200  | DG324NRK       | TG4324R          | GF324NR | D324NRB   |
| 400  | DG325FRK       | TG3325R          | GF325NR | D325NR    |
| 600  | DG326FRK       | TG3326R          | GF326NR | D326NR    |
| <b>Fusible, 3-Pole, 4-Wire, 240 Vac, NEMA 3R</b>     |                |                  |         |           |
| 30   | DG321NRB       | TG4321R          | GF321NR | D321NRB   |
| 60   | DG322NRB       | TG4322R          | GF322NR | D322NRB   |
| 100  | DG323NRB       | TG4323R          | GF323NR | D323NRB   |
| 200  | DG324NRK       | TG4324R          | GF324NR | D324NRB   |
| 400  | DG325NRK       | TG3325R ①        | GF325NR | D325NR    |
| 600  | DG326NRK       | TG3326R ①        | GF326NR | D326NR    |
| <b>Non-Fusible, 2-Pole, 2-Wire, 240 Vac, NEMA 3R</b> |                |                  |         |           |
| 30   | DG221URB       | TGN3321R         | GNF321R | DU221RB   |
| 60   | DG222URB       | TGN3322R         | GNF322R | DU222RB   |
| 100  | DG223URB       | TGN3323R         | GNF323R | Q02000NRB |
| 200  | DG324URK       | TGN3324R         | GNF324R | DU324RB   |
| <b>Non-Fusible, 3-Pole, 3-Wire, 240 Vac, NEMA 3R</b> |                |                  |         |           |
| 30   | DG321URB       | TGN3321R         | GNF321R | DU321RB   |
| 60   | DG322URB       | TGN3322R         | GNF322R | DU322RB   |
| 100  | DG323URB       | TGN3323R         | GNF323R | DU323RB   |
| 200  | DG324URK       | TGN3324R         | GNF324R | DU324RB   |
| 400  | DG325URK       | N/A              | N/A     | N/A       |
| 600  | DG326URK       | N/A              | N/A     | N/A       |

① Separate neutral kit required.

**Note:** Always verify the number of poles and wires required since catalog numbers may appear in multiple tables.

