

RETROFIT STOCKING KITS (BR & CH KITS AVAILABLE)

5 Recommended Groups: Existing Box Height Determines Retro Group Size

Retrofit Kit Interior Cat. #	Description BR-Aluminium Bus / CH-Copper Bus	Collar Cat. #	Cover Cat. #	Existing Enclosure Parameters			Existing Box Height Determines Retro Size Group
				H	W	D	
RAABR12L125	BR 125A MLO 12/24 ckt Retro Kit	Included	Included	14 - 18"	10 1/2 - 12 1/2"	3 1/2 - 5 1/4"	Retro Size AA / Size 14" - 21"
RAABR10B100	BR 100A MCB 10/20 ckt Retro Kit	Included	Included	14 - 18"	10 1/2 - 12 1/2"	3 1/2 - 5 1/4"	
RAABR12L125A	BR 125A MLO 12/24 ckt Retro Kit	Included	Included	14 - 21"	10 1/2 - 15 1/2"	3 1/2 - 5 1/4"	
RAABR10B100A	BR 100A MCB 10/20 ckt Retro Kit	Included	Included	14 - 21"	10 1/2 - 15 1/2"	3 1/2 - 5 1/4"	
RACH22B125i	CH Interior 125A MCB 22 cks	RACHFRAME	CH8CF	21 - 30"	13 - 22"	4 1/4 - 6"	Retro Size A / Size 21" - 30"
RACH24L125i	CH Interior 125A MLO 24 cks	RACHFRAME	CH8CF	21 - 30"	13 - 22"	4 1/4 - 6"	
RBCH24B150i	CH Interior 150A MCB 24 cks	RACHFRAME	CH8EF	29 - 36"	13 - 22"	4 1/4 - 6"	Retro Size B / Size 29" - 36"
RBCH32L225i	CH Interior 225A MLO 32 cks	RACHFRAME	CH8DF	29 - 36"	13 - 22"	4 1/4 - 6"	
RCCH32B200i	CH Interior 200A MCB 32 cks	RCCHFRAME	CH8JF	34 - 41"	13 - 22"	4 1/4 - 6"	Retro Size C / Size 34" - 41"
RCCH42L225i	CH Interior 225A MLO 42 cks	RCCHFRAME	CH8GF	34 - 41"	13 - 22"	4 1/4 - 6"	
RDCH42B200i	CH Interior 200A MCB 42 cks	RDCHFRAME	CH8KF	37 - 45"	13 - 22"	4 1/4 - 6"	Retro Size D / Size 37" - 45"
RDCH42L225i	CH Interior 225A MLO 42 cks	RDCHFRAME	CH8KF	37 - 45"	13 - 22"	4 1/4 - 6"	

Other options are available.

CH Retrofit Interiors and Collar Cartons are color coded to ensure accuracy of kit.