

# Eaton 3S UPS

550 – 700 VA



## Ideal for protecting:

- computers and peripherals
- Broadband modems (internet and TV)
- IP telephony equipment
- POS equipment



## Power protection for office and home computer equipment

### Protection against power problems

- The Eaton 3S UPS helps to protect your computer equipment in case of everyday events such as lightning strikes, storms, over-demand on the utility grid, accidents, and natural disasters knocking out power without warning.
- In the event of a total blackout, the unit provides sufficient battery backup time to last through most power outages.
- The 3S also protects telephone, broadband and Ethernet line from “back door” power surges.
- The shutdown software makes it possible to automatically save your work and shut down your application without losing any data. Once the power is restored, you can continue working exactly where you left off.

### Easy integration and installation

- Attractive design and glossy finish make the 3S a perfect fit for the modern office environment.
- The 3S comes with 8 IEC outlets for easy connection of typical computer configurations with peripherals.
- The 3S features a HID-compliant USB port (cable supplied), for automatic integration with common operating systems (Windows/Mac OS/Linux).
- Compact unit fits on or under your desk or can be mounted on a wall.
- Easy-to-replace battery helps to extend UPS service life.

# EATON

Powering Business Worldwide

Celebrating  
**100** YEARS  
Ideals that Endure

# Eaton 3S UPS

- 1 4 IEC outlets with surge protection
- 2 4 IEC outlets with battery backup and surge protection
- 3 On / Off button + LED interface
- 4 USB port
- 5 Dataline protection
- 6 Replaceable battery
- 7 Reset button (circuit breaker)
- 8 Wall-mounting system



Eaton 3S 550/700 IEC

TECHNICAL SPECIFICATIONS	Eaton 3S 550	Eaton 3S 700
Rating (VA/W)	550 VA / 330 W	700 VA / 420 W
<b>Application</b>		
Output connection (IEC models)	4 outlets with battery backup and surge protection + 4 outlets with surge protection	
<b>Characteristics</b>		
Input voltage	Up to 161-284 V (adjustable)	
Output voltage	230 V (settable to 220 V, 230 V or 240 V)	
Frequency	50-60 Hz autoselect	
Input protection	Resettable circuit breaker	
<b>Battery</b>		
Battery type	Compact, sealed lead-acid (replaceable)	
Battery test	Yes	Yes
Cold start (no mains power)	Yes	Yes
Deep-discharge protection	Yes	Yes
Battery replacement indicators	LED	LED
50% load backup	10 min	9 min
70% load backup	6 min	6 min
<b>Communication</b>		
Communications port	HID-compliant USB port for automatic integration with most common operating systems (Windows XP, Vista and 7, Linux, Mac OS X), cable supplied	
Line protection	Tel/fax/modem/internet/Ethernet	
<b>Standards compliance</b>		
Safety	IEC/EN 62040-1-1, CE mark	
EMC	IEC 62040-2	
<b>Dimensions, weight and colour</b>		
Dimensions H x W x D	86 x 140 x 335 mm	86 x 170 x 335 mm
Weight	2.9 kg	3.8 kg
Colour	Black	Black
<b>Customer service &amp; support</b>		
Warranty	3 years on electronics, 2 years on batteries	
<b>Part numbers</b>		
IEC sockets	550 3S550IEC	700 3S700IEC

In the interests of continuous product improvement all specifications are subject to change without notice.

SINGAPORE  
Tel : +65 6825 1684  
Fax : +65 6825 1689  
EatonSEA@eaton.com

INDONESIA  
Tel : +62 21 522 6181  
Fax : +62 21 522 6182

THAILAND  
Tel : +66 2575 0530  
Fax : +66 2575 1579

MALAYSIA  
Tel : +603 7804 3618  
Fax : +603 7803 6193

VIETNAM  
Tel : +84 4 3936 5303  
Fax : +84 4 3936 5307

Eaton is a trade name, trademark and/or service mark of Eaton Corporation or its subsidiaries and affiliates.