

6" INCANDESCENT REFLECTOR TRIMS

6 INCH INCANDESCENT REFLECTOR TRIMS



6"

6 INCH INCANDESCENT REFLECTOR TRIMS

B607CP-WH Reflector R/PAR30



B607RG-WH



B607W-WH



B607MB-WH




B607CL-WH



B607 _____ - _____

O. D.	REFLECTOR	TRIM/RING	HOUSING	MAX. LAMP W.
7-1/4"	CL, RG, W, MB, BZ, CP, SN, SHZ	WH, BK, SN, CP, CH, PB, BZ	B6IC, B6RIC, B26IC, B26RIC	75W R/PAR30
			B6, B6R, B26, B26R	100W R/PAR30
			B6IC-100, B600-IC	100W R/PAR30



B627RG-WH Reflector R40/PAR38



B627CP-WH



B627W-WH



B627MB-WH




B627CL-WH



B627 _____ - _____

O. D.	REFLECTOR	TRIM/RING	HOUSING	MAX. LAMP W.
7-1/4"	CL, RG, W, MB, BZ, CP, SN, SHZ	WH, BK, SN, CP, CH, PB, BZ	B6, B6R, B26, B26R	150W R40/PAR38
			B6IC-100, B600-IC	100W R40/PAR38



B608CL-WH Cone Reflector A-19



B608RG-WH



B608W-WH



B608MB-WH




B608CP-WH



B608 _____ - _____

O. D.	REFLECTOR	TRIM/RING	HOUSING	MAX. LAMP W.
7-1/4"	CL, RG, W, MB, BZ, CP, SN, SHZ	WH, BK, SN, CP, CH, PB, BZ	B6IC, B6RIC	75W A19
			B6, B6R	150W A21
			B6IC-100, B600-IC	100W A19



B617CL-WH Shallow Cone Reflector A-19



B617RG-WH



B617W-WH




B617MB-WH



B617 _____ - _____

O. D.	REFLECTOR	TRIM/RING	HOUSING	MAX. LAMP W.
7-1/4"	CL, RG, W, MB, BZ, CP, SN, SHZ	WH, BK, SN, CP, CH, PB, BZ	B26IC, B26RIC	60W A19
			B26, B26R	100W A21



BAFFLE FINISH:

W White
P Black
SN Satin Nickel
CP Copper
BZ Bronze

REFLECTOR FINISH:

CL Chrome
RG Gold
W White
MB Black

BZ Bronze
CP Copper
SN Satin Nickel
SHZ Satin Haze

RING/TRIM FINISH:

WH White
BK Black
SN Satin Nickel
CP Copper

CH Chrome
PB Polish Brass
BZ Bronze



General Lighting



Accent Lighting



Task Lighting



Wall Wash Lighting



Sloped Ceiling Lighting