

## Three-Phase Encapsulated—Type EPT, 60 Hz

2

## 240 Delta Volts to 208Y/120 Volts

kVA	Full Capacity Taps		Type	°C Temp. Rise	Frame	Wiring Diagram Number	Weight Lbs (kg)	Weathershield	Catalog Number
	FCAN	FCBN							
9	—	2 at -5%	EPT	115	FR103	70C	190 (86)	Indoor-Outdoor	<b>Y24G28T09N</b> ①
15	—	2 at -5%	EPT	115	FR95	70C	275 (125)	Indoor-Outdoor	<b>Y24G28T15N</b> ①
30	2 at +2.5%	4 at -2.5%	EPT	115	FR243	84C	422 (191)	Indoor-Outdoor	<b>Y24M28T30N</b>
45	2 at +2.5%	4 at -2.5%	EPT	115	FR244	84C	660 (299)	Indoor-Outdoor	<b>Y24M28T45N</b>

## 380 Delta Volts to 190Y/110 Volts

kVA	Full Capacity Taps		Type	°C Temp. Rise	Frame	Wiring Diagram Number	Weight Lbs (kg)	Weathershield	Catalog Number
	FCAN	FCBN							
3	—	2 at -5%	EPT	115	FR201	70F	116 (53)	Indoor-Outdoor	<b>Y38G19T03A</b> ①
6	—	2 at -5%	EPT	115	FR200	70F	165 (75)	Indoor-Outdoor	<b>Y38G19T06A</b> ①
9	—	2 at -5%	EPT	115	FR95	70F	275 (125)	Indoor-Outdoor	<b>Y38G19T09A</b> ①
15	—	2 at -5%	EPT	115	FR95	72R	275 (125)	Indoor-Outdoor	<b>Y38G19T15A</b> ①
30	2 at +2.5%	4 at -2.5%	EPT	115	FR243	84AC	422 (191)	Indoor-Outdoor	<b>Y38M19T30A</b>
45	2 at +2.5%	4 at -2.5%	EPT	115	FR244	84AC	660 (299)	Indoor-Outdoor	<b>Y38M19T45A</b>
75	2 at +2.5%	4 at -2.5%	EPT	115	FR245	84AC	1275 (580)	Indoor-Outdoor	<b>Y38M19T75A</b> ②

## 380 Delta Volts to 208Y/120 Volts

kVA	Full Capacity Taps		Type	°C Temp. Rise	Frame	Wiring Diagram Number	Weight Lbs (kg)	Weathershield	Catalog Number
	FCAN	FCBN							
3	—	2 at -5%	EPT	115	FR201	70D	116 (53)	Indoor-Outdoor	<b>Y38G28T03A</b> ①
6	—	2 at -5%	EPT	115	FR200	70F	165 (75)	Indoor-Outdoor	<b>Y38G28T06A</b> ①
9	—	2 at -5%	EPT	115	FR103	70D	185 (84)	Indoor-Outdoor	<b>Y38G28T09A</b> ①
15	—	2 at -5%	EPT	115	FR95	70D	275 (125)	Indoor-Outdoor	<b>Y38G28T15A</b> ①
30	2 at +2.5%	4 at -2.5%	EPT	115	FR243	84H	422 (191)	Indoor-Outdoor	<b>Y38M28T30A</b>
45	2 at +2.5%	4 at -2.5%	EPT	115	FR244	84R	660 (299)	Indoor-Outdoor	<b>Y38M28T45A</b>
75	2 at +2.5%	4 at -2.5%	EPT	115	FR245	84R	1275 (580)	Indoor-Outdoor	<b>Y38M28T75A</b> ②

**Notes**

① T-T (Scott T) connected secondary.

② Floor-mount only.

Contact your local Eaton sales office for CE Mark transformer requirements. For other ratings or catalog numbers not shown, or for special enclosure types (including stainless steel), refer to Eaton. Frame drawings/dimensions information begins on **Page V2-T2-216**.