


Universal Pedestal Clamp with Cable Management Feature

Features

- Only one attachment required for both mesh bonding and cable management
- Eliminates need for separate mounting brackets for different pedestal types or sizes
- Stainless steel construction of bracket and hardware reduces potential for galvanic corrosion
- Mesh bonding conductors do not have to be bent around each pedestal to conform to grid pattern
- Reduces material and labor cost
- Provides attachment points for CADDY® CAT LINKS J-Hooks
- Code compliance (NEC® Article 250 and NEC Article 300)
- UL® Listed as a grounding/bonding clamp in addition to a cable support



MBNUPCJ240



MBNUPCJ82

The Universal Pedestal Clamp, part of the ERITECH® line from ERICO, allows for fast, simple and economical field construction of mesh bonding network (MBN) and cable management systems in data centers and computer rooms. In addition to multiple cross-wire bonding connections, each connector will also accommodate additional pigtailed that can be used to connect to building steel and equipment.

Universal Pedestal Clamp

Part Number	Pedestal Size (Round or Square)	Conductor Size Range	Standard Packaging Quantity
MBNUPCJ82	7/8" - 2" (2.2 cm - 5.1 cm)	#8 AWG - #2 AWG (10 mm ² - 35 mm ²) Solid or Stranded	25
MBNUPCJ240	7/8" - 2" (2.2 cm - 5.1 cm)	#2 AWG - 4/0 AWG (35 mm ² - 100 mm ²) Solid or Stranded	25



MBNUPCJ240 +
CAT32HP (2" J-Hook)



MBNUPCJ82 +
CAT48HP (3" J-Hook)



MBNUPCJ82 +
CAT32HP (2" J-Hook) +
CAT48HP (3" J-Hook)

Compatible J-Hook Sizes



J-Hooks may be combined in trees, with a load not exceeding 50 lbs (22.7 kg).

Part Number	Diameter	Standard Packaging Quantity
CAT16HP	1" (25 mm)	50
CAT32HP	2" (50 mm)	50
CAT48HP	3" (75 mm)	25
CAT64HP	4" (100 mm)	25

NEC is a registered trademark of, and National Electrical Code (NEC) standard is a copyright of the National Fire Protection Association. UL is a registered trademark of UL LLC.

WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright ©2011, 2012 ERICO International Corporation. All rights reserved. CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

www.erico.com

