



NEW!

Shower Trim with Round Drop Lens

EL996W White Ring
Lamp: 30W R20
O.D.: 4 7/8"



NEW!

Shower Trim with Reflector and Albalite Lens

EL9114BZ Bronze Ring
EL9114CP Copper Ring
EL9114W White Ring
EL9114SH Lexan Ring
Lamp: 40W A19, 50W PAR20, R20
O.D.: 4 3/4"



NEW!

Shower Trim with Clear Lens and Reflector

EL9111W White Ring
EL9111SH Lexan Ring
Lamp: 30W R20
O.D.: 4 3/4"



NEW!

Shower Trim with Reflector and Frosted Pinhole Glass

EL9115BZ Bronze Ring
EL9115CP Copper Ring
EL9115W White Ring
EL9115SH Lexan Ring
Lamp: 40W A19, 50W PAR20, R20
O.D.: 4 3/4"



NEW!

Shower Trim with Frosted Lens and Reflector

EL9112W White Ring
EL9112B Black Ring
EL9112BZ Bronze Ring
EL9112C Clear Ring
EL9112CP Copper Ring
EL9112G Gold Ring
EL9112N Nickel Ring
EL9112SH Lexan Ring
Lamp: 40W A19, 50W PAR20, R20
O.D.: 4 3/4"



NEW!

Shower Trim with Reflector and Drop Opal Lens

EL9116C Clear Ring
EL9116B Black Ring
EL9116BZ Bronze Ring
EL9116CP Copper Ring
EL9116G Gold Ring
EL9116SH Lexan Ring
EL9116W White Ring
Lamp: 40W A19, 50W PAR20, R20
O.D.: 4 3/4"



NEW!

Shower Trim with Fresnel Lens and Reflector

EL9113W White Ring
EL9113BZ Bronze Ring
EL9113CP Copper Ring
EL9113G Gold Ring
EL9113SH Lexan Ring
Lamp: 40W A19, 50W PAR20, R20
O.D.: 4 3/4"



Adjustable Gimbal Ring with Deep Baffle

EL934WB Black Bfl. White Ring
EL934WW All White
Lamp: 50W JDR, 120V MR16 with PSA28 or PSA29
O.D.: 4 3/4"



Adjustable Spot Trim

EL988BW Black Spot White Ring
EL988B All Black
EL988G All Gold
EL988W All White
Lamp: 50W JDR, 120V MR16 with PSA28 or PSA29
O.D.: 4 3/4"



Adjustable Spot Cylinder Trim

EL995W All White
EL995B All Black
EL995BW Black Cylinder White Ring
Lamp: 50W JDR, 120V MR16 with PSA28 or PSA29
O.D.: 4 3/4"



Baffle with Adjustable Lamp Holder Bracket

EL995W All White
EL995B Black Bfl. White Ring
EL995BZ All Bronze **NEW!**
EL995CP All Copper **NEW!**
EL995N All Nickel
Lamp: 50W PAR20, 55W PAR16
O.D.: 4 3/4"



Reflector with Adjustable Lamp Holder Bracket

EL977C Clear Ref. White Ring
EL977B Black Ref. White Ring
EL977G Gold Ref. White Ring
EL977W All White
Lamp: 50W PAR20, 55W PAR16
O.D.: 4 3/4"



Eyeball Trim

EL998W All White
EL998B All Black
EL998BZ All Bronze **NEW!**
EL998C All Clear
EL998CP All Copper **NEW!**
EL998N All Nickel
EL998G All Gold
Lamp: 50W PAR20, 55W PAR16
O.D.: 4 3/4"



Adjustable Gimbal Ring

EL985N All Nickel
EL985B All Black
EL985BZ All Bronze **NEW!**
EL985CP All Copper **NEW!**
Lamp: 50W PAR20
O.D.: 4 3/4"



NEW!

Eyeball Trim with Special Clips and Socket

EL998SB All Black
EL998SW All White
Lamp: 50W PAR20, 55W PAR16
O.D.: 4 3/4"

Recessed Lighting

For use with EL99, EL99A, EL99R, EL99RA, and EL99IC housings (p. 30).




Adjustable Spot Cylinder Trim

EL955W All White
EL955B All Black
EL955BW Black Cylinder White Ring
 Lamp: 50W JDR, 120V MR16 with PSA28 or PSA29
 O.D.: 4 3/4"

Adjustable Spot Trim

EL988BW Black Spot White Ring
EL988W All White
EL988B All Black
EL988G All Gold
 Lamp: 50W JDR, 120V MR16 with PSA28 or PSA29
 O.D.: 4 3/4"



Reflector with Adjustable Lamp Holder Bracket

EL977C Clear Ref. White Ring
EL977G Gold Ref. White Ring
EL977B Black Ref. White Ring
EL977W All White
 Lamp: 50W PAR20, 55W PAR16
 O.D.: 4 3/4"

Eyeball Trim

EL998W All White
EL998G All Gold
EL998B All Black
EL998BZ All Bronze **NEW!**
EL998C All Clear
EL998CP All Copper **NEW!**
EL998N All Nickel
 Lamp: 50W PAR20, 55W PAR16
 O.D.: 4 3/4"

All 3" Line Voltage Housings are:

- UL damp location listed
- UL feed through listed



3" Miniature Airtight Housing

EL39A NEW!
 • Height: 4 7/8"
 • Opening: 3 5/8"
 • Lamp: 50W max 120V GU10



3" Miniature Airtight Remodel Housing

EL39RA NEW!
 • Height: 5 3/8"
 • Opening: 3 5/8"
 • Lamp: 50W max 120V GU10



3" Miniature Airtight IC Housing

EL39ICA NEW!
 • Height: 5 1/2"
 • Opening: 3 5/8"
 • Lamp: 50W max 120V GU10



3" Incandescent Remodel Downlight with Open Trim

RR300W
 • Lamp: 50W PAR20, R20
 • O.D. 5"



3" Incandescent Remodel Downlight with Baffle Trim

RR301B
 • Lamp: 50W PAR20, R20
 • O.D. 5"



3" Incandescent Remodel Downlight with Baffle Trim

RR301W
 • Lamp: 50W PAR20, R20
 • O.D. 5"



3" Incandescent Remodel Downlight with Eyeball Trim

RR302W
 • Lamp: 50W PAR20, R20
 • O.D. 5"

Recessed Lighting