

6" Horizontal CFL Optics

Catalog Number:
BHHR6PL-1X9-Mark10-MVOLT-6501-CL-WH

Project Name:

Type:

Note:

MAXILUME
ARCHITECTURAL LIGHTING

<p>6501-CL Reflector</p>  <p>REFLECTOR FINISH: CL, WT, MB, SHZ, W</p> <p>RING FINISH: WH, SCH, SHZ</p> <p>A= 5-1/2" • B= 7-3/8"</p>	<p>6502-WH-CL Baffle with Reflector</p>  <p>BAFFLE FINISH: WH, P</p> <p>REFLECTOR FINISH: CL</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>	<p>6507-SHZ Wall Wash Reflector</p>  <p>REFLECTOR FINISH: CL, WT, MB, SHZ, W</p> <p>RING FINISH: WH, SCH, SHZ</p> <p>A= 5-1/2" • B= 7-3/8"</p>	<p>6508-CL Crossblade Reflector</p>  <p>REFLECTOR FINISH: CL, WT, MB, SHZ</p> <p>RING FINISH: WH</p> <p>A= 5-1/2" • B= 7-3/8"</p>
<p>6503-CL Reflector with Fresnel Glass Lens</p>  <p>FOR WET LOCATION</p> <p>REFLECTOR FINISH: CL, WT, MB, SHZ, W</p> <p>RING FINISH: WH</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>	<p>6504-CL Reflector with Prismatic Glass Lens</p>  <p>FOR WET LOCATION</p> <p>REFLECTOR FINISH: CL, WT, MB, SHZ, W</p> <p>RING FINISH: WH</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>	<p>6505-P Baffle with Fresnel Glass Lens</p>  <p>FOR WET LOCATION</p> <p>BAFFLE FINISH: WH, P</p> <p>RING FINISH: WH</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>	<p>6506-WH Baffle with Prismatic Glass Lens</p>  <p>FOR WET LOCATION</p> <p>BAFFLE FINISH: WH, P</p> <p>RING FINISH: WH</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>
<p>6514-CL Reflector with Frosted Glass Lens</p>  <p>FOR WET LOCATION</p> <p>REFLECTOR FINISH: CL, WT, MB, SHZ, W</p> <p>RING FINISH: WH, SCH, SHZ</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>	<p>6515-WT Reflector with Tempered Clear Glass</p>  <p>FOR WET LOCATION</p> <p>REFLECTOR FINISH: CL, WT, MB, SHZ, W</p> <p>RING FINISH: WH, SCH, SHZ</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>	<p>6512-WH Baffle with Frosted Glass Lens</p>  <p>FOR WET LOCATION</p> <p>BAFFLE FINISH: WH, P</p> <p>RING FINISH: WH</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>	<p>6513-WH Baffle with Tempered Clear Glass</p>  <p>FOR WET LOCATION</p> <p>BAFFLE FINISH: WH, P</p> <p>RING FINISH: WH</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>
<p>6516-CL Reflector with Prismatic Plastic Lens</p>  <p>FOR WET LOCATION</p> <p>REFLECTOR FINISH: CL, WT, MB, SHZ, W</p> <p>RING FINISH: WH</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>	<p>6518-WT Reflector with Tempered Clear Plastic</p>  <p>FOR WET LOCATION</p> <p>REFLECTOR FINISH: CL, WT, MB, SHZ, W</p> <p>RING FINISH: WH</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>	<p>6517-WH Baffle with Prismatic Plastic Lens</p>  <p>FOR WET LOCATION</p> <p>BAFFLE FINISH: WH, P</p> <p>RING FINISH: WH</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>	<p>6519-WH Baffle with Tempered Clear Plastic</p>  <p>FOR WET LOCATION</p> <p>BAFFLE FINISH: WH, P</p> <p>RING FINISH: WH</p> <p>A= 5-1/2" • B= 7-3/8" • C= 1"</p>