


6" COMPACT FLUORESCENT TRIMS

6 INCH COMPACT FLUORESCENT TRIMS

6"

6 INCH COMPACT FLUORESCENT TRIMS



PATENT #:
7,736,031 / D571,036

B725W-WH Baffle with Frosted Dome

The new B725 trim with opalescent lens is designed to give the appearance of the incandescent light output on a compact fluorescent housing while reducing glare and improving light distribution.

B725 _____ - _____




O. D.	BAFFLE	TRIM/RING	HOUSING	MAX. LAMP W.
7-1/4"	W, P, SN, CP, BZ	WH, BK, SN, CP, CH, PB, BZ	B6PL(IC), B6PLR(IC) B6PLIC-26/32-E B6-GU24-IC, B6-GU24-RIC	18W TTT, 26W TTT 26W TTT 14W, 19W, 26W GU24

B731W-WH Full Cone Baffle



B731P-WH



PATENT #:
7,597,460 / D551,384

B731 _____ - _____




O. D.	AVAILABLE COLORS	HOUSING	MAX. LAMP W.
7-1/4"	W-WH, P-WH, SN-SN, CP-CP, BZ-BZ	B6PLIC, B6PLRIC, B6PLIC-32 B6PL, B6PLR B6-GU24-IC, B6-GU24-RIC	18W TTT, 26W TTT, 32TTT 18W, 26W, 32W, 42W TTT 14W, 19W, 26W GU24

B722W-CL-WH Cone Reflector/Baffle



B722P-CL-WH



PATENT #:
7,597,460 / D551,797

B722 _____ - _____ - _____



O. D.	AVAILABLE COLORS	HOUSING	MAX. LAMP W.
7-1/4"	W-CL-WH, P-CL-WH, W-W-WH	B6PLIC, B6PLRIC, B6PLIC-32 B6PL, B6PLR B6-GU24-IC, B6-GU24-RIC	18W TTT, 26W TTT, 32TTT 18W, 26W, 32W, 42W TTT 14W, 19W, 26W GU24

AF724W-WH Deep Self Flange Air-Shut Baffle




AF724CP-CP



AF724SN-SN



AF724P-WH



AF724 _____ - _____



NEW CLIP DESIGN

O. D.	AVAILABLE COLORS	HOUSING	MAX. LAMP W.
7-1/4"	W-WH, P-WH, SN-SN, CP-CP, BZ-BZ	B6-GU24-IC B6-GU24-RIC	14W, 19W, 26W GU24

BAFFLE FINISH:

- W** White
- P** Black
- SN** Satin Nickel
- CP** Copper
- BZ** Bronze

REFLECTOR FINISH:

- CL** Chrome
- RG** Gold
- W** White
- MB** Black

- BZ** Bronze
- CP** Copper
- SN** Satin Nickel
- SHZ** Satin Haze

RING/TRIM FINISH:

- WH** White
- BK** Black
- SN** Satin Nickel
- CP** Copper
- CH** Chrome
- PB** Polish Brass
- BZ** Bronze

