


[Products](#)

[401 Clevis Hanger](#)

401 Clevis Hanger

4010200EG (179423)

 [All Countries](#) [Change](#)

 [Print this page](#)



Features


- Recommended for the suspension of stationary non-insulated pipe lines
- Also commonly used for the suspension of insulated pipe lines
- Flared edges help prevent sharp surfaces from coming into contact with the pipe (1/2" to 2" pipe sizes)
- Clevis bottom pivots to allow pipe to be fed from either direction
- Conforms with U.S. Federal Specification WW-H-171 (Type 1), Manufacturers Standardization Society (MSS) SP-58 (Type 1)

Product Specifications

Part Number	4010200EG
Article Number	179423
Material	Steel
Finish	Electrogalvanized, Pregalvanized
Pipe Size	2"
NB/DN	50
Outer Diameter (OD)	2 3/8", 60 mm
Rod Size (RS)	3/8", M10

A	4 5/16", 110 mm
B	2 1/2", 63 mm
C	7/8", 22 mm
Static Load (F)	610 lb, 2,700 N
Standard Packaging Quantity	50 pc
UPC	78285635624
UNSPSC	40141725
EAN-13	8711893038125
ETIM	EC010049
Certifications	cULus, FM

A shield is recommended for insulated pipe applications to effectively distribute the load.



Application Photos






Downloads

Catalogs

-  [CADDY® Fixings and Supports for Heating, Plumbing, Air Conditioning and Ventilation](#)
13.75 MB English
-  [CADDY® Fixings and Supports for Heating, Plumbing, Air Conditioning and Ventilation, Pocket Catalog](#)
12.64 MB English
-  [CADDY® Fixings and Supports for Plumbing, Fire Protection, Heating, Ventilation and Air Conditioning Catalog](#)
6.43 MB English
-  [CADDY® Mechanical Hangers and Supports for Plumbing, HVAC and Fire Protection Catalog](#)
9.42 MB English
-  [Fire Sprinkler Hanging & Bracing Products](#)
3.69 MB English
-  [Fixings and Supports for Plumbing, Fire Protection, Heating, Ventilation and Air Conditioning](#)
1.28 MB English
-  [CADDY® Fijaciones y Soportes para Calefaccion, Fontaneria, Aire Acondicionado, y Ventilacion Catálogo \(Europa\)](#)
13.14 MB Español
-  [CADDY® Soportes mecánicos para plomería, calefacción / ventilación / aire acondicionado \(HVAC\) y protección contra incendios](#)
7.29 MB Español
-  [Supports et attaches mécaniques pour plomberie, chauffage, climatisation et protection incendie](#)
29.88 MB Français
-  [固定及支撑件 - 消防、暖通、空调及排水](#)
5.94 MB 中文

Certifications

-  [cUL VFXT7.EX2452](#)
ULC/ORD-C203
-  [FM](#)
582 KB English
-  [UL VFXT.EX2452](#)
ANSI/UL 203

Warning, Warranty and Limitation of Liability

Due to a policy of continued product development, specifications are subject to change without notice.
CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

FM is a registered certification mark of FM Approvals LLC, LTD.

UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

