

Products

510 CADDY® EZ RISER

510 CADDY® EZ RISER

5100100EG (179327)

[All Countries](#) [Change](#)

[Print this page](#)



Features

- Recommended for suspending vertical steel pipe risers
- Slotted holes make assembly easy, eliminating loose hardware
- Serrated flange-head bolts eliminate need for wrenches on both bolt and nut
- Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)


Product Specifications

Part Number	5100100EG
Article Number	179327
Material	Steel
Finish	Electrogalvanized
Pipe Size	1"
NB/DN	25
Outer Diameter (OD)	1.315", 34 mm
Hole Size (HS)	7/16", 11 mm
A	9", 229 mm


B	1", 25 mm
Static Load (F)	255 lb, 1,100 N
Standard Packaging Quantity	25 pc
UPC	78285636924
UNSPSC	40141725
EAN-13	8711893089431
ETIM	EC010049

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Slotted holes and bolts for pipe sizes up to 12" only.



Application Photos



Downloads

Catalogs

 [CADDY® Fixings and Supports for Heating, Plumbing, Air Conditioning and Ventilation, Pocket Catalog](#)
12.64 MB English


 [CADDY® Fixings and Supports for Plumbing, Fire Protection, Heating, Ventilation and Air Conditioning Catalog](#)
6.42 MB English

6.45 MB English

 [CADDY® Mechanical Hangers and Supports for Plumbing, HVAC and Fire Protection Catalog](#)
9.42 MB English

 [Fire Sprinkler Hanging & Bracing Products](#)
3.69 MB English

 [Fixings and Supports for Plumbing, Fire Protection, Heating, Ventilation and Air Conditioning](#)
1.28 MB English

 [CADDY® Soportes mecánicos para plomería, calefacción / ventilación / aire acondicionado \(HVAC\) y protección contra incendios](#)
7.29 MB Español

 [Supports et attaches mécaniques pour plomberie, chauffage, climatisation et protection incendie](#)
29.88 MB Français

 [固定及支撑件 - 消防、暖通、空调及排水](#)
5.94 MB 中文

Datasheets

 [510 Riser Clamp](#)
111 KB English

Warning, Warranty and Limitation of Liability

Due to a policy of continued product development, specifications are subject to change without notice.
CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.