

MBJ Grounding and Bonding Braid, Tinned Copper – MBJ70-300-12 (563420)



MBJ Grounding and Bonding Braids are a reliable and convenient grounding solution for applications that require flexibility and durability. The tinned copper ground braids with massivated palms come ready to install without any additional cutting, stripping, crimping or punching and do not require the addition of tin or crimped lugs. The proprietary manufacturing process optimizes the electrical contact between each wire and helps eliminate moisture issues in the palms, preventing corrosion and lengthening the useful life of the braid.

- Complete range of earth/ground flexible connections from 6 - 100 mm² (11.84 - 197.35 kcmil) cross section and from 100 - 500 mm (3.937" - 19.685") length
- Integral palm, without tin or crimped lugs for superior electrical contact and tensile strength resistance
- Resistant to vibration and fatigue, reducing maintenance
- Provides weight savings, material savings and lower impedance when compared to similar lugged cables with insulation
- Ready to use out of the box, eliminates the need for cutting, stripping, crimping and punching
- Quick and easy to install
- Recommended by the EMC/EMI directives and less impedance than cables
- EAC compliant
- RoHS compliant



| | |
|---------------------|---|
| Part Number | MBJ70-300-12 |
| Article Number | 563420 |
| Material | Copper |
| Finish | Tinned |
| Working Temperature | 221 °F Max |
| Complies With | IEC® 60439.1 IEC® 61439.1 |
| Intensity | 290 A |
| Thickness (T) | 0.133" |
| Cross Section | 138.15 kcmil |
| Length (L) | 11.811" |
| Hole Size (HS) | 0.492" |
| A | 1.102" |
| B | 1.3" |
| Unit Weight | 0.462 lb |
| Certifications | CE cULus EAC 741300009 (Russian Federation) |

| | |
|-----------------------------|---------------|
| Part Number | MBJ70-300-12 |
| | RoHS |
| Standard Packaging Quantity | 10 pc |
| UPC | 78285657960 |
| EAN-13 | 3479775634203 |

IEC is a registered trademark of the International Electrotechnical Commission. UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

Pentair products shall be installed and used only as indicated in Pentair's product instruction sheets and training materials. Instruction sheets are available at erico.pentair.com and from your Pentair customer service representative. Improper installation, misuse, misapplication or other failure to completely follow Pentair's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2017 Pentair All rights reserved

Pentair, CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH and LENTON are owned by Pentair or its global affiliates.

All other trademarks are the property of their respective owners. Pentair reserves the right to change specifications without prior notice.