


# Molded Case Circuit Breakers

## External Accessories

### Door-Mounted Operators



TDM Operating Handle, Fixed or Adjustable Shaft

### TDM Handle Operating Mechanisms, Door Mounted

Complete mechanism with handle UL listed, E-57253

Operating mechanism only, UL Component Recognized, E-57253

Breaker Type	Box Depth in Inches	Complete Mechanism <sup>1</sup> with NEMA 1, 3R, 12 Handle Product Number	Operating Mechanism Only Product Number	Handle Only	
				NEMA 1, 3R, 12 Product Number	NEMA 4/4X Product Number
TQD, THQD	Extended Shaft 4 5/16 - 14 5/16	TQDHM2	TQDOM2 <sup>2</sup>		
	Shallow Mount 4 3/16	TEFHM1	TEFOM1		
TEB, TEC, TB1, TED, THED	Extended Shaft 5-1/8 - 5 7/32	TEFHM3	TEFOM3	TH1	
	5 1/8 - 5 13/16	TEFHM4	TEFOM4		
	5 1/8 - 15	TEFHM2	TEFOM2		
TFC, TFJ, TFK, THFK	Shallow Mount 5 7/8	TFKHM1	TFKOM1		THCH45 <sup>3,4</sup>
	Extended Shaft 6 7/8 - 15 1/2	TFKHM2	TFKOM2 <sup>2</sup>		
TJC, TJD, TJJ, TJK, THJK, TB4, TBC4	Shallow Mount 5 7/8	TJKHM1	TJKOM1	TH2	
	Extended Shaft 5 5/8 - 15 5/8	TJKHM2	TJKOM2 <sup>4</sup>		
TKC, TKM, THKM, TB6, TBC6, TB8, TBC8	Shallow Mount 7 7/16	TKMHM1	TKMOM1		
	Extended Shaft 7 1/32 - 17 5/16	TKMHM2	TKMOM2 <sup>4</sup>		
SE150 (GEH-5611) <sup>5</sup>	4 3/16	SEFHM1	SEFOM1	TH1	
	6 1/8 - 15	SEFHM2	SEFOM2 <sup>2</sup>		
SF250 (GEH-5611) <sup>5</sup>	5 7/8	SEFHM1	SEFOM1		THCH45 <sup>3,4</sup>
	7 3/4 - 15 1/2	SEFHM2	SEFOM2 <sup>2</sup>		
SG600 (GEH-5653) <sup>5</sup>	5 7/8	SGHM1	SGOM1	TH2	
	5 5/8 - 15 5/8	SGHM2	SGOM2 <sup>4</sup>		
SK1200 (GEH-5612) <sup>5</sup>	6	SKHM1	SKOM1		
	7	SKHM2	SKOM2 <sup>4</sup>		

<sup>1</sup>Handle assembly and operating mechanism separately packaged.

<sup>2</sup>For 15-inch long shaft order Product Number 788A831G10. For 20-inch long shaft order Product Number 788A831G20.

<sup>3</sup>Provides interlocking for J600, SG600 SK1200, and K1200 breakers when used with the extended shaft operating mechanism. For interlocking with E150/SE150, F225 and SF250 order special shaft Product Number 788A832G1.

<sup>4</sup>For 15-inch long shaft order Product Number 788A832G2. For 20-inch long shaft order Product Number 788A832G5.

<sup>5</sup>Installation instructions publication number.

<sup>6</sup>MOD 1 is 7 7/16; MOD 2 is 8 3/32.

<sup>7</sup>MOD 1 is 7 3/16 - 17 3/16; MOD 2 is 7 15/16 - 17 15/16.

### Handle Accessories for TDM Operating Mechanisms

Device	Product Number
Replacement neoprene gaskets for NEMA 1, 3R and 12 enclosures	
Use with TH1	788A742P3
Use with TH2	788A742P4

