

Modular Metering Meter Mod III

Main Modules
Single-Phase and Three-Phase

Section 2

Factory Installed Lug Kit

Main Breaker	Amp Rating	Phase		Neutral		GE Lug Kit Product No.	Lugs Per Kit	Total Lugs Per Device
		Wire Size	Wire Size	Wire Size	Wire Size			
TMP3SB4R	400	AL:(2) 2/0-500 or (1) 6-600 Cu	2/0-400 or (1) 6-600	(2) 2-600		TCLK265	2 lugs per kit	
TMP3SB4R	400	AL:(2) 2/0-500 or (1) 6-600 Cu	2/0-400 or (1) 6-600	(2) 2-600		TCLK365	3 lugs per kit	
TMP3HB4R	400	AL:(2) 2/0-500 or (1) 6-600 Cu	2/0-400 or (1) 6-600	(2) 2-600		TCLK265	2 lugs per kit	
TMP3HB4R	400	AL:(2) 2/0-500 or (1) 6-600 Cu	2/0-400 or (1) 6-600	(2) 2-600		TCLK365	3 lugs per kit	
TMP3B6R	600	AL:(2) 2/0-500 or (1) 6-600 Cu	2/0-400 or (1) 6-600	(2) 2-600		TCLK265	2 lugs per kit	
TMP3SB6R	600	AL:(2) 2/0-500 or (1) 6-600 Cu	2/0-400 or (1) 6-600	(2) 2-600		TCLK365	3 lugs per kit	
TMP3HB6R	600	AL:(2) 2/0-500 or (1) 6-600 Cu	2/0-400 or (1) 6-600	(2) 2-600		TCLK265	2 lugs per kit	
TMP3HB6R	600	AL:(2) 2/0-500 or (1) 6-600 Cu	2/0-400 or (1) 6-600	(2) 2-600		TCLK365	3 lugs per kit	
TMP3B8R	800	AL/Cu (3) 3/0-500		(4) 250-500		TCAL124	1 lug per kit	
TMP3SB8R	800	AL/Cu (3) 3/0-500		(4) 250-500		TCAL124	1 lug per kit	
TMP3B10R	1000	Al(4) 250-500 Cu(4) 250/350		(4) 250-500		TCAL125	1 lug per kit	
TMP3SB10R	1000	Al(4) 250-500 Cu(4) 250/350		(4) 250-500		TCAL125	1 lug per kit	
TMP3B12R	1200	Al(4) 250-500 Cu(4) 250/350		(4) 250-500		TCAL125	1 lug per kit	
TMP3SB12R	1200	Al(4) 250-500 Cu(4) 250/350		(4) 250-500		TCAL125	1 lug per kit	
TMPBB14R	1400	Al/Cu (4) 500-1000		Al/Cu (4) 500-1000		TMPL1600RD	1 lug per kit, 4 holes per lug	3 lugs per device
TMPBT14R	1400	Al/Cu (4) 500-1000		Al/Cu (4) 500-1000		TMPL1600RD	1 lug per kit, 4 holes per lug	3 lugs per device
TMP3BB14R	1400	Al/Cu (4) 500-1000		Al/Cu (4) 500-1000		TMPL1600RD	1 lug per kit, 4 holes per lug	4 lugs per device
TMP3BT14R	1400	Al/Cu (4) 500-1000		Al/Cu (4) 500-1000		TMPL1600RD	1 lug per kit, 4 holes per lug	4 lugs per device
TMPBB16R	1600	Al/Cu (4) 500-1000		Al/Cu (4) 500-1000		TMPL1600RD	1 lug per kit, 4 holes per lug	3 lugs per device
TMP3BB16R	1600	Al/Cu (4) 500-1000		Al/Cu (4) 500-1000		TMPL1600RD	1 lug per kit, 4 holes per lug	4 lugs per device
TMPBB16RST	1600	Al/Cu (4) 500-1000		Al/Cu (4) 500-1000		TMPL1600RD	1 lug per kit, 4 holes per lug	3 lugs per device
TMP3BB16RST	1600	Al/Cu (4) 500-1000		Al/Cu (4) 500-1000		TMPL1600RD	1 lug per kit, 4 holes per lug	4 lugs per device
TMPBT16R	1600	Al/Cu (4) 500-1000		Al/Cu (4) 500-1000		TMPL1600RD	1 lug per kit, 4 holes per lug	3 lugs per device
TMP3BT16R	1600	Al/Cu (4) 500-1000		Al/Cu (4) 500-1000		TMPL1600RD	1 lug per kit, 4 holes per lug	4 lugs per device
TMPBT16RST	1600	Al/Cu (4) 500-1000		Al/Cu (4) 500-1000		TMPL1600RD	1 lug per kit, 4 holes per lug	3 lugs per device
TMP3BT16RST	1600	Al/Cu (4) 500-1000		Al/Cu (4) 500-1000		TMPL1600RD	1 lug per kit, 4 holes per lug	4 lugs per device
TMPBB20R	2000	Al/Cu (6) #2-600		Al/Cu (6) #2-600		TMPL2000RD	9 lugs per kit	6 lugs per device, 3 lugs/neutral
TMP3BB20R	2000	Al/Cu (6) #2-600		Al/Cu (6) #2-600		TMPL2000RD	9 lugs per kit	9 lugs per device, 3 lugs/neutral
TMPBT20R	2000	Al/Cu (6) #2-600		Al/Cu (6) #2-600		TMPL2000RD	9 lugs per kit	6 lugs per device, 3 lugs/neutral
TMP3BT20R	2000	Al/Cu (6) #2-600		Al/Cu (6) #2-600		TMPL2000RD	9 lugs per kit	9 lugs per device, 3 lugs/neutral

Optional Lug Kit

Main Breaker	Amp Rating	Phase			Neutral		
		Wire Size	GE Lug Kit Product No.	GE Lug Product No.	Lugs Per Kit	Wire Size	GE Lug Kit Product No.
TMPBB14R	1400	(6) #2-600	TMPL2000RD	N/A	9	(6) #2-600	TMPL2000N
TMPBT14R	1400	(6) #2-600	TMPL2000RD	N/A	9	(6) #2-600	TMPL2000N
TMP3BB14R	1400	(6) #2-600	TMPL2000RD	N/A	9	(6) #2-600	TMPL2000N
TMP3BT14R	1400	(6) #2-600	TMPL2000RD	N/A	9	(6) #2-600	TMPL2000N
TMPBB16R	1600	(6) #2-600	TMPL2000RD	N/A	9	(6) #2-600	TMPL2000N
TMP3BB16R	1600	(6) #2-600	TMPL2000RD	N/A	9	(6) #2-600	TMPL2000N
TMPBB16RST	1600	(6) #2-600	TMPL2000RD	N/A	9	(6) #2-600	TMPL2000N
TMP3BB16RST	1600	(6) #2-600	TMPL2000RD	N/A	9	(6) #2-600	TMPL2000N
TMPBT16R	1600	(6) #2-600	TMPL2000RD	N/A	9	(6) #2-600	TMPL2000N
TMP3BT16R	1600	(6) #2-600	TMPL2000RD	N/A	9	(6) #2-600	TMPL2000N
TMPBT16RST	1600	(6) #2-600	TMPL2000RD	N/A	9	(6) #2-600	TMPL2000N
TMP3BT16RST	1600	(6) #2-600	TMPL2000RD	N/A	9	(6) #2-600	TMPL2000N

