

Pilot and Signaling Devices Heavy-Duty 30.5 mm Watertight/Oiltight Accessories

Section 9


CR104P

Nameplates and Legend Inserts
600 Volts max. AC/DC
10 Amperes Continuous


Nameplates—Standard Lithographed

Unless otherwise indicated, all nameplates are black and available in Sizes 1-3 only. To select size, replace asterisk (*) in product number with appropriate digit from Sizes table.


| Nameplate Marking | Product Number | List Price GO-10P1 |
|--|----------------|-----------------------|
| Blank (Sizes 1-5) | CR104PXN*B | \$1.80 |
| Blank (Red, sizes 1-5) | CR104PXN*R | \$1.80 |
| Blank (with round) | CR104PXN6E | \$2.50 |
| CLOSE | CR104PXN*BP006 | \$1.80 |
| DECREASE | CR104PXN*BP007 | \$1.80 |
| DOWN | CR104PXN*BP008 | \$1.80 |
| EMERGENCY STOP (Red) | CR104PXN*RP009 | \$1.80 |
| FAST | CR104PXN*BP010 | \$1.80 |
| FORWARD | CR104PXN*BP011 | \$1.80 |
| HIGH | CR104PXN*BP012 | \$1.80 |
| IN | CR104PXN*BP013 | \$1.80 |
| INCH | CR104PXN*BP014 | \$1.80 |
| INCREASE | CR104PXN*BP017 | \$1.80 |
| JOG | CR104PXN*BP018 | \$1.80 |
| JOG FORWARD | CR104PXN*BP019 | \$1.80 |
| JOG REVERSE | CR104PXN*BP020 | \$1.80 |
| LEFT | CR104PXN*BP021 | \$1.80 |
| LOW | CR104PXN*BP022 | \$1.80 |
| LOWER | CR104PXN*BP023 | \$1.80 |
| OFF | CR104PXN*BP024 | \$1.80 |
| ON | CR104PXN*BP025 | \$1.80 |
| OPEN | CR104PXN*BP026 | \$1.80 |
| OUT | CR104PXN*BP027 | \$1.80 |
| POWER ON | CR104PXN*BP084 | \$1.80 |
| RAISE | CR104PXN*BP028 | \$1.80 |
| RESET | CR104PXN*BP030 | \$1.80 |
| RETURN | CR104PXN*BP031 | \$1.80 |
| REVERSE | CR104PXN*BP032 | \$1.80 |
| RIGHT | CR104PXN*BP033 | \$1.80 |
| RUN | CR104PXN*BP034 | \$1.80 |
| SLOW | CR104PXN*BP036 | \$1.80 |
| START | CR104PXN*BP037 | \$1.80 |
| START CYCLE | CR104PXN*BP038 | \$1.80 |
| STOP (Red) | CR104PXN*RP040 | \$1.80 |
| STOP CYCLE (Red) | CR104PXN*RP041 | \$1.80 |
| TEST | CR104PXN*BP043 | \$1.80 |
| UP | CR104PXN*BP047 | \$1.80 |
| EMERGENCY STOP PULL TO TEST (Red) | CR104PXN*BP048 | \$1.80 |
| PUSH TO STOP PULL TO START | CR104PXN*BP085 | \$1.80 |
| FOR REV | CR104PXN*BP050 | \$1.80 |
| HAND AUTO | CR104PXN*BP051 | \$1.80 |
| HIGH LOW | CR104PXN*BP052 | \$1.80 |
| JOG RUN | CR104PXN*BP053 | \$1.80 |
| LEFT RIGHT | CR104PXN*BP054 | \$1.80 |
| LOW HIGH | CR104PXN*BP055 | \$1.80 |
| LOWER RAISE | CR104PXN*BP056 | \$1.80 |
| OFF ON | CR104PXN*BP057 | \$1.80 |
| OPEN CLOSE | CR104PXN*BP058 | \$1.80 |
| RAISE LOWER | CR104PXN*BP059 | \$1.80 |
| REV FOR | CR104PXN*BP060 | \$1.80 |
| RUN JOG | CR104PXN*BP061 | \$1.80 |
| SAFE RUN | CR104PXN*BP062 | \$1.80 |
| SAFE STOP RUN | CR104PXN*BP063 | \$1.80 |
| SLOW FAST | CR104PXN*BP064 | \$1.80 |
| START JOG | CR104PXN*BP087 | \$1.80 |
| START STOP | CR104PXN*BP086 | \$1.80 |
| STOP START | CR104PXN*BP065 | \$1.80 |
| UP DOWN | CR104PXN*BP066 | \$1.80 |
| OFF COOLANT ON | CR104PXN*BP067 | \$1.80 |
| AUTO OFF-HAND | CR104PXN*BP083 | \$1.80 |
| FOR OFF REV | CR104PXN*BP068 | \$1.80 |
| FOR STOP REV | CR104PXN*BP069 | \$1.80 |
| HAND OFF AUTO | CR104PXN*BP070 | \$1.80 |
| JOG OFF RUN | CR104PXN*BP071 | \$1.80 |
| JOG SAFE RUN | CR104PXN*BP072 | \$1.80 |
| LOW OFF HIGH | CR104PXN*BP073 | \$1.80 |
| LOWER OFF RAISE | CR104PXN*BP074 | \$1.80 |
| MAN OFF AUTO | CR104PXN*BP076 | \$1.80 |
| OPEN OFF CLOSE | CR104PXN*BP077 | \$1.80 |
| REV OFF FOR | CR104PXN*BP079 | \$1.80 |
| SLOW OFF FAST | CR104PXN*BP080 | \$1.80 |
| SLOW STOP FAST | CR104PXN*BP081 | \$1.80 |
| POTENTIOMETER MARKINGS | CR104PXN*BP082 | \$1.80 |
| OFF AUTO | CR104PXN1BP090 | \$1.80 |
| ON OFF AUTO | CR104PXN1BP091 | \$1.80 |
| PUSH TO STOP - TURN TO RESET (Round w/Yellow Background) | CR104PXN6EP092 | \$2.50 |
| Yellow Background Emergency Stop | CR104PXN6EP009 | \$2.50 |




Standard (Size 1)




Large (Size 2)



Extra-large Automotive (Size 3)



Small Joystick (Size 4; available for XN*R and XN*B only)



Large Joystick (Size 5; available for XN*R and XN*B only)

Sizes*

| Nameplate | Dimensions (H x W, Inches) | *Product No. Digit |
|---|----------------------------|--------------------|
| Standard (Size 1) | 1.98 x 1.93 | 1 |
| Large (Size 2) | 1.98 x 2.63 | 2 |
| Extra-large, automotive (Size 3) | 2.40 x 2.44 | 3 ¹ |
| Small joystick (Size 4; available for XN*R and XN*B only) | 2.32 x 2.32 | 4 ¹ |
| Large joystick (Size 5; available for XN*R and XN*B only) | 2.92 x 2.92 | 5 ¹ |

¹These nameplates do not fit standard enclosures.

