


Molded Case Circuit Breakers

External Accessories

Lugs and Associated Hardware

Section 6



Breaker with Line and Load Studs

Lugs, Line Shields, Covers and Bus Connectors

Accessory	Wire Range	For Use With	Product Number	Description	
Copper-Aluminum Lugs	(1) #14-6 Cu, #12-2 Al	TQC (15-60A) (Non DIN Rail)	TQAL3	Single Lug	
	(1) #4-1/0 Cu-Al	TQC (70-100A)	TQAL4	Single Lug	
	(1) #4-300 kcmil Cu-Al	TQD		TCAL25	Single Lug
				TCALK325	3-Lug Kit
	(1) #14-8	E150, THLC1, TB1, (15-30A)	TCAL14	Single Lug	
	(1) #14-3 Cu, #12-1 Al	E150, THLC1, TB1, (15-60A)	TCAL12	Single Lug	
	(1) #6-2/0 Cu, #4-2/0 Al	E150, THLC1, TB1, (70-90A)	TCAL12A	Single Lug	
	(1) #3-3/0 Cu, #1-3/0 Al	E150, THLC1, TB1, (100-150A)	TCAL15	Single Lug	
	(1) #4-300 kcmil Cu-Al	F225		TCAL24	Single Lug
				TCALK324	3-Lug Kit
	(1) 6-600 kcmil or (2) 2/0-250 kcmil Cu-Al	J400, TB4, J600 (Thru 400A), TJD	TCAL43	Single Lug	
	(2) 4/0-350 kcmil Cu or (2) 300-500 kcmil Al	J600 (450-600A)		TCAL63	Single Lug
				TCALK363	3-Lug Kit
	(1) 750 kcmil Cu-Al	J400 TJD	TCAL47	Single Lug	
	(1) 3/0-500 kcmil or (2) 3/0-250 kcmil Cu-Al	TLB4, THLC4	TCLK43	Single Lug	
	(2) 1/0-250 kcmil or (1) #4-600 kcmil Cu-Al	K1200, TB6 (300-400A)	TCAL41	Single Lug	
	(2) 2/0-500 kcmil Cu-A	K1200, TB6 (300-600A)		TCAL61	Single Lug
				TCALK261	2-Lug Kit w/ Wrench
				TCALK361	3-Lug Kit w/ Wrench
	(3) 3/0-500 kcmil Cu-Al	K1200, TB8 (600-800A)		TCAL81 ¹	Single Lug
				TCALK281 ¹	2-Lug Kit w/ Wrench
				TCALK381 ¹	3-Lug Kit w/ Wrench
	(3) 3/0-500 kcmil Cu-Al	TK4V - Load end		TCAL91 ¹	Single Lug
				TCALK291 ¹	2-Lug Kit w/ Wrench
				TCALK391 ¹	3-Lug Kit w/ Wrench
	(4) 250-350 kcmil Cu or (4) 250-500 kcmil Al	K1200 (1000-1200A)		TCAL121 ²	Single Lug
				TCALK2121 ²	2-Lug Kit w/ Wrench
				TCALK3121 ²	3-Lug Kit w/ Wrench
(3) 750 kcmil Cu-Al	K1200 (1200A)		TCAL122 ³	Single Lug	
			TCALK2122 ³	2-Lug Kit w/ Wrench	
			TCALK3122 ³	3-Lug Kit w/ Wrench	
(4) 250-350 kcmil Cu or (4) 250-500 kcmil Al	TK4V - Load end	TCAL131 ²	Single Lug		
Copper Only Lugs With Follower and Extra Plating	#14-2/0	E150, TB1 (thru 150A)	TC012	Single Lug	
	#4-300 kcmil Cu	TFJ (250A)	TC024	Single Lug	
	(1) 6-600 kcmil or (2) 1/0-250 kcmil Cu	J400, TB4	TC043	Single Lug	
			TC063	Single Lug	
	(1) 1/0-600 kcmil or (2) 1/0-250 kcmil Cu	K1200, TB6 (300-400A)	TC041 ⁴	Single Lug	
			TC061	Single Lug	
	(2) 2/0-500 kcmil Cu	K1200, TB6, (300-600A)	TC081A	Single Lug	
	(3) 3/0-500 kcmil Cu	K1200, TB8 (600-800A)	TC081A	Single Lug	
	(3) 3/0-500 kcmil Cu	TK4V - Load end	TC091	Single Lug	
	(4) 250-400 kcmil Cu	K1200 (1000-1200A)	TC0121	Single Lug	
	(4) 250-400 kcmil Cu	TK4V - Load end	TC0131	Single Lug	
	Line Shield		TEB, TEC, TED, THED	TEDLS	
TFJ, TFK, TFC			TFKLS		
TJJ, TJK, TJC			TJKLS		
Lug Cover, TKM Breaker (two per breaker)		TC061, TCAL61, TCAL81 Lugs, TC081A	789A448G1		
		TC0121, TCAL121 Lugs	789A448G2		
Connector (back strap)		TKM	TKMC1		
Line voltage control wire kit for terminating control wire at breaker lugs		K1200	SKLVK ⁶		

¹Not suitable for 100 A aluminum conductor.

²Suitable for 500 kcmil copper for voltage drop considerations.

³Not UL listed, requires user supplied lug cover.

⁴Not UL listed.

⁵End cover supplied with 800A frame is used as lug cover.

⁶3-pole kit.

