

Control Renewal Parts

Renewal Parts

Section 14

For NEMA Rated 300- and 200-Line Magnetic Contactors and Starters
NEMA Sizes 00-7

Magnet Coil

NEMA Size	Starter Prefix	Product Number	List Price GO-11G
00,0,1	300- and 200-Line	15D21G***	\$57.00
2	300- and 200-Line	15D22G***	\$81.00
3	300- and 200-Line	55-501336G***	\$148.00
4	300- and 200-Line	55-501463G***	\$202.00
5	200-Line	55-501493G***	\$222.00
5	300-Line	55-530249G***	\$222.00
6	300- and 200-Line	55-536548G*** ¹	\$402.00



Magnet Coil

***Coil Suffix Table

List prices are for coils with standard voltages and frequencies. For pricing of coils with special voltages and frequencies, refer to current issue of GEP-3910.

Voltage							
60 Hertz	24	115-120	200-208	230-240	265-277	460-480	575-600
Specify Suffix	024	002	023	003	013	004	005

Voltage					
50 Hertz	110	220	380	440	550
Specify Suffix	002	003	064	004	005


Note: The 002 coil suffix (115-120 V, 60 Hz/110V, 50 Hz) supersedes the 022 coil suffix (120 V, 60 Hz).

AC Replacement Coils

NEMA Size	Coil Voltage	Starter Prefix	Product Number	List Price GO-11G
6	115/120	300- and 200-Line	55-522089G011 ²	\$525.00
6	200/208, 230	300- and 200-Line	55-522089G007 ²	\$525.00
6	380, 415	300- and 200-Line	55-522089G005 ²	\$525.00
6	460	300- and 200-Line	55-522089G004 ²	\$525.00
6	575	300- and 200-Line	55-522089G003 ²	\$525.00
7	115/120	300- and 200-Line	55-522003G009	\$608.00
7	200/208, 230	300- and 200-Line	55-522003G006	\$608.00
7	380, 415	300- and 200-Line	55-522003G004	\$608.00
7	460	300- and 200-Line	55-522003G003	\$608.00
7	575	300- and 200-Line	55-522003G002	\$608.00

Contact Kit


NEMA Size	No. of Poles	Starter Prefix	Product Number	List Price GO-11GS
00	4	300- and 200-Line	55-152313G009	\$44.00
0	4	300- and 200-Line	546A300G002	\$76.00
1	4	300- and 200-Line	546A301G053	\$114.00
2	3	300- and 200-Line	546A780G051	\$174.00
3	3	300- and 200-Line	55-153677G002	\$308.00
4	3	300- and 200-Line	55-153678G002	\$628.00
5	3	200-Line	55-154607G002	\$1516.00
5	3	300-Line	55-154607G041	\$1516.00
6	3	300- and 200-Line	55-186556G004 ¹	\$1628.00
6	3	300- and 200-Line	232A6724G009 ²	\$1859.00
6	2	300- and 200-Line	232A6724G011 ²	\$1259.00
7	3	300- and 200-Line	232A6724G010	\$2062.00
7	2	300- and 200-Line	232A6724G012	\$1375.00



Contact Kit

200-Line Block Overload Relay

NEMA Size	Starter Prefix	Reference Number	Product Number	List Price GO-10H
00, 0, 1	200-Line	CR224C310F	CR324C310F9X ³	\$54.00
2	200-Line	CR224D310F	CR324D310FX ³	\$78.00
3	200-Line	CR224E310F	CR324E310FX ³	\$108.00
4	200-Line	CR224F310F	CR324F310FX ³	\$168.00
5	200-Line	CR224G310F	CR324G310FX ^{3,4,5}	\$54.00



200-Line Block Overload Relay

¹Size 6 with 305HH, 306HH, 307HH, and 308HH nomenclature.

²Size 6 with 385H, 386H, 387H, 388H, and 389H nomenclature.

³Order by new CR324 product number. Obsolete CR224 product number is for reference only.

⁴If current transformer assembly is also required, order: one 55-501394G012 and two 55-501394G013, \$180.00 each, GO-11G.

⁵Power Factor capacitor terminals are not part of Size 5 and 6 overload relays.

