

Panelboards Spectra™ Series Panelboards Renewal Parts

Mounting Hardware

Order from the Customer Service Center

Section 11

Filler Plates Plug-In or Bolt-On Spectra™

Use to cover unused spaces.

Includes filler plate support brackets and hardware.

| Space X Height ¹ | Box Width Range | Switchboard Section Widths | Product Number |
|-----------------------------|-----------------|----------------------------|----------------|
| 1X | 27", 31" | 35 | APP1S |
| 2X | 27", 31" | 35 | APP2S |
| 3X | 27", 31" | 35 | APP3S |
| 4X | 27", 31" | 35 | APP4S |
| 5X | 27", 31" | 35 | APP5S |
| 6X | 27", 31" | 35 | APP6S |
| 1X | 36", 40" | 40 | APP1 |
| 2X | 36", 40" | 40 | APP2 |
| 3X | 36", 40" | 40 | APP3 |
| 4X | 36", 40" | 40 | APP4 |
| 5X | 36", 40" | 40 | APP5 |
| 6X | 36", 40" | 40 | APP6 |
| 1X | 44" | 45 | APP1W |
| 2X | 44" | 45 | APP2W |
| 3X | 44" | 45 | APP3W |
| 4X | 44" | 45 | APP4W |
| 5X | 44" | 45 | APP5W |
| 6X | 044" | 45 | APP6W |

¹ X-height: 1X = 1 3/8"

Mounting Hardware Plug-In or Bolt-On Spectra™ ADS Switch Replacement Load Base Kits

Includes load base, clips and lugs.

| Replacement for Load Base Part Number | Load Base Ampere Rating | Load Base - No. of Poles | Load Base Voltage | Product Number |
|---------------------------------------|-------------------------|--------------------------|-------------------|----------------|
| ADS22030HD | - | - | - | 331A1519G1 |
| ADS32030HD | - | - | - | 331A1519G2 |
| ADS322060HD | - | - | - | 331A1519G3 |
| ADS32060HD | - | - | - | 331A1519G4 |
| ADS26030HD | - | - | - | 331A1519G5 |
| ADS36030HD | - | - | - | 331A1519G6 |
| ADS26060HD | - | - | - | 331A1519G7 |
| ADS36060HD | - | - | - | 331A1519G8 |
| ADS36200JD | - | - | - | 331A1519G12 |
| ADS26200JD | - | - | - | 331A1519G16 |
| ADS36200JM | - | - | - | 331A1519G20 |
| ADS26200JM | - | - | - | 331A1519G22 |
| - | 100A | 2-pole | 240V & 600V | 331A1519G9 |
| - | 100A | 3-pole | 240V & 600V | 331A1519G10 |
| - | 100A | 3-pole | 240V & 600V | 331A1519G14 |
| - | 100A | 2-pole | 240V & 600V | 331A1519G18 |
| - | 200A | 3-pole | 240V & 600V | 331A1519G11 |
| - | 200A | 2-pole | 240V & 600V | 331A1519G13 |
| - | 200A | 2-pole | 240V & 600V | 331A1519G15 |
| - | 200A | 2-pole | 240V & 600V | 331A1519G17 |
| - | 200A | 3-pole | 240V & 600V | 331A1519G19 |
| - | 200A | 2-pole | 240V & 600V | 331A1519G21 |
| - | 400A | 2-pole | 240V & 600V | 331A1545G1 |
| - | 400A | 3-pole | 240V & 600V | 331A1545G3 |
| - | 400A | 2-pole | 240V & 600V | 331A1545G5 |
| - | 400A | 3-pole | 240V & 600V | 331A1545G7 |
| - | 600A | 2-pole | 240V & 600V | 331A1545G2 |
| - | 600A | 3-pole | 240V & 600V | 331A1545G4 |
| - | 600A | 2-pole | 240V & 600V | 331A1545G6 |
| - | 600A | 3-pole | 240V & 600V | 331A1545G8 |
| - | 400-1200A | - | - | 331A1543G1 |

Mounting Hardware Single Breaker Plug-In Spectra™

Included when ordering AMC module. Only required when mounting breaker on existing module.

Kit contains screws and washers to mount one circuit breaker on AMC circuit breaker mounting module.

| Circuit Breaker Mounting Module Part Number | Product Number |
|---|----------------|
| AMC6EB | AHKE1 |
| AMC4SE | |
| AMC4EB | |
| AMC6EBS | |
| AMC6EL | AHKEL1 |
| AMC2FLS | AHKF1 |
| AMC6FJ | |
| AMC4FJ | |
| AMC3FJ | |
| AMC2FJ | |
| AMC6FLS | |
| AMC3FLS | |
| AMC4FLS | |
| AMC2GM | AHKG1 |
| AMC6GB | |
| AMC4GB | |
| AMC3GM | |
| AMC2JK | AHKJ1 |
| AMC6JK | |
| AMC4JK | |
| AMC3JK | |
| AMC3LB | AHKLB1 |
| AMC6LB | |
| AMC4QD | AHKQ1 |
| AMC6QD | |
| FCS, FCV, FCN, FCH or FCL | AHKFD1 |
| FGV, FGN, FGH or FGP | AHKFG1 |

Mounting Hardware—Hardware only; no brackets or straps Bolt-On Spectra™

| Breaker Frame | Product Number |
|---------------------------|----------------|
| SE | AHKBE1 |
| SF | AHKBF1 |
| SG | AHKBG1 |
| THQD | AHKBQ1 |
| FCS, FCV, FCN, FCH or FCL | AHKBFD1 |
| FGV, FGN, FGH or FGP | AHKBFG1 |
| FB | AHKBFB1 |

