

# Molded Case Circuit Breakers

## Q-Line Circuit Breakers

Accessories  
240V Class

## Section 6

### Terminals (Lugs) for Q-Line Circuit Breakers


Ampere Rating	Termination Type	Wire Range (Cu/Al)	Product Number
15-60	Lug (line only)	14-6/12-2	TQAL3A
15-60	Lug (load only)	14-2/12-2	THQEL3
15-60	Quick connector (load only)	(4) 14/(4) 12	THQECC



Quick Connector THQECC

### Mounting Accessories for THQB, THQC

Product Type	Ampere Rating	# of Poles	Used With Frame	Product Number
Bolt-on Mounting Base		3	THQB/TEY	TEY3B
Back Mounting Plates		1	THQC	TQCBMPA1
Screw Type				
Back Mounting Plates		2	THQC	TQCBMPA2
Screw Type				
Back Mounting Plates		3	THQC	TQCBMPA3
Screw Type				
Back Mounting Plates		10	THQC	TQCBMPA10
Screw Type				
Front-mounting Plates		1	THQC	TQCFMP1 <sup>1</sup>
Front-mounting Plates		2	THQC	TQCFMP2 <sup>1</sup>
Front-mounting Plates		3	THQC	TQCFMP3 <sup>1</sup>
Front-mounting Plates		4	THQC	TQCFMP4 <sup>1</sup>
Pack of 48 Front/Rear Mounting Clips		1 & 2-pole 15-60A	THQC	THQCFMK
Pack of 24 DIN rail clips			THQC	THQCDIN




Load Lug THQEL3

<sup>1</sup>Not UL listed.

### Mounting Accessories for THQC, THQC-GF, GFEP

Product Type	# of Poles	Used With Frame	Product Number
Snap In Back Mounting Plates	1	THQC, THQC-GF	TQCGFBMPA1
Snap In Back Mounting Plates	2	THQC, THQC-GF	TQCGFBMPA2
Snap In Back Mounting Plates	3	THQC, THQC-GF	TQCGFBMPA3
Snap In Back Mounting Plates	10	THQC, THQC-GF	TQCGFBMPA10



Mounting Kit THQCFMK

### Mounting Accessories for TQL

Product Type	Ampere Rating	# of Poles	Used With Frame	Product Number
Plug-in Mounting Base	70 amp	2	TQL	571B595DDG1
Plug-in Mounting Base	70 amp	3	TQL	571B595DDG2
Plug-in Mounting Base	100 amp	3	TQL	565B837G1
Plug-in Mounting Base	100 amp	2	TQL	565B837G2

