



GROUND ROD COUPLINGS

Refer to ground rod part number for appropriate coupling

Threadless Couplings for "Copper-Coated" Rods - Cast Bronze



Refer to ground rod part number for appropriate coupling

Catalog Number	Rod Size	Pcs. Per Ctn.	Wt. Per 100	NAED UPC No. 632591-
50-TC*	1/2"	25	22	61344-6
60-TC**	5/8"	25	25	70724-4
70-TC*	3/4"	10	40	61223-4

Notes: * UL and CSA Listed/For use with UL and/or CSA Listed copper-coated rods only.
** UL and RUS Listed/For use with UL Listed copper-coated rods only.

Threaded Couplings for "Copper-Coated" Sectional Rods - Cast Bronze



Refer to ground rod part number for appropriate coupling

Catalog Number	Rod Size	Pcs. Per Ctn.	Wt. Per 100	NAED UPC No. 632591-
50-LC*	1/2" (9/16"-12)	25	17	70735-0
60-C**	5/8" (5/8"-11)	25	25	70720-6
70-C*	3/4" (3/4" - 10)	25	40	70721-3
80-C*	1" (1"-8)	25	100	70722-0

Notes: * UL and CSA Listed for US and Canada
** UL, RUS and CSA Listed
Made from high-strength corrosion-resistant copper alloy, tapped for use on all standard threaded sectional rods.

Threadless Couplings for "Hot-Dip Galvanized" Rods - Plated Steel




Refer to ground rod part number for appropriate coupling

Catalog Number	Rod Size	Pcs. Per Ctn.	Wt. Per 100	NAED UPC No. 632591-
GRC-54G ^a	5/8"	100	30	61134-3
GRC-625G ^o	5/8"	100	30	61132-9
GRC-34G	3/4"	25	38	61133-6
GRC-100F ^s	1"	25	90	61492-4

Notes: ^a For GR6258 /UL Listed ^o For GR6258F
^s Coupling CSA Listed for US and Canada

Threadless Couplings for "Stainless Steel" Rods (304 Stainless)



Refer to ground rod part number for appropriate coupling

Catalog Number	Rod Size	Pcs. Per Ctn.	Wt. Per 100	NAED UPC No. 632591-
GRC-58SS	5/8"	25	30	70683-4
GRC-34SS	3/4"	25	38	70684-1
GRC-100SS	1"	25	90	61493-1

Notes: Listed by CSA for US and Canada

Threaded Couplings for "Stainless Steel" Rods (304 Stainless)



Refer to ground rod part number for appropriate coupling

Catalog Number	Rod Size	Pcs. Per Ctn.	Wt. Per 100	NAED UPC No. 632591-
GRC-58SST	5/8" (5/8" - 11)	25	30	61122-0
GRC-34SST	3/4" (3/4" - 10)	25	38	61123-7
GRC-100SST	1" (1" - 8)	25	90	61494-8

Notes: Listed by CSA for US and Canada