



## POOL and SPA

# "Jones Bond"™ system

### GROUND ROD CLAMPS

For connecting ground wire to ground rod  
 Cast bronze body with silicon bronze bolt, for use with copper wire only  
 UL listed for direct burial in earth and concrete

NAED NUMBER	CATALOG NUMBER	GROUND ROD SIZE (IN)	GROUND WIRE MAX	CTN QTY	EST. SHIPPING	
					WEIGHT (lbs)	UNIT
27000	G 29	3/8	#4 STR	50	3.3	CTN
27010	G 30	1/2	#4 SOL	50	4.2	CTN
27020	G 31	5/8	1/0 SOL	50	5.6	CTN
27030	G 32	3/4	#2 SOL	50	6.7	CTN
27040	G 100	1	1/0 STR	25	7.6	CTN

**Direct Burial**  
 Copper wire only



### PIPE CLAMPS

For connecting ground wire to water pipe  
 Cast bronze body, silicon bronze screws, for use with copper wire only  
 UL listed for direct burial in earth and concrete

NAED NUMBER	CATALOG NUMBER	WATER PIPE SIZE (IPS)	GROUND WIRE MAX	CTN QTY	EST. SHIPPING	
					WEIGHT (lbs)	UNIT
70620	G 1S-DB	1/2 - 1	#2 STR	50	9.5	CTN
70622	G 2S-DB	1 1/4 - 2	#2 STR	25	9.0	CTN

**Direct Burial**




### U-BOLT CLAMPS

Heavy Duty U-bolt Clamps  
 Use to connect wire to pipe, rod, or fence posts  
 Cast bronze bodies with silicon bronze hardware, for use with copper wire only  
 CSA NRTL/C Certified for direct burial in earth and concrete

NAED NUMBER	CATALOG NUMBER	ROD SIZE (IN)	WATER PIPE SIZE (IPS)	CABLE RANGE	EST. SHIPPING	
					WEIGHT (lbs)	UNIT
25020	C 101	1/2	1/4		0.5	EA
25080	C 104	5/8 - 3/4	3/8	2/0 - #4	0.6	EA
25160	C 108	7/8 - 1	1/2 - 3/4		0.6	EA
25260	C 114	-	1		0.7	EA
25360	C 120	-	1 1/4	2/0 - #4	0.9	EA
25560	C 132	-	2		1.0	EA
71245	C 142	-	3		1.5	EA

**Direct Burial**



Parallel or 90° connection to rod or pipe

See C100 Series for complete listing of sizes.  
 PLATING: For tin plating of above items add suffix "P" to CATALOG NUMBER.

### STAINLESS STEEL HARDWARE KITS

Sets of stainless steel screws, washers, and nuts  
 Use to mount BTL-DB and BL Series lugs to equipment  
 Each kit packaged in clear plastic display box

**Direct Burial**

NAED NUMBER	CATALOG NUMBER	SCREW		KIT CONTENTS				EST. SHIPPING	
		SIZE	L (IN)	SCREWS	WASHERS FLAT	NUTS LOCK	WEIGHT (lbs)	UNIT	
27221	SS 10-A	10-24	1/2	50	100	50	50	.4	KIT
27223	SS 10-B		3/4					.5	KIT
27225	SS 10-C		1					.6	KIT
27226	SS 10-D		1 1/4					.6	KIT
27231	SS 0-A	1/4-20	1/2	25	50	25	25	.6	KIT
27233	SS 0-B		3/4					.7	KIT
27235	SS 0-C		1					.8	KIT
27237	SS 0-D		1 1/2					.9	KIT



For larger sizes of stainless steel or silicon bronze see HARDWARE pages.