

TYPICAL GENERATOR/TRANSFER SWITCH COMBINATIONS

| Current Model - NEXUS | Current Switch model # | Description | Prior Models (5/08-5/09) | Prior Switch model # (*see note) |
|-----------------------|------------------------|-------------|--------------------------|----------------------------------|
|-----------------------|------------------------|-------------|--------------------------|----------------------------------|

Nexus models / transfer switches and prior models / transfer switches listed CAN be used together. See notes below for details

| | | | | |
|--|----------------------------------|---|--------------------|-----------|
| QT02224ANAX QT02516ANSX QT02724ANAX QT03016ANSX | | 22 kW Liquid-Cooled Generator, 1phase - Aluminum | QT02224ANAN | |
| | | 25 kW Liquid-Cooled Generator, 1phase - Steel | QT02516ANSN | |
| | | 27 kW Liquid-Cooled Generator, 1phase - Steel | QT02724ANAN | |
| | | 30 kW Liquid-Cooled Generator, 1phase - Steel | QT03016ANSN | |
| | RTSX100A3 | 100 amp Normal Nexus Smart Switch | | RTSN100A3 |
| | RTSD100A3 | 100 amp Service Entrance Rated Nexus Smart Switch | | RTSE100A3 |
| | RTSX150A3 | 150 amp Normal Nexus Smart Switch | | |
| | RTSD150A3 | 150 amp Service Entrance Rated Nexus Smart Switch | | |
| | RTSX200A3 | 200 amp Normal Nexus Smart Switch | | RTSN200A3 |
| | RTSD200A3 | 200 amp Service Entrance Rated Nexus Smart Switch | | RTSE200A3 |
| | RTSJ200A3 | LTS Load Shedding 200 amp switch | | RTSS200A3 |
| | 5449 | GenReady Load Center NEMA 1 | | 5449 |
| | 5454 | GenReady Load Center NEMA 3R | | 5454 |
| 5448 | Basic GenReady Load Center | | 5448 | |
| RTSE100A3CSA | 100 amp CSA Service Rated Switch | | | |
| RTSE200A3CSA | 200 amp CSA Service Rated Switch | | | |

| | | | | |
|--------------------|----------------------------------|---|--------------------|-----------|
| QT03624ANAX | | 36 kW Liquid-Cooled Generator - Aluminum | QT03624ANAN | |
| | RTSX100A3 | 100 amp Normal Nexus Smart Switch | | RTSN100A3 |
| | RTSD100A3 | 100 amp Service Entrance Rated Nexus Smart Switch | | RTSE100A3 |
| | RTSX150A3 | 150 amp Normal Nexus Smart Switch | | |
| | RTSD150A3 | 150 amp Service Entrance Rated Nexus Smart Switch | | |
| | RTSX200A3 | 200 amp Normal Nexus Smart Switch | | RTSN200A3 |
| | RTSD200A3 | 200 amp Service Entrance Rated Nexus Smart Switch | | RTSE200A3 |
| | RTSJ200A3 | LTS Load Shedding 200 amp switch | | RTSS200A3 |
| RTSE100A3CSA | 100 amp CSA Service Rated Switch | | | |
| RTSE200A3CSA | 200 amp CSA Service Rated Switch | | | |

| | | | | |
|--------------------|----------------------------------|---|--------------------|-----------|
| QT04524ANSX | | 45 kW Liquid-Cooled Generator - Steel | QT04524ANSN | |
| | RTSX100A3 | 100 amp Normal Nexus Smart Switch | | RTSN100A3 |
| | RTSD100A3 | 100 amp Service Entrance Rated Nexus Smart Switch | | RTSE100A3 |
| | RTSX200A3 | 200 amp Normal Nexus Smart Switch | | RTSN200A3 |
| | RTSD200A3 | 200 amp Service Entrance Rated Nexus Smart Switch | | RTSE200A3 |
| | RTSJ200A3 | LTS Load Shedding 200 amp switch | | RTSS200A3 |
| | RTSE100A3CSA | 100 amp CSA Service Rated Switch | | |
| RTSE200A3CSA | 200 amp CSA Service Rated Switch | | | |

| | | | | |
|--------------------|-----------------------------------|---|--------------------|-----------|
| QT04842ANAX | | 48 kW Liquid-Cooled Generator - Aluminum | QT04842ANAN | |
| | RTSX100A3 | 100 amp Normal Nexus Smart Switch | | RTSN100A3 |
| | RTSD100A3 | 100 amp Service Entrance Rated Nexus Smart Switch | | RTSE100A3 |
| | RTSX200A3 | 200 amp Normal Nexus Smart Switch | | RTSN200A3 |
| | RTSD200A3 | 200 amp Service Entrance Rated Nexus Smart Switch | | RTSE200A3 |
| | RTSJ200A3 | LTS Load Shedding 200 amp switch | | RTSS200A3 |
| | RTSE100A3CSA | 100 amp CSA Service Rated Switch | | |
| | RTSE200A3CSA | 200 amp CSA Service Rated Switch | | |
| RTSX400A3 | 400 amp Normal Nexus Smart Switch | | RTSE200A3 | |

| | | | | |
|--|----------------------------------|---|--------------------|-----------|
| QT06024ANSX* *This model available in Steel or Aluminum; Natural Gas or LP | | 60 kW Liquid-Cooled Generator - | QT06024ANSN | |
| | RTSX100A3 | 100 amp Normal Nexus Smart Switch | | RTSN100A3 |
| | RTSX200A3 | 100 amp Service Entrance Rated Nexus Smart Switch | | RTSN200A3 |
| | RTSD200A3 | 200 amp Normal Nexus Smart Switch | | RTSE200A3 |
| | RTSX400A3 | 200 amp Service Entrance Rated Nexus Smart Switch | | RTSN400A3 |
| | RTSD400A3 | 400 amp Normal Nexus Smart Switch | | RTSE200A3 |
| | RTSE100A3CSA | 100 amp CSA Service Rated Switch | | |
| RTSE200A3CSA | 200 amp CSA Service Rated Switch | | | |

| | | |
|---------------------------|---|---------------------------|
| RTS 100 - 400 amp* | 22-60 kW Liquid-Cooled Generator - 3 phase options | HTS 100 - 400 amp* |
| RTS 100 - 800 amp* | 70-150 kW Liquid-Cooled Generator | HTS 100 -800 amp* |

*(all NON service entrance rated)

NOTE: Combining a previous model transfer switch with a current Nexus model generator requires a kit #0H93030SRV to be installed to complete the battery charging circuit.