


High Density Slotted Duct



File # E64139 File # 49249

Product Selection													
Article No.	Part No.	Type	Width (W)	Height (H)	Width (W2)	Width (W3)	Width (W4)	Width (W5)	Width (W6)	Description	Color	Pkg. Qty.	
			in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)	in. (mm)			ft. (6 ft. lengths)	
2" x 3" (50.8 x 76.2) Nominal Duct Size													
184-23006	SLHD2X3W4	SLHD2X3								Three rows of holes .50" (12.7)	Non-Adhesive	White	120 ft
184-23003	SLHDA2X3W4	SLHDA2X3									Adhesive	White	120 ft
184-23004	SLHD2X3G4	SLHD2X3	2.02"	3.06"	2.00"	.16"	.40"	2.60"			Non-Adhesive	Gray	120 ft
181-00646	SLHDA2X3G4	SLHDA2X3	(51.3)	(77.7)	(50.8)	(4.1)	(10.2)	(66.0)			Adhesive	Gray	120 ft
181-00609	SLHD2X3BK4	SLHD2X3									Non-Adhesive	Black	120 ft
181-00645	SLHDA2X3BK4	SLHDA2X3									Adhesive	Black	120 ft
2" x 4" (50.8 x 101.6) Nominal Duct Size													
184-24007	SLHD2X4W4	SLHD2X4								Three rows of holes .50" (12.7)	Non-Adhesive	White	120 ft
184-24003	SLHDA2X4W4	SLHDA2X4									Adhesive	White	120 ft
184-24004	SLHD2X4G4	SLHD2X4	2.00"	4.06"	2.00"	.16"	.40"	3.60"			Non-Adhesive	Gray	120 ft
181-00648	SLHDA2X4G4	SLHDA2X4	(50.8)	(103.1)	(50.8)	(4.1)	(10.2)	(91.4)			Adhesive	Gray	120 ft
181-00610	SLHD2X4BK4	SLHD2X4									Non-Adhesive	Black	120 ft
181-00647	SLHDA2X4BK4	SLHDA2X4									Adhesive	Black	120 ft
3" x 1" (76.2 x 25.4) Nominal Duct Size													
181-00613	SLHD3X1W4	SLHD3X1								Three rows of holes 1.00" (25.4)	Non-Adhesive	White	120 ft
181-00652	SLHDA3X1W4	SLHDA3X1									Adhesive	White	120 ft
181-00612	SLHD3X1G4	SLHD3X1	3.02"	1.00"	3.00"	.16"	.40"	.75"			Non-Adhesive	Gray	120 ft
181-00651	SLHDA3X1G4	SLHDA3X1	(76.7)	(25.4)	(76.2)	(4.1)	(10.2)	(19.1)			Adhesive	Gray	120 ft
181-00611	SLHD3X1BK4	SLHD3X1									Non-Adhesive	Black	120 ft
181-00649	SLHDA3X1BK4	SLHDA3X1									Adhesive	Black	120 ft
3" x 2" (76.2 x 50.8) Nominal Duct Size													
184-32004	SLHD3X2W4	SLHD3X2								Three rows of holes 1.00" (25.4)	Non-Adhesive	White	120 ft
181-00655	SLHDA3X2W4	SLHDA3X2									Adhesive	White	120 ft
184-32001	SLHD3X2G4	SLHD3X2	3.03"	2.06"	3.00"	.16"	.40"	1.62"			Non-Adhesive	Gray	120 ft
181-00654	SLHDA3X2G4	SLHDA3X2	(77.0)	(52.3)	(76.2)	(4.1)	(10.2)	(41.1)			Adhesive	Gray	120 ft
181-00614	SLHD3X2BK4	SLHD3X2									Non-Adhesive	Black	120 ft
181-00653	SLHDA3X2BK4	SLHDA3X2									Adhesive	Black	120 ft
3" x 3" (76.2 x 76.2) Nominal Duct Size													
184-33004	SLHD3X3W4	SLHD3X3								Three rows of holes 1.00" (25.4)	Non-Adhesive	White	120 ft
184-33001	SLHDA3X3W4	SLHDA3X3									Adhesive	White	120 ft
184-33002	SLHD3X3G4	SLHD3X3	3.02"	3.06"	3.00"	.16"	.40"	2.60"			Non-Adhesive	Gray	120 ft
181-00657	SLHDA3X3G4	SLHDA3X3	(76.7)	(77.7)	(76.2)	(4.1)	(10.2)	(66.0)			Adhesive	Gray	120 ft
181-00615	SLHD3X3BK4	SLHD3X3									Non-Adhesive	Black	120 ft
181-00656	SLHDA3X3BK4	SLHDA3X3									Adhesive	Black	120 ft
3" x 4" (76.2 x 101.6) Nominal Duct Size													
184-34005	SLHD3X4W4	SLHD3X4								Three rows of holes 1.00" (25.4)	Non-Adhesive	White	120 ft
184-34001	SLHDA3X4W4	SLHDA3X4									Adhesive	White	120 ft
184-34003	SLHD3X4G4	SLHD3X4	3.00"	4.06"	3.00"	.16"	.40"	3.60"			Non-Adhesive	Gray	120 ft
181-00659	SLHDA3X4G4	SLHDA3X4	(76.2)	(103.1)	(76.2)	(4.1)	(10.2)	(91.4)			Adhesive	Gray	120 ft
181-00616	SLHD3X4BK4	SLHD3X4									Non-Adhesive	Black	120 ft
181-00658	SLHDA3X4BK4	SLHDA3X4									Adhesive	Black	120 ft

Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes. High density slotted wall duct in larger sizes continued on the next page. Covers are listed on page 117.