

Cable Ties with open head Q50I

Q-ties, Article number: 109-00049



[18 more images to Q50I >](#)

Features

- Open lock head for quick and easy insertion
- Integrated pre-locking function
- More than 25 % faster in application
- Inside serration for a strong hold around bundles
- Easy application either manually or with a processing tool

Certifications & Approvals



Application

Q-Series cable ties for bundling and securing cables, pipes a.d hoses. The innovative and effective cable ties enable a simple and quick installation.

Q-ties is suitable for following markets and industries




[Cable Ties with open head >](#)

Base Data

Application Tool	MK3PNSP2, MK3SP, MK6, MK7HT, MK7P, MK9HT/EVO9HT, MK9P, MK9/EVO9, MK20, MK21, EVO7, EVO7SP, EVO9, MK9SST
Colour	Black (BK)
Description Short (BMEcat) (max. 150 characters)	Cable Tie with open head 290x4.7 black
Fixation Method	None
Global Part Name	Q50I-PA66-BK
Identification Plate Position	none
Manufacturer Type	Q50I PA66 BK 100
Pack Cont.	100 pcs.
Product Family	Q-ties
Product Group	Cable Ties with open head
Quantity per	Bag
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Variant	Inside Serrated

Product Dimensions



Bundle Ø max.	75.0 mm
Length (L)	290 mm
Min.Tensile Strength	220 N
Thickness (T)	1.5 mm
Width (W)	4.7 mm

Material and Specifications

ELV compliant Dir. Art. 4 (2)	YES
Flammability	UL94 V2
Halogenfree	Yes
Hazardous goods	No
Material	Polyamide 6.6 (PA66)
Operating Temperature - °C	-40 °C to +85 °C

Logistics and Packaging

More Information

ETIM 5.0	EC000046
ETIM 6.0	EC000046
UNSPSC Key	39121703

Accessories



EVO9
110-80002
Manual Tensioning Tool
Plastic Housing



MK9P
110-09110
Pneumatic Tensioning Tool
Plastic Housing



MK21
110-21016
Manual Tensioning Tool for
Cable Ties, simple version



EVO7
110-70129
Manual Tensioning Tool
with Plastic Housing



EVO7SP
110-70130
Manual Tensioning Tool
Plastic Housing



MK9P
110-09100
Pneumatic Tensioning Tool
Plastic Housing

Similar products



Q18R
109-00030
Cable Ties with open head



Q18R
109-00147
Cable Ties with open head



Q18R
109-00148
Cable Ties with open head



Q18R
109-00149
Cable Ties with open head



Q18R
109-00150
Cable Ties with open head



Q18R
109-00059
Cable Ties with open head