


HS & S SERIES WIREWAY ACCESSORIES						
CATALOG NUMBER						DESCRIPTION
2.50 x 2.50 (64 x 64)	4.00 x 4.00 (102 x 102)	6.00 x 6.00 (152 x 152)	8.00 x 8.00 (203 x 203)	10.00 x 10.00* (254 x 254)	12.00 x 12.00* (305 x 305)	
E0202	E0404	E0606	E0808	—	—	End caps (with knockouts)
E0202NK	E0404NK	E0606NK	E0808NK	E1010NK	E1212NK	End caps (without knockouts)
T0202	T0404	T0606	T0808	T1010	T1212	Tee
X0202	X0404	X0606	X0808	X1010	X1212	Cross
AF0202	AF0404	AF0606	AF0808	AF1010	AF1212	Telescope
C0202	C0404	C0606	C0808	C1010	C1212	Connectors
PA0202	PA0404	PA0606	PA0808	PA1010	PA1212	Panel-Adapter
BH0202	BH0404	BH0606	BH0808	BH1010	BH1212	Bracket Hanger
—	R0402	R0604	R0806	R1008	R1208	Reducer
SL020290	SL040490	SL060690	SL080890	SL101090	SL121290	Sweep Elbow – 90°
L020290	L040490	L060690	L080890	L101090	L121290	Elbow – 90°
L020245	L040445	L060645	L080845	L101045	L121245	Elbow – 45°
S SERIES ACCESSORIES (GALVANIZED)						
—	E0404G	E0606G	E0808G	—	—	End caps (without knockouts)
E0202GNK	—	—	—	E1010GNK	E1212GNK	End caps (with knockouts)
T0202G	T0404G	T0606G	T0808G	T1010G	T1212G	Galvanized Tee
X0202G	X0404G	X0606G	X0808G	X1010G	X1212G	Galvanized Cross
AF0202G	AF0404G	AF0606G	AF0808G	AF1010G	AF1212G	Galvanized Telescope
C0202G	C0404G	C0606G	C0808G	C1010G	C1212G	Galvanized Connectors
PA0202G	PA0404G	PA0606G	PA0808G	PA1010G	PA1212G	Galvanized Panel-Adapter
BH0202G	BH0404G	BH0606G	BH0808G	BH1010G	BH1212G	Galvanized Bracket Hanger
—	R0402G	R0604G	R0806G	R1008G	R1208G	Galvanized Reducer
SL020290G	SL040490G	SL060690G	SL080890G	SL101090G	SL121290G	Galvanized Sweep Elbow – 90°
L020290G	L040490G	L060690G	L080890G	L101090G	L121290G	Galvanized Elbow – 90°
L020245G	L040445G	L060645G	L080845G	L101045G	L121245G	Galvanized Elbow – 45°

HS SERIES 2" STRAIGHT SECTION DIMENSIONS			
CATALOG NUMBER	A	B	C
HS221 & HS221NK	12.00 (300)	—	3.00 (75)
HS222 & HS222NK	24.00 (600)	1.00 (25)	7.00 (175)
HS223 & HS223NK	36.00 (900)	2.00 (50)	11.00 (275)
HS224 & HS224NK	48.00 (1200)	3.00 (75)	15.00 (375)
HS225 & HS225NK	60.00 (1500)	4.00 (100)	19.00 (475)
HS226 & HS226NK	72.00 (1800)	5.00 (125)	23.00 (575)
HS2210 & HS2210NK	120.00 (3000)	9.00 (225)	39.00 (975)

NK = No Knockouts



**HS SERIES 2" STRAIGHT SECTION DIMENSIONS**

PART NUMBER	PAGE	PART NUMBER	PAGE	PART NUMBER	PAGE	PART NUMBER	PAGE
JWN662	G12	L121290G	G2	LJW8QRSP	G8	LJWL908A	G8
JWN663	G12	LHPC02	G8	LJW902CCW	G8	LJWL908B	G8
JWN666	G12	LJW1261	G8	LJW902CW	G8	LJWL908C	G8
JWN881	G12	LJW12610	G8	LJW904CCW	G8	LJWN1266	G8
JWN882	G12	LJW1262	G8	LJW904CW	G8	LJWN221	G8
JWN883	G12	LJW1263	G8	LJW906CCW	G8	LJWN222	G8
JWN886	G12	LJW1264	G8	LJW906CW	G8	LJWN223	G8
JWRB42C	G12	LJW1265	G8	LJW908CCW	G8	LJWN226	G8
JWRB64C	G12	LJW126ASP	G8	LJW908CW	G8	LJWN441	G8
JWRB84C	G12	LJW126QRSP	G8	LJWA126	G8	LJWN442	G8
JWRB86C	G12	LJW21	G8	LJWA2	G8	LJWN443	G8
JWS2	G12	LJW210	G8	LJWA4	G8	LJWN446	G8
JWS4	G12	LJW21CCW	G8	LJWA6	G8	LJWN661	G8
JWS6	G12	LJW21CW	G8	LJWA8	G8	LJWN662	G8
JWS8	G12	LJW22	G8	LJWE126	G8	LJWN663	G8
JWSC22	G12	LJW23	G8	LJWE2	G8	LJWN666	G8
JWSC44	G12	LJW24	G8	LJWE4	G8	LJWN881	G8
JWSC66	G12	LJW25	G8	LJWE6	G8	LJWN882	G8
JWT2	G12	LJW2ASP	G8	LJWE8	G8	LJWN883	G8
JWT4	G12	LJW2QRSP	G8	LJWF126	G8	LJWN886	G8
JWT6	G12	LJW41	G8	LJWF2	G8	LJWRB1266	G8
JWT8	G12	LJW410	G8	LJWF4	G8	LJWRB42	G8
JWX2	G12	LJW41CCW	G8	LJWF6	G8	LJWRB64	G8
JWX4	G12	LJW41CW	G8	LJWF8	G8	LJWRB86	G8
JWX6	G12	LJW42	G8	LJWL45126A	G8	LJWS126	G8
JWX8	G12	LJW43	G8	LJWL452A	G8	LJWS2	G8
L020245	G2	LJW44	G8	LJWL452B	G8	LJWS4	G8
L020245G	G2	LJW45	G8	LJWL452C	G8	LJWS6	G8
L020290	G2	LJW4ASP	G8	LJWL454A	G8	LJWS8	G8
L020290G	G2	LJW4QRSP	G8	LJWL454B	G8	LJWT126A	G8
L040445	G2	LJW61	G8	LJWL454C	G8	LJWT2A	G8
L040445G	G2	LJW610	G8	LJWL456A	G8	LJWT2C	G8
L040490	G2	LJW61CCW	G8	LJWL456B	G8	LJWT4A	G8
L040490G	G2	LJW61CW	G8	LJWL456C	G8	LJWT4C	G8
L060645	G2	LJW62	G8	LJWL458A	G8	LJWT6A	G8
L060645G	G2	LJW63	G8	LJWL458B	G8	LJWT6C	G8
L060690	G2	LJW64	G8	LJWL458C	G8	LJWT8A	G8
L060690G	G2	LJW65	G8	LJWL90126A	G8	LJWT8C	G8
L080845	G2	LJW6ASP	G8	LJWL90126B	G8	LJWX126	G8
L080845G	G2	LJW6QRSP	G8	LJWL90126C	G8	LJWX2	G8
L080890	G2	LJW81	G8	LJWL902A	G8	LJWX4	G8
L080890G	G2	LJW810	G8	LJWL902B	G8	LJWX6	G8
L101045	G2	LJW81CCW	G8	LJWL902C	G8	LJWX8	G8
L101045G	G2	LJW81CW	G8	LJWL904A	G8	LOH100806	B8
L101090	G2	LJW82	G8	LJWL904B	G8	LOH121006	B8
L101090G	G2	LJW83	G8	LJWL904C	G8	LOH121206	B8
L121245	G2	LJW84	G8	LJWL906A	G8	LOH161206	B8
L121245G	G2	LJW85	G8	LJWL906B	G8	LOH161606	B8
L121290	G2	LJW8ASP	G8	LJWL906C	G8	LOH201606	B8