




15A 125V
 NEMA 5-15R
 UL CSA
 0.5 HP




20A 125V
 NEMA 5-20R
 UL CSA
 1 HP

Permanently Marked Receptacles


Duplex




BR15C1WHI



BR20C2GN



DR15C1GRY



DR20C2I

Description	Color	Catalog Number	
Smooth nylon face, one controlled face split circuit hot tab, permanently marked for use with automatic outlet control systems, back and side wired.	Black	BR15C1BLK	BR20C1BLK
	Blue	BR15C1BL	BR20C1BL
	Brown	BR15C1	BR20C1
	Gray	BR15C1GRY	BR20C1GRY
	Green	BR15C1GN	BR20C1GN
	Ivory	BR15C1I	BR20C1I
	Light Almond	BR15C1LA	BR20C1LA
	Red	BR15C1R	BR20C1R
	White	BR15C1WHI	BR20C1WHI
	Smooth nylon face, two controlled faces, permanently marked for use with automatic outlet control systems, back and side wired.	Black	BR15C2BLK
Blue		BR15C2BL	BR20C2BL
Brown		BR15C2	BR20C2
Gray		BR15C2GRY	BR20C2GRY
Green		BR15C2GN	BR20C2GN
Ivory		BR15C2I	BR20C2I
Light Almond		BR15C2LA	BR20C2LA
Red		BR15C2R	BR20C2R
White		BR15C2WHI	BR20C2WHI

Style Line® Decorator

Description	Color	Catalog Number	
Smooth nylon face, one controlled face split circuit hot tab, permanently marked for use with automatic outlet control systems, back and side wired.	Black	DR15C1BLK	DR20C1BLK
	Blue	DR15C1BL	DR20C1BL
	Brown	DR15C1	DR20C1
	Gray	DR15C1GRY	DR20C1GRY
	Green	DR15C1GN	DR20C1GN
	Ivory	DR15C1I	DR20C1I
	Light Almond	DR15C1LA	DR20C1LA
	Red	DR15C1R	DR20C1R
	White	DR15C1WHI	DR20C1WHI
	Smooth nylon face, two controlled faces, permanently marked for use with automatic outlet control systems, back and side wired.	Black	DR15C2BLK
Blue		DR15C2BL	DR20C2BL
Brown		DR15C2	DR20C2
Gray		DR15C2GRY	DR20C2GRY
Green		DR15C2GN	DR20C2GN
Ivory		DR15C2I	DR20C2I
Light Almond		DR15C2LA	DR20C2LA
Red		DR15C2R	DR20C2R
White		DR15C2WHI	DR20C2WHI

Permanent Controlled Receptacle Label

Description	Catalog Number
For use in retrofit applications where indication of a controlled receptacle is required. This label is UL approved for marking and labeling. 60 labels of each per pack	CL60

Dimensions in Inches (mm)