


**HUBBELL**  
**DELIVERY**

# HBL4750 Series Steel Raceway

Color	Base, 10ft	Cover, 5ft
Ivory	<b>HBL4750B10IV</b>	<b>HBL4750CIV</b>
Gray	<b>HBL4750B10GY</b>	<b>HBL4750CGY</b>

Note: Ivory metal raceway uses Almond (AL) plates, frames, devices, jacks and snap fits.



A: 4.75" (121)  
B: 1.75" (44)

Color	31.5" Precut Cover For mounting devices on 36" centers	19.5" Precut Cover For mounting devices on 24" centers	13.5" Precut Cover For mounting devices on 18" centers	7.5" Precut Cover For mounting devices on 12" centers
Ivory	<b>HBL4750C315IV</b>	<b>HBL4750C195IV</b>	<b>HBL4750C135IV</b>	<b>HBL4750C075IV</b>
Gray	<b>HBL4750C315GY</b>	<b>HBL4750C195GY</b>	<b>HBL4750C135GY</b>	<b>HBL4750C075GY</b>



Material	Divider 5ft Painted Steel	By-Pass Divider Painted Steel	Divider Clip use every 2.5ft	Coupling to couple together raceway	Wire Clip to hold conductors in place	Internal Corner Coupling
Galv. Steel	<b>HBL4750DGY</b>	<b>HBL4750BP</b>	<b>HBL4751DA</b>	<b>HBL4751AC</b>	<b>HBL4750WCGY</b>	<b>HBL4717TCAGY</b>



Color	Internal or External Elbow 45°	Internal Elbow Divided 1 1/4" Bend Radius	Internal Elbow Undivided	Internal Elbow Inverted Connects vertical run with horizontal run	External Elbow Divided 1 1/4" Bend Radius	External Elbow Undivided
Ivory	<b>HBL4712TXIV</b>	<b>HBL4717DFOIV</b>	<b>HBL4717IV</b>	<b>HBL4717NIV</b>	<b>HBL4718DFOIV</b>	<b>HBL4718IV</b>
Gray	<b>HBL4712TXGY</b>	<b>HBL4717DFOGY</b>	<b>HBL4717GY</b>	<b>HBL4717NGY</b>	<b>HBL4718DFOGY</b>	<b>HBL4718GY</b>



Color	Flat Elbow Divided 1 1/4" Bend Radius	Flat Elbow Undivided	Tee Fitting Divided 1 1/4" Bend Radius	Tee Fitting Undivided	Wall Box Connector for back feeding raceway	Bridge Fitting to bridge raceway over obstruction
Ivory	<b>HBL4711DFOIV</b>	<b>HBL4711IV</b>	<b>HBL4715DFOIV</b>	<b>HBL4715IV</b>	<b>HBL4714AIV</b>	<b>HBL4775DKITIV</b>
Gray	<b>HBL4711DFOGY</b>	<b>HBL4711GY</b>	<b>HBL4715DFOGY</b>	<b>HBL4715GY</b>	<b>HBL4714AGY</b>	<b>HBL4775DKITGY</b>



Color	Blank End Fitting (2) 1/2" KOs	Entrance End Fitting Divided 1 1/4" Bend Radius, 3/4", 1 and 1 1/4" KOs	Entrance End Fitting Undivided, 3/4", 1 and 1 1/4" KOs	90° Take-Off Connector for connecting HBL4750 to HBL3000	Connection Cover to hide seams in cover	Panel Connector for connecting to surface type panel boxes
Ivory	<b>HBL4710BIV</b>	<b>HBL4710DFOIV</b>	<b>HBL4710IV</b>	<b>HBL4774AIV</b>	<b>HBL4756AIV</b>	<b>HBL4786AIV</b>
Gray	<b>HBL4710BGY</b>	<b>HBL4710DFOGY</b>	<b>HBL4710GY</b>	<b>HBL4774AGY</b>	<b>HBL4756AGY</b>	<b>HBL4786AGY</b>