

| JW SERIES FEED THROUGH WIREWAY (FITTINGS) | | | | |
|---|----------------------------|----------------------------|----------------------------|--|
| CATALOG NUMBER | | | | DESCRIPTION |
| 2.50 x 2.50 (64 x 64) | 4.00 x 4.00 (102 x 102) | 6.00 x 6.00 (152 x 152) | 8.00 x 8.00 (203 x 203) | |
| JWS2 | JWS4 | JWS6 | JWS8 | Telescope* |
| JWF2 | JWF4 | JWF6 | JWF8 | Cut-off (1 set of gaskets and screws included) |
| JWL902 | JWL904 | JWL906 | JWL908 | 90 Degree elbow (1 set of gaskets and screws included) |
| JWL452 | JWL454 | JWL456 | JWL458 | 45 Degree elbow (1 set of gaskets and screws included) |
| JWT2 | JWT4 | JWT6 | JWT8 | Tee-top (2 sets of gaskets and screws included) |
| JWX2 | JWX4 | JWX6 | JWX8 | Cross (3 sets of gaskets and screws included) |
| JWE2 | JWE4 | JWE6 | JWE8 | End plate (1 set of gaskets and screws included) |
| JWA2 | JWA4 | JWA6 | JWA8 | Box adaptor (1 set of gaskets and screws included) |
| — | JWRB42C | — | — | Reducer 4.00" (102) to 2.50" (54) center hole** |
| — | — | JWRB64C | — | Reducer 6.00" (152) to 4.00" (102) center hole** |
| — | — | — | JWRB84C | Reducer 8.00" (203) to 4.00" (102) center hole** |
| — | — | — | JWRB86C | Reducer 8.00"(203) to 6.00" (152) center hole** |
| JWD2 | JWD4 | JWD6 | JWD8 | Drop-hanger |
| JWBH2 | JWBH4 | JWBH6 | JWBH8 | Bracket-hanger |
| JWN221 | JWN441 | JWN661 | JWN881 | 1.00" Nipple |
| JWN222 | JWN442 | JWN662 | JWN882 | 2.00" Nipple |
| JWN223 | JWN443 | JWN663 | JWN883 | 3.00" Nipple |
| JWN226 | JWN446 | JWN666 | JWN886 | 6.00" Nipple |
| JWSC22 | JWSC44 | JWSC66 | — | Swivel nipple-regular |
| JWFF2 | JWFF4 | JWFF6 | JWFF8 | Flexible fitting*** |
| — | JW4BK60 | JW6BK60 | JW8BK60 | 60.00" Barrier kit |
| JWG22 | JWG44 | JWG66 | JWG88 | Extra gasket and screws |

*Not UL listed.

**One set of gaskets and screws included with all reducers.

***Minimum length 3", maximum length 8".

| JW SERIES WIREWAY & FITTINGS DIMENSIONS | | | | | | | | | | | | | | | | | | |
|---|----------------|----------------|----------------|-----------------|-----------------|------------------|---------------|---------------|----------------|----------------|---------------|--------------|---------------|----------------|--------------|----------------|----------------|---------------|
| A X B | C - LENGTH | | | | | | D | E | F | G | H | J | K | P | R | S | T | U |
| 2.50x2.50 (64x64) | 12.00 (305) | 24.00 (610) | 36.00 (914) | 48.00 (1219) | 60.00 (1524) | 120.00 (3048) | 3.88 (99) | 3.88 (99) | 5.50 (140) | 8.50 (216) | 2.50 (64) | 2.00 (51) | 4.25 (108) | 4.63 (118) | 3.75 (95) | 9.31 (236) | 4.50 (114) | 4.38 (111) |
| 4.00x4.00 (102x102) | 12.00 (305) | 24.00 (610) | 36.00 (914) | 48.00 (1219) | 60.00 (1524) | 120.00 (3048) | 5.38 (137) | 5.38 (137) | 7.00 (178) | 10.00 (254) | 3.25 (83) | 2.44 (62) | 5.00 (127) | 6.13 (156) | 3.75 (95) | 11.75 (298) | 6.00 (152) | 5.88 (149) |
| 6.00x6.00 (152x152) | 12.00 (305) | 24.00 (610) | 36.00 (914) | 48.00 (1219) | 60.00 (1524) | 120.00 (3048) | 7.63 (194) | 7.63 (194) | 9.00 (229) | 12.00 (305) | 4.25 (108) | 3.00 (76) | 6.00 (152) | 8.25 (210) | 3.75 (95) | 15.25 (387) | 8.13 (207) | 7.88 (200) |
| 8.00x8.00 (203x203) | 12.00 (305) | 24.00 (610) | 36.00 (914) | 48.00 (1219) | 60.00 (1524) | 120.00 (3048) | 9.63 (245) | 9.63 (245) | 11.00 (279) | 14.00 (356) | 5.25 (133) | 3.75 (95) | 7.00 (178) | 10.25 (260) | 3.75 (95) | 20.56 (522) | 12.13 (308) | 9.88 (251) |

| PART NUMBER | PAGE | PART NUMBER | PAGE | PART NUMBER | PAGE | PART NUMBER | PAGE |
|---------------|------|-----------------|------|-----------------|------|----------------|------|
| JWN662..... | G12 | L121290G..... | G2 | LJW8QRSP..... | G8 | LJWL908A..... | G8 |
| JWN663..... | G12 | LHPC02..... | G8 | LJW902CCW..... | G8 | LJWL908B..... | G8 |
| JWN666..... | G12 | LJW1261..... | G8 | LJW902CW..... | G8 | LJWL908C..... | G8 |
| JWN881..... | G12 | LJW12610..... | G8 | LJW904CCW..... | G8 | LJWN1266..... | G8 |
| JWN882..... | G12 | LJW1262..... | G8 | LJW904CW..... | G8 | LJWN221..... | G8 |
| JWN883..... | G12 | LJW1263..... | G8 | LJW906CCW..... | G8 | LJWN222..... | G8 |
| JWN886..... | G12 | LJW1264..... | G8 | LJW906CW..... | G8 | LJWN223..... | G8 |
| JWRB42C..... | G12 | LJW1265..... | G8 | LJW908CCW..... | G8 | LJWN226..... | G8 |
| JWRB64C..... | G12 | LJW126ASP..... | G8 | LJW908CW..... | G8 | LJWN441..... | G8 |
| JWRB84C..... | G12 | LJW126QRSP..... | G8 | LJWA126..... | G8 | LJWN442..... | G8 |
| JWRB86C..... | G12 | LJW21..... | G8 | LJWA2..... | G8 | LJWN443..... | G8 |
| JWS2..... | G12 | LJW210..... | G8 | LJWA4..... | G8 | LJWN446..... | G8 |
| JWS4..... | G12 | LJW21CCW..... | G8 | LJWA6..... | G8 | LJWN661..... | G8 |
| JWS6..... | G12 | LJW21CW..... | G8 | LJWA8..... | G8 | LJWN662..... | G8 |
| JWS8..... | G12 | LJW22..... | G8 | LJWE126..... | G8 | LJWN663..... | G8 |
| JWSC22..... | G12 | LJW23..... | G8 | LJWE2..... | G8 | LJWN666..... | G8 |
| JWSC44..... | G12 | LJW24..... | G8 | LJWE4..... | G8 | LJWN881..... | G8 |
| JWSC66..... | G12 | LJW25..... | G8 | LJWE6..... | G8 | LJWN882..... | G8 |
| JWT2..... | G12 | LJW2ASP..... | G8 | LJWE8..... | G8 | LJWN883..... | G8 |
| JWT4..... | G12 | LJW2QRSP..... | G8 | LJWF126..... | G8 | LJWN886..... | G8 |
| JWT6..... | G12 | LJW41..... | G8 | LJWF2..... | G8 | LJWRB1266..... | G8 |
| JWT8..... | G12 | LJW410..... | G8 | LJWF4..... | G8 | LJWRB42..... | G8 |
| JWX2..... | G12 | LJW41CCW..... | G8 | LJWF6..... | G8 | LJWRB64..... | G8 |
| JWX4..... | G12 | LJW41CW..... | G8 | LJWF8..... | G8 | LJWRB86..... | G8 |
| JWX6..... | G12 | LJW42..... | G8 | LJWL45126A..... | G8 | LJWS126..... | G8 |
| JWX8..... | G12 | LJW43..... | G8 | LJWL452A..... | G8 | LJWS2..... | G8 |
| L020245..... | G2 | LJW44..... | G8 | LJWL452B..... | G8 | LJWS4..... | G8 |
| L020245G..... | G2 | LJW45..... | G8 | LJWL452C..... | G8 | LJWS6..... | G8 |
| L020290..... | G2 | LJW4ASP..... | G8 | LJWL454A..... | G8 | LJWS8..... | G8 |
| L020290G..... | G2 | LJW4QRSP..... | G8 | LJWL454B..... | G8 | LJWT126A..... | G8 |
| L040445..... | G2 | LJW61..... | G8 | LJWL454C..... | G8 | LJWT2A..... | G8 |
| L040445G..... | G2 | LJW610..... | G8 | LJWL456A..... | G8 | LJWT2C..... | G8 |
| L040490..... | G2 | LJW61CCW..... | G8 | LJWL456B..... | G8 | LJWT4A..... | G8 |
| L040490G..... | G2 | LJW61CW..... | G8 | LJWL456C..... | G8 | LJWT4C..... | G8 |
| L060645..... | G2 | LJW62..... | G8 | LJWL458A..... | G8 | LJWT6A..... | G8 |
| L060645G..... | G2 | LJW63..... | G8 | LJWL458B..... | G8 | LJWT6C..... | G8 |
| L060690..... | G2 | LJW64..... | G8 | LJWL458C..... | G8 | LJWT8A..... | G8 |
| L060690G..... | G2 | LJW65..... | G8 | LJWL90126A..... | G8 | LJWT8C..... | G8 |
| L080845..... | G2 | LJW6ASP..... | G8 | LJWL90126B..... | G8 | LJWX126..... | G8 |
| L080845G..... | G2 | LJW6QRSP..... | G8 | LJWL90126C..... | G8 | LJWX2..... | G8 |
| L080890..... | G2 | LJW81..... | G8 | LJWL902A..... | G8 | LJWX4..... | G8 |
| L080890G..... | G2 | LJW810..... | G8 | LJWL902B..... | G8 | LJWX6..... | G8 |
| L101045..... | G2 | LJW81CCW..... | G8 | LJWL902C..... | G8 | LJWX8..... | G8 |
| L101045G..... | G2 | LJW81CW..... | G8 | LJWL904A..... | G8 | LOH100806..... | B8 |
| L101090..... | G2 | LJW82..... | G8 | LJWL904B..... | G8 | LOH121006..... | B8 |
| L101090G..... | G2 | LJW83..... | G8 | LJWL904C..... | G8 | LOH121206..... | B8 |
| L121245..... | G2 | LJW84..... | G8 | LJWL906A..... | G8 | LOH161206..... | B8 |
| L121245G..... | G2 | LJW85..... | G8 | LJWL906B..... | G8 | LOH161606..... | B8 |
| L121290..... | G2 | LJW8ASP..... | G8 | LJWL906C..... | G8 | LOH201606..... | B8 |