

JW SERIES FEED THROUGH WIREWAY (FITTINGS)				
CATALOG NUMBER				DESCRIPTION
2.50 x 2.50 (64 x 64)	4.00 x 4.00 (102 x 102)	6.00 x 6.00 (152 x 152)	8.00 x 8.00 (203 x 203)	
JWS2	JWS4	JWS6	JWS8	Telescope*
JWF2	JWF4	JWF6	JWF8	Cut-off (1 set of gaskets and screws included)
JWL902	JWL904	JWL906	JWL908	90 Degree elbow (1 set of gaskets and screws included)
JWL452	JWL454	JWL456	JWL458	45 Degree elbow (1 set of gaskets and screws included)
JWT2	JWT4	JWT6	JWT8	Tee-top (2 sets of gaskets and screws included)
JWX2	JWX4	JWX6	JWX8	Cross (3 sets of gaskets and screws included)
JWE2	JWE4	JWE6	JWE8	End plate (1 set of gaskets and screws included)
JWA2	JWA4	JWA6	JWA8	Box adaptor (1 set of gaskets and screws included)
—	JWRB42C	—	—	Reducer 4.00" (102) to 2.50" (54) center hole**
—	—	JWRB64C	—	Reducer 6.00" (152) to 4.00" (102) center hole**
—	—	—	JWRB84C	Reducer 8.00" (203) to 4.00" (102) center hole**
—	—	—	JWRB86C	Reducer 8.00"(203) to 6.00" (152) center hole**
JWD2	JWD4	JWD6	JWD8	Drop-hanger
JWBH2	JWBH4	JWBH6	JWBH8	Bracket-hanger
JWN221	JWN441	JWN661	JWN881	1.00" Nipple
JWN222	JWN442	JWN662	JWN882	2.00" Nipple
JWN223	JWN443	JWN663	JWN883	3.00" Nipple
JWN226	JWN446	JWN666	JWN886	6.00" Nipple
JWSC22	JWSC44	JWSC66	—	Swivel nipple-regular
JWFF2	JWFF4	JWFF6	JWFF8	Flexible fitting***
—	JW4BK60	JW6BK60	JW8BK60	60.00" Barrier kit
JWG22	JWG44	JWG66	JWG88	Extra gasket and screws

*Not UL listed.

**One set of gaskets and screws included with all reducers.

***Minimum length 3", maximum length 8".

JW SERIES WIREWAY & FITTINGS DIMENSIONS																		
A X B	C - LENGTH						D	E	F	G	H	J	K	P	R	S	T	U
2.50x2.50 (64x64)	12.00 (305)	24.00 (610)	36.00 (914)	48.00 (1219)	60.00 (1524)	120.00 (3048)	3.88 (99)	3.88 (99)	5.50 (140)	8.50 (216)	2.50 (64)	2.00 (51)	4.25 (108)	4.63 (118)	3.75 (95)	9.31 (236)	4.50 (114)	4.38 (111)
4.00x4.00 (102x102)	12.00 (305)	24.00 (610)	36.00 (914)	48.00 (1219)	60.00 (1524)	120.00 (3048)	5.38 (137)	5.38 (137)	7.00 (178)	10.00 (254)	3.25 (83)	2.44 (62)	5.00 (127)	6.13 (156)	3.75 (95)	11.75 (298)	6.00 (152)	5.88 (149)
6.00x6.00 (152x152)	12.00 (305)	24.00 (610)	36.00 (914)	48.00 (1219)	60.00 (1524)	120.00 (3048)	7.63 (194)	7.63 (194)	9.00 (229)	12.00 (305)	4.25 (108)	3.00 (76)	6.00 (152)	8.25 (210)	3.75 (95)	15.25 (387)	8.13 (207)	7.88 (200)
8.00x8.00 (203x203)	12.00 (305)	24.00 (610)	36.00 (914)	48.00 (1219)	60.00 (1524)	120.00 (3048)	9.63 (245)	9.63 (245)	11.00 (279)	14.00 (356)	5.25 (133)	3.75 (95)	7.00 (178)	10.25 (260)	3.75 (95)	20.56 (522)	12.13 (308)	9.88 (251)

PART NUMBER	PAGE	PART NUMBER	PAGE	PART NUMBER	PAGE	PART NUMBER	PAGE
JWN662.....	G12	L121290G.....	G2	LJW8QRSP.....	G8	LJWL908A.....	G8
JWN663.....	G12	LHPC02.....	G8	LJW902CCW.....	G8	LJWL908B.....	G8
JWN666.....	G12	LJW1261.....	G8	LJW902CW.....	G8	LJWL908C.....	G8
JWN881.....	G12	LJW12610.....	G8	LJW904CCW.....	G8	LJWN1266.....	G8
JWN882.....	G12	LJW1262.....	G8	LJW904CW.....	G8	LJWN221.....	G8
JWN883.....	G12	LJW1263.....	G8	LJW906CCW.....	G8	LJWN222.....	G8
JWN886.....	G12	LJW1264.....	G8	LJW906CW.....	G8	LJWN223.....	G8
JWRB42C.....	G12	LJW1265.....	G8	LJW908CCW.....	G8	LJWN226.....	G8
JWRB64C.....	G12	LJW126ASP.....	G8	LJW908CW.....	G8	LJWN441.....	G8
JWRB84C.....	G12	LJW126QRSP.....	G8	LJWA126.....	G8	LJWN442.....	G8
JWRB86C.....	G12	LJW21.....	G8	LJWA2.....	G8	LJWN443.....	G8
JWS2.....	G12	LJW210.....	G8	LJWA4.....	G8	LJWN446.....	G8
JWS4.....	G12	LJW21CCW.....	G8	LJWA6.....	G8	LJWN661.....	G8
JWS6.....	G12	LJW21CW.....	G8	LJWA8.....	G8	LJWN662.....	G8
JWS8.....	G12	LJW22.....	G8	LJWE126.....	G8	LJWN663.....	G8
JWSC22.....	G12	LJW23.....	G8	LJWE2.....	G8	LJWN666.....	G8
JWSC44.....	G12	LJW24.....	G8	LJWE4.....	G8	LJWN881.....	G8
JWSC66.....	G12	LJW25.....	G8	LJWE6.....	G8	LJWN882.....	G8
JWT2.....	G12	LJW2ASP.....	G8	LJWE8.....	G8	LJWN883.....	G8
JWT4.....	G12	LJW2QRSP.....	G8	LJWF126.....	G8	LJWN886.....	G8
JWT6.....	G12	LJW41.....	G8	LJWF2.....	G8	LJWRB1266.....	G8
JWT8.....	G12	LJW410.....	G8	LJWF4.....	G8	LJWRB42.....	G8
JWX2.....	G12	LJW41CCW.....	G8	LJWF6.....	G8	LJWRB64.....	G8
JWX4.....	G12	LJW41CW.....	G8	LJWF8.....	G8	LJWRB86.....	G8
JWX6.....	G12	LJW42.....	G8	LJWL45126A.....	G8	LJWS126.....	G8
JWX8.....	G12	LJW43.....	G8	LJWL452A.....	G8	LJWS2.....	G8
L020245.....	G2	LJW44.....	G8	LJWL452B.....	G8	LJWS4.....	G8
L020245G.....	G2	LJW45.....	G8	LJWL452C.....	G8	LJWS6.....	G8
L020290.....	G2	LJW4ASP.....	G8	LJWL454A.....	G8	LJWS8.....	G8
L020290G.....	G2	LJW4QRSP.....	G8	LJWL454B.....	G8	LJWT126A.....	G8
L040445.....	G2	LJW61.....	G8	LJWL454C.....	G8	LJWT2A.....	G8
L040445G.....	G2	LJW610.....	G8	LJWL454A.....	G8	LJWT2C.....	G8
L040490.....	G2	LJW61CCW.....	G8	LJWL456A.....	G8	LJWT4A.....	G8
L040490G.....	G2	LJW61CW.....	G8	LJWL456B.....	G8	LJWT4C.....	G8
L060645.....	G2	LJW62.....	G8	LJWL456C.....	G8	LJWT6A.....	G8
L060645G.....	G2	LJW63.....	G8	LJWL458A.....	G8	LJWT6C.....	G8
L060690.....	G2	LJW64.....	G8	LJWL458B.....	G8	LJWT8A.....	G8
L060690G.....	G2	LJW65.....	G8	LJWL458C.....	G8	LJWT8C.....	G8
L080845.....	G2	LJW6ASP.....	G8	LJWL90126A.....	G8	LJWX126.....	G8
L080845G.....	G2	LJW6QRSP.....	G8	LJWL90126B.....	G8	LJWX2.....	G8
L080890.....	G2	LJW81.....	G8	LJWL90126C.....	G8	LJWX4.....	G8
L080890G.....	G2	LJW810.....	G8	LJWL902A.....	G8	LJWX6.....	G8
L101045.....	G2	LJW81CCW.....	G8	LJWL902B.....	G8	LJWX8.....	G8
L101045G.....	G2	LJW81CW.....	G8	LJWL902C.....	G8	LOH100806.....	B8
L101090.....	G2	LJW82.....	G8	LJWL904A.....	G8	LOH121006.....	B8
L101090G.....	G2	LJW83.....	G8	LJWL904B.....	G8	LOH121206.....	B8
L121245.....	G2	LJW84.....	G8	LJWL904C.....	G8	LOH161206.....	B8
L121245G.....	G2	LJW85.....	G8	LJWL906A.....	G8	LOH161606.....	B8
L121290.....	G2	LJW8ASP.....	G8	LJWL906B.....	G8	LOH201606.....	B8
				LJWL906C.....	G8		