

Kellems® Wire Management Products

Deluxe Cord Grips

Aluminum Fittings, Stainless Steel Mesh, Liquidtight, for Insulated Cables



Straight Female Thread

N.P.T. Thread Size Inches	Grip Diameter Range Inches (cm)	Form Size	Catalog Number
1/2	.375"-.500" (.95-1.27)	F2	07401043
	.500"-.625" (1.27-1.59)		07401045
3/4	.500"-.625" (1.27-1.59)	F2	07401052
3/4	.625"-.750" (1.59-1.90)	F4	07401053

WARNING!

It is important that you read all breaking strength, safety and technical data relating to this product on pages T-71 through T-76.

90° Male Thread

N.P.T. Thread Size Inches	Grip Diameter Range Inches (cm)	Form Size	Catalog Number
3/8	.250"-.312" (.63-.79)	F1	07401071
	.312"-.375" (.79-.95)		07401072
	.375"-.437" (.95-1.11)		07401073
1/2	.187"-.250" (.47-.63)	F2	07401074
	.250"-.375" (.63-.95)		07401076
	.375"-.500" (.95-1.27)		07401078
	.500"-.625" (1.27-1.59)		07401080*
3/4	.375"-.500" (.95-1.27)	F3	07401081
	.500"-.625" (1.27-1.59)		07401083
	.625"-.750" (1.59-1.90)		07401084*
	.750"-.875" (1.90-2.22)		074011275*
	.500"-.625" (1.27-1.59)		07401085
1	.625"-.750" (1.59-1.90)	F4	07401087
	.750"-.875" (1.90-2.22)		07401089
	.875"-.1.000" (2.22-2.54)		07401091*
	1.000"-.1.125" (2.54-2.86)		074011229*
	.750"-.875" (1.90-2.22)		074011230
1 1/4	.875"-.1.000" (2.22-2.54)	F5	07401137
	1.000"-.1.125" (2.54-2.86)		07401108
	1.125"-.1.250" (2.86-3.17)		074011042*
	1.000"-.1.125" (2.54-2.86)		074011045
1 1/2	1.125"-.1.250" (2.86-3.17)	F5	074011046
	1.250"-.1.375" (3.17-3.49)		074011047
	1.312"-.1.437" (3.33-3.65)		074011233
2	1.437"-.1.562" (3.65-3.97)	F6	074011244
	1.687"-.1.812" (4.28-4.60)		074011246
	1.750"-.1.875" (4.44-4.76)		074011234*



Straight Female



90° Male



45° Male

45° Male Thread

N.P.T. Thread Size Inches	Grip Diameter Range Inches (cm)	Form Size	Catalog Number
1/2	.250"-.375" (.63-.95)	F2	074011236
	.375"-.500" (.95-1.27)		074011021
	.500"-.625" (1.27-1.59)		074011237*
3/4	.500"-.625" (1.27-1.59)	F3	074011049
	.625"-.750" (1.59-1.90)		074011051*
	.750"-.875" (1.90-2.22)		074011239*
1	.625"-.750" (1.59-1.90)	F4	074011055
	.750"-.875" (1.90-2.22)		074011057
	.875"-.1.000" (2.22-2.54)		074011199*
1 1/4	1.000"-.1.125" (2.54-2.86)	F5	074011059
	1.125"-.1.250" (2.86-3.17)		074011060

Note: Kellems® Deluxe Cord Grips are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 of the National Electric Code Sections 501.10(b)(2), 502.10(a)(2), 502.10(b)(2), 503.10(a)(2) and 503.10(b).

* Cable jacket may have to be stripped to pass through connector body.

