











Straight Blade Devices
15 and 20 Ampere, 125 Volts
 2 Pole, 3 Wire Grounding
**Commercial Specification Grade
 Duplex Receptacles**



Receptacles

Commercial Specification Grade, Duplex, Side Wired Only

Description	Color	Catalog Number	
Smooth nylon face.	Almond	CR15AL	CR20AL
	Black	CR15BLK	CR20BLK
	Brown	CR15	CR20
	Gray	CR15GRY	CR20GRY
	Ivory	CR15I	CR20I
	Light Almond	CR15LA	CR20LA
	Office White	CR15OW	CR20OW
	White	CR15WHI	CR20WHI
 Tamper-Resistant*, smooth nylon face.	Almond	CR15ALTR	CR20ALTR
	Black	CR15BLKTR	CR20BLKTR
	Brown	CR15TR	CR20TR
	Gray	CR15GRYTR	CR20GRYTR
	Ivory	CR15ITR	CR20ITR
	Light Almond	CR15LATR	CR20LATR
	White	CR15WHITR	CR20WHITR
	Finder groove, nylon face.	Almond	CRF15AL
Black		CRF15BLK	CRF20BLK
Brown		CRF15	CRF20
Gray		CRF15GRY	CRF20GRY
Ivory		CRF15I	CRF20I
Light Almond		CRF15LA	CRF20LA
Office White		CRF15OW	CRF20OW
White		CRF15WHI	CRF20WHI
Pre-wired receptacles; smooth nylon face; self-grounding; 8" solid wire leads.	Almond	CR15ALP1	CR20ALP1
	Black	CR15BLKP1	CR20BLKP1
	Brown	CR15P1	CR20P1
	Gray	CR15GRYP1	CR20GRYP1
	Ivory	CR15IP1	CR20IP1
	Light Almond	CR15LAP1	CR20LAP1
	White	CR15WHIP1	CR20WHIP1
	Pre-wired receptacles; smooth nylon face; self-grounding; 8" stranded wire leads.	Almond	CR15ALP2
Black		CR15BLKP2	CR20BLKP2
Brown		CR15P2	CR20P2
Gray		CR15GRYP2	CR20GRYP2
Ivory		CR15IP2	CR20IP2
Light Almond		CR15LAP2	CR20LAP2
White		CR15WHIP2	CR20WHIP2
 Pre-wired receptacles; Tamper-Resistant*, smooth nylon face; self-grounding; 8" solid wire leads.		Almond	CR15ALTRP1
	Black	CR15BLKTRP1	CR20BLKTRP1
	Brown	CR15TRP1	CR20TRP1
	Gray	CR15GRYTRP1	CR20GRYTRP1
	Ivory	CR15ITRP1	CR20ITRP1
	Light Almond	CR15LATRP1	CR20LATRP1
	White	CR15WHITRP1	CR20WHITRP1
	 Pre-wired receptacles; Tamper-Resistant*, smooth nylon face; self-grounding; 8" stranded wire leads.	Almond	CR15ALTRP2
Black		CR15BLKTRP2	CR20BLKTRP2
Brown		CR15TRP2	CR20TRP2
Gray		CR15GRYTRP2	CR20GRYTRP2
Ivory		CR15ITRP2	CR20ITRP2
Light Almond		CR15LATRP2	CR20LATRP2
White		CR15WHITRP2	CR20WHITRP2



Note: * Tamper-resistant devices are not Fed. Spec. Listed.
 See page A-15 for NEC® Tamper-Resistant Code Requirements.
 See page A-46 for accessories.
 See page A-57 for technical information.
 See Section K for wallplates.